#### 25A-JMHZ2 Series

RoHS

Compact Type Parallel Style Air Gripper/With Positioning Pins on the Lateral Mounting Surface

25A-JMHZ2-X6900(A, B) (Made to Order)
Compact Type Parallel Style Air Gripper/Lateral Auto Switch Mounting

**25A-JMHZ2-X7460** (Made to Order)

Ø8, Ø12, Ø16, Ø20

How to Order

#### **Bore Size**

ø**8 to** ø**20** 

25A-JMHZ2-16D - M9BW


Series compatible with secondary batteries

Number of fingers
2 2

2 Bore size	
8	8 mm
12	12 mm
16	16 mm
20	20 mm

3 Action		
D	Double acting	

1	Finger option	
[	Nil	Standard
	1	Side tapped mounting
	2	Through-holes in opening/ closing direction



Number of auto switches

Nil 2
S 1
n n

\* The 25A- series specifications and dimensions are the same as those of the standard model. For details, refer to the Web Catalog.

#### **Bore Size**

Ø8 to Ø20 Made to Order

Series compatible with secondary batteries

With positioning pins on the lateral mounting surface


Number of fingers

2 Bore size		
8	8 mm	
12	12 mm	
16	16 mm	
20	20 mm	



4 Finger option	
Nil	Standard
1	Side tapped mounting
2	Through-holes in opening/ closing direction





Auto switch

Without auto switch

Nil Without auto switch (Built-in magnet)

 Refer to page 260 for applicable auto switch models. 6 Number of auto switches

Nil	2
S	1
n	n

\* The 25A- series have the same specifications and dimensions as those of the JMHZ2-X6900(A, B) (made-to-order individual specifications). For details, refer to the Web Catalog.

#### **Bore Size**

Ø8 to Ø20
Made to Order

25A-JMHZ2-16D - M9BW - X7460

Series compatible with secondary batteries

Number of fingers
2 2

2 Bore size		
8	8 mm	
12	12 mm	
16	16 mm	
20	20 mm	

3 Action
D Double actin

4 Finger option		
g	Nil	Standard
	1	Side tapped mounting
	2	Through-holes in opening/ closing direction

Auto switch
 Without auto switch

Nil Without auto switch (Built-in magnet)

Refer to page 260 for applicable auto switch models.

6 Number of auto switches		
Nil	2	
S	1	

switch mounting

\* The 25A- series have the same specifications and dimensions as those of the JMHZ2-X7460 (made-to-order individual specifications). For details, refer to the Web Catalog.

164

rs Control Valves

Related Air Cylinders

tors Pro

Air Grippers

Vacuum Equipment

Air Preparation Equipment

Clean Air Filters

Modular F.R.L./ ressure Control Equipment

Flow Control Equipment/ Fittings

> Detection Switches

Fluid Control Equipment

Process Gas Equipment


Electric Actuators


# Parallel Type Air Gripper Standard Type

## 25A-MHZ2 Series

Ø10, Ø16, Ø20, Ø25, Ø32, Ø40








\* The 25A- series specifications and dimensions are the same as those of the standard model.

# Parallel Type Air Gripper Long Stroke Type

25A-MHZL2 Series



Ø10, Ø16, Ø20, Ø25



The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.

Air Cylinders Control Valves

Related Products

Rotary Actuators Air Grippers

Equipment Vacuum

Air Preparation


Flow Control Equipment/ Fittings

Detection Switches


Process Gas Fluid Control Equipment Equipment

Electric Actuators

#### **Parallel Type Air Gripper with Dust Cover 25A-MHZJ2** Series **RoHS 25A-MHZJ2-X6100** (Made to Order) Parallel Type Air Gripper with Dust Cover: Long Stroke Type **25A-MHZL2-X5955** (Made to Order)



Long Stroke Type/ With Dust Cover (Made to Order)



For details, refer to the Web Catalog.

MHZJ2-X6100 (made-to-order individual specifications).


For details, refer to the Web Catalog.



### **Low Profile Air Gripper** 25A-MHF2 Series

Ø8, Ø12, Ø16, Ø20





\* The 25A- series specifications and dimensions are the same as those of the standard model.


For details, refer to the Web Catalog.

#### Parallel Type Air Gripper: Wide Type

# 25A-MHL2 Series


Ø10, Ø16, Ø20, Ø25, Ø32, Ø40

RoHS



\* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.



\* The 25A- series specifications and dimensions are the same as those of the standard model.




## Parallel Type Air Gripper

# 25A-MHS Series

Ø16, Ø20, Ø25, Ø32

RoHS





\* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.

Air Cylinders Control Valves

Related Products

Rotary Actuators

Air Grippers

Vacuum Equipment

Air Preparation Equipment

Clean Air Filters

Flow Control Equipment/ Fittings

Detection Switches

Process Gas Fluid Control Equipment Equipment


Electric Actuators

# Parallel Type Air Gripper 3-Finger Type with Dust Cover

# 25A-MHSJ3 Series

Ø16, Ø20, Ø25, Ø32

RoHS



\* The 25A- series specifications and dimensions are the same as those of the standard model.


For details, refer to the **Web Catalog**.

#### 180° Angular Type Air Gripper Cam Type

# 25A-MHY2 Series

Ø10, Ø16, Ø20, Ø25

**RoHS** 




\* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.

Air Cylinders Control Valves

# 180° Angular Type Air Gripper Rack & Pinion Type 25A-NHV2 Series Ø20, Ø25, Ø32, Ø40, Ø50



- \* Change of material and surface treatment are not available for the bearing or the parallel key.
- \* As metal-to-metal collision occurs when the fingers are fully closed, dust particles may be generated.

\* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.