25A-VP346E/546E/746E/946E Series

CE UKCA cULus RoHS

* Excludes the high-pressure (K) type

How to Order

Modular Type **25A – VP [5] 46 E [ ] – 5 [DZ] [ ] 1 – [R] – [ ]**


Series compatible with secondary batteries

Series


3	VP300
5	VP500
7	VP700
9	VP900

Symbol

Residual pressure relief 3-port solenoid valve



With soft start-up function



Solenoid valve type

E	Residual pressure relief 3-port solenoid valve

Pressure specifications

		Series			
		VP300	VP500	VP700	VP900
Nil	Standard (0.7 MPa)	●	●	●	●
K	High pressure (1.0 MPa)	–	●	●	–

Soft start-up function

Nil	None
S	With soft start-up function

Flow direction




Nil	Left to right
R	Right to left

Rated voltage

DC

5	24 VDC

Electrical entry

DIN terminal	DIN (EN 175301-803C) terminal	M12 connector
		
D: With connector **DZ**: With connector/ With light/surge voltage suppressor	**Y**: With connector **YZ**: With connector/ With light/surge voltage suppressor	**KOZ**: Without connector

Manual override

			Series			
			VP300	VP500	VP700	VP900
Nil	Non-locking push type		●	●	●	●
A	Non-locking push type (Manual)		–	●	●	–
E	Push-turn locking type (Manual)		●	●	●	●

Refer to the Web Catalog.

• Specifications/Dimensions
* Same as the standard product

Click here for details. ▶▶▶