

## Product Information for Series EAK

MODELS			
Model	Port Size	Effective Area (mm <sup>2</sup> )	Weight (g)
EAK2000-F01	1/8	25	105
EAK2000-F02	1/4	27.5	100
EAK4000-F02	1/4	47	155
EAK4000-F03	3/8	85	150
EAK4000-F04	1/2	95	140
EAK6000-F06	3/4	200	345
EAK6000-F10	1	230	315
SPECIFICATIONS			
<b>Fluid</b>	Air		
<b>Proof pressure</b>	1.5MPa		
<b>Maximum operating pressure</b>	1MPa		
<b>Minimum operating pressure</b>	0.02MPa		
<b>Ambient and fluid temperature</b>	-5 to 60°C (no freezing)		

*Last Updated on 4/8/02*

*By LA*