



Product Note, PN 416, Rev 14
Product Shipping Weights

January 20, 2025

Caution: Shipping weights are approximate and vary per configuration, installed accessories and mode of packaging.

REGULATORS

MODEL	WEIGHT-POUNDS	WEIGHT-KILOGRAMS
AP20	0.4	0.18
AP500	1.00	0.45
AP1000, AZ1000	2.75	1.25
AP1100	2.75	1.25
AP1200, AZ1200	4.40	2.00
AZ1300	4.40	2.00
AP1400, AZ1400	4.50	2.04
AP1500, AZ1500	2.80	1.27
AZ9200	5.00	2.27
AP1600	3.40	1.54
AP1700	4.50	2.04
AP1900	3.40	1.54
AP2700	5.00	2.27
AP9000, AP90PA	13.0	5.90
AP10PA, AZ10PA	3.00	1.36
AP12PA, AZ12PA	5.15	2.34
AP14PAT, AZ14PAT	5.25	2.39
AP15PA, AZ15PA	3.00	1.36
SL5200	1.00	0.45
SL5400	4.20	1.91
SL5500	3.60	1.63
SL5800	4.20	1.91
AK100	1.00	0.45
AK1000	2.40	1.09
AK1000T	1.4	0.64
AK1100	2.40	1.09
AK1200	4.40	2.00
AK1300	4.40	2.00
AK1400	4.50	2.04

AK1500	2.60	1.18
AK1700	4.30	1.95
BP1000	2.50	1.20
AKM60	5.00	2.26
AK M80	8.00	3.60
KT8	3.00	1.36
KT9	3.00	1.36
KT10	5.00	2.30
KT12	7.00	3.10
VS1000	3.95	1.79
AK10PA	3.00	1.36
AK12PA	5.15	2.34
AK14PAT	5.25	2.39
AK15PA	3.00	1.36
AK9200	4.75	2.16

VALVES

MODEL	WEIGHT-POUNDS	WEIGHT-KILOGRAMS
AK/AP/AZ3000	2.8	1.27
AK/AP/AZ3004	2.8	1.27
AK/AP/AZ3007	3.1	1.40
AK/AP/AZ3080, 3084	3.1	1.40
AP3100	2.8	1.27
AP3200, 3202	2.8	1.27
AP3260, 3262, 3225	1.0	.45
AK/AP/AZ3540, 4540	1.5	0.68
AK/AP/AZ3542, 4542	1.5	0.68
AK/AP/AZ3550, 4550	1.8	0.82
AK/AP/AZ3571, 4571	1.8	0.82
AK/AP/AZ3580, 4580	1.5	0.68
AK/AP/AZ3600, 4600	0.9	0.41
AK/AP/AZ3604	0.9	0.41
AK/AP/AZ3624	1.0	0.45
AK/AP/AZ3625, 4625	1.0	0.45
AK/AP/AZ3627	1.2	0.55
AK/AP/AZ3650, 4650	0.9	0.40
AK/AP/AZ3652, 4652	1.0	0.45
AK/AP/AZ3657, 4657	0.9	0.40
AP3659/4659	1.0	0.45
AK/AP/AZ3672, 3675	0.6	0.27
AP3700	3.4	1.54
AZ3700	3.2	1.45
AP3800	3.0	1.36
AZ3800	2.8	1.27



AP3900	3.2	1.45
AZ3900	3.0	1.36
AP4000	2.8	1.27
AP/AZ4141	2.0	0.91
AP/AZ4150, 4157	1.6	0.73
AP4440	1.9	.86
AP4457, 4459	1.5	.69
AZ9600	7.6	3.45
APM60	4.3	1.95
BZ91TM 2P B16 B16 00 (BZ Weight Varies by Model)	14.0	6.36

OTHER UHP DEVICES

MODEL	WEIGHT-POUNDS	WEIGHT-KILOGRAMS
AP64	0.05	0.02
AP7	0.25	0.11
AP70	0.30	0.14
AP71	0.30	0.14
AP72	1.80	0.82
AP74	0.25	0.11
AP74B	1.25	0.56