



SY3000 Accessory Components

Replacement One Touch Fittings				
Port Size		Type	Part Number	
A, B Port	Metric Size	Straight Type	Ø2	VVQ1000-50A-C2
			Ø3.2	VVQ1000-50A-C3
			Ø4	VVQ1000-50A-C4
			Ø6	VVQ1000-50A-C6
		Elbow Type	Ø4	SZ3000-73-1A-L4
			Ø6	SZ3000-73-1A-L6
	Inch Size	Straight Type 	Ø1/8"	VVQ1000-50A-N1
			Ø5/32"	VVQ1000-50A-N3
			Ø1/4"	VVQ1000-50A-N7
		Elbow Type	Ø5/32"	KJL03-95-X224
			Ø1/4"	KJL07-95-X224
		Long Elbow Type 	Ø5/32"	KJL03-95-X225
	Ø1/4"	KJL07-95-X225		
P, E Port	Metric Size	Straight Type	Ø8	VVQ1000-51A-C8
		Elbow Type	Ø8	SZ3000-74-1A-L8
		Long Elbow Type	Ø8	SZ3000-74-2A-L8
	Inch Size	Straight Type	Ø5/16"	VVQ1000-51A-N9
		Elbow Type	Ø5/16"	KQ2L09-14-X224
		Long Elbow Type	Ø5/16"	KQ2L09-14-X225
A, B Port			VVQ0000-58A	
P, E Port			VVQ1000-58A	

Manifold Options	Port Size		Type	Part Number
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Ø2	Straight	SY30M-78-1A-C2
		Ø3		SY30M-78-1A-C3
		Ø4		SY30M-78-1A-C4
		Ø6		SY30M-78-1A-C6
	Inch	Ø1/8"	Straight	SY30M-78-1A-N1
		Ø5/32"		SY30M-78-1A-N3
		Ø1/4"		SY30M-78-1A-N7
	Metric	Ø4	Short Elbow	SY30M-78-2A-L4
		Ø6		SY30M-78-2A-L6
	Inch	Ø5/32"	Short Elbow	SY30M-78-2A-LN3
		Ø1/4"		SY30M-78-2A-LN7
	Metric	Ø4	Long Elbow	SY30M-78-3A-L4
Ø6		SY30M-78-3A-L6		
Inch	Ø5/32"	SY30M-78-3A-LN3		
	Ø1/4"	SY30M-78-3A-LN7		
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Ø2	Straight	SY30M-79-1A-C2
		Ø3		SY30M-79-1A-C3
		Ø4		SY30M-79-1A-C4
		Ø6		SY30M-79-1A-C6
	Inch	Ø1/8"	Straight	SY30M-79-1A-N1
		Ø5/32"		SY30M-79-1A-N3
		Ø1/4"		SY30M-79-1A-N7
	Metric	Ø4	Short Elbow	SY30M-79-2A-L4
		Ø6		SY30M-79-2A-L6
	Inch	Ø5/32"	Short Elbow	SY30M-79-2A-LN3
		Ø1/4"		SY30M-79-2A-LN7
	Metric	Ø4	Long Elbow	SY30M-79-3A-L4
Ø6		SY30M-79-3A-L6		
Inch	Ø5/32"	SY30M-79-3A-LN3		
	Ø1/4"	SY30M-79-3A-LN7		
SUP blocking disk				SY30M-40-1A
EXH Blocking Disk				SY30M-40-2A
Label for Blocking Disk				SJ3000-155-1A
Back Pressure Check Valve Assembly				SY30M-24-1A

Cable Type	Length	Part Number
D-SUB	1.5 m	AXT100-DS25-015
	3 m	AXT100-DS25-030
	5 m	AXT100-DS25-050
IP67 D-SUB	1.5 m	SY30M-DS25-015
	3 m	SY30M-DS25-030
	5 m	SY30M-DS25-050
Flat Ribbon 26 Pin	1.5 m	AXT100-FC26-1
	3 m	AXT100-FC26-2
	5 m	AXT100-FC26-3
Flat Ribbon 20 Pin	1.5 m	AXT100-FC20-1
	3 m	AXT100-FC20-2
	5 m	AXT100-FC20-3
Flat Ribbon 10 Pin	1.5 m	AXT100-FC10-1
	3 m	AXT100-FC10-2
	5 m	AXT100-FC10-3