



SY3000 D-SUB, Flat Ribbon, PC Wiring Accessory Components

Replacement One Touch Fittings				
Port Size		Fitting Type	Part Number	
A, B Port	Metric	Straight	Ø2	VVQ1000-50A-C2
			Ø3.2	VVQ1000-50A-C3
			Ø4	VVQ1000-50A-C4
			Ø6	VVQ1000-50A-C6
		Elbow	Ø4	SZ3000-73-1A-L4
			Ø6	SZ3000-73-1A-L6
	Long Elbow	Ø4	SZ3000-73-2A-L4	
		Ø6	SZ3000-73-2A-L6	
	Inch	Straight 	Ø1/8"	VVQ1000-50A-N1
			Ø5/32"	VVQ1000-50A-N3
			Ø1/4"	VVQ1000-50A-N7
		Elbow	Ø5/32"	KJL03-95-X224
			Ø1/4"	KJL07-95-X224
		Long Elbow 	Ø5/32"	KJL03-95-X225
Ø1/4"			KJL07-95-X225	
P, E Port	Metric	Straight	Ø8	VVQ1000-51A-C8
			Elbow	SZ3000-74-1A-L8
		Long Elbow	SZ3000-74-2A-L8	
	Inch	Straight	Ø5/16"	VVQ1000-51A-N9
			Elbow	KQ2L09-14-X224
		Long Elbow	KQ2L09-14-X225	
Plug Assembly		For A, B Port	VVQ0000-58A	
		For P, E Port	VVQ1000-58A	

Manifold Options	Port Size		Type	Part Number
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Ø2 Ø3 Ø4 Ø6	Straight	SY30M-78-1A-C2
				SY30M-78-1A-C3
				SY30M-78-1A-C4
				SY30M-78-1A-C6
				SY30M-78-1A-N1
				SY30M-78-1A-N3
	Inch	Ø1/8" Ø5/32" Ø1/4"		SY30M-78-1A-N7
	Metric	Ø4 Ø6	Short Elbow	SY30M-78-2A-L4
				SY30M-78-2A-L6
				SY30M-78-2A-LN3
	Inch	Ø5/32" Ø1/4"		SY30M-78-2A-LN7
	Metric	Ø4 Ø6	Long Elbow	SY30M-78-3A-L4
SY30M-78-3A-L6				
SY30M-78-3A-LN3				
SY30M-78-3A-LN7				
Inch	Ø5/32" Ø1/4"			
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Ø2 Ø3 Ø4 Ø6	Straight	SY30M-79-1A-C2
				SY30M-79-1A-C3
				SY30M-79-1A-C4
				SY30M-79-1A-C6
				SY30M-79-1A-N1
				SY30M-79-1A-N3
	Inch	Ø1/8" Ø5/32" Ø1/4"		SY30M-79-1A-N7
	Metric	Ø4 Ø6	Short Elbow	SY30M-79-2A-L4
				SY30M-79-2A-L6
				SY30M-79-2A-LN3
	Inch	Ø5/32" Ø1/4"		SY30M-79-2A-LN7
	Metric	Ø4 Ø6	Long Elbow	SY30M-79-3A-L4
SY30M-79-3A-L6				
SY30M-79-3A-LN3				
SY30M-79-3A-LN7				
Inch	Ø5/32" Ø1/4"			
SUP blocking disk				SY30M-40-1A
EXH Blocking Disk				SY30M-40-2A
Label for Blocking Disk				SJ3000-155-1A
Back Pressure Check Valve Assembly				SY30M-24-1A

Cable Type	Length	Part Number
D-SUB	1.5 m	AXT100-DS25-015
	3 m	AXT100-DS25-030
	5 m	AXT100-DS25-050
IP67 D-SUB	1.5 m	SY30M-DS25-015
	3 m	SY30M-DS25-030
	5 m	SY30M-DS25-050
Flat Ribbon 26 Pin	1.5 m	AXT100-FC26-1
	3 m	AXT100-FC26-2
	5 m	AXT100-FC26-3
Flat Ribbon 20 Pin	1.5 m	AXT100-FC20-1
	3 m	AXT100-FC20-2
	5 m	AXT100-FC20-3
Flat Ribbon 10 Pin	1.5 m	AXT100-FC10-1
	3 m	AXT100-FC10-2
	5 m	AXT100-FC10-3