

# SY3000 EX260 Accessory Components

Replacement One Touch Fittings				
Port Size		Fitting Type	Part Number	
A, B Port	Metric	Straight	Ø2	VVQ1000-50A-C2
			Ø3.2	VVQ1000-50A-C3
			Ø4	VVQ1000-50A-C4
			Ø6	VVQ1000-50A-C6
		Elbow	Ø4	SZ3000-73-1A-L4
			Ø6	SZ3000-73-1A-L6
	Inch	Straight	Ø4	SZ3000-73-2A-L4
			Ø6	SZ3000-73-2A-L6
			Ø1/8"	VVQ1000-50A-N1
		Elbow	Ø5/32"	VVQ1000-50A-N3
			Ø1/4"	VVQ1000-50A-N7
			Ø5/32"	KJL03-95-X224
Long Elbow	Ø1/4"	KJL07-95-X224		
	Ø5/32"	KJL03-95-X225		
	Ø1/4"	KJL07-95-X225		
P, E Port	Metric	Straight	VVQ1000-51A-C8	
		Elbow	SZ3000-74-1A-L8	
		Long Elbow	SZ3000-74-2A-L8	
	Inch	Straight	VVQ1000-51A-N9	
		Elbow	KQ2L09-14-X224	
		Long Elbow	KQ2L09-14-X225	
Plug Assembly		For A, B Port	VVQ0000-58A	
		For P, E Port	VVQ1000-58A	

Fieldbus Communication Cable (M12, 5m)	Part Number
DeviceNet™ Communication Cable (Socket)	PCA-1557633
DeviceNet™ Communication Cable (Plug)	PCA-1557646
PROFIBUS-DP Communication Cable (Socket)	PCA-1557688
PROFIBUS-DP Communication Cable (Plug)	PCA-1557691
CC-Link Communication Cable (Socket)	PCA-1567720
CC-Link Communication Cable (Plug)	PCA-1567717
Fieldwireable Connector (M12)	Part Number
Fieldwireable connector for DeviceNet™ (Plug)	PCA-1557659
Fieldwireable connector for DeviceNet™ (Socket)	PCA-1557662
Fieldwireable connector for PROFIBUS-DP (Plug)	PCA-1557701
Fieldwireable connector for PROFIBUS-DP (Socket)	PCA-1557714
Fieldwireable connector for DeviceNet™ (Plug)	PCA-1557617
Fieldwireable connector for DeviceNet™ (Socket)	PCA-1557620

Communication Cable for EtherNet/IP™, EtherCAT®, and PROFINET	Part Number
Cable with Connector (D-Coded, 5m, Cable)	PCA-1446566
Fieldwireable connector (D-Coded)	PCA-1446553
Cable with Ethernet Connector (D-Coded, 1m, RJ45)	EX9-AC010EN-PSRJ
Cable with Ethernet Connector (D-Coded, 2m, RJ45)	EX9-AC020EN-PSRJ
Cable with Ethernet Connector (D-Coded, 3m, RJ45)	EX9-AC030EN-PSRJ
Cable with Ethernet Connector (D-Coded, 5m, RJ45)	EX9-AC050EN-PSRJ
Cable with Ethernet Connector (D-Coded, 10m, RJ45)	EX9-AC100EN-PSRJ

Manifold Options	Port Size	Type	Part Number	
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Straight	Ø2	SY30M-78-1A-C2
			Ø3	SY30M-78-1A-C3
			Ø4	SY30M-78-1A-C4
			Ø6	SY30M-78-1A-C6
	Inch	Straight	Ø1/8"	SY30M-78-1A-N1
			Ø5/32"	SY30M-78-1A-N3
			Ø1/4"	SY30M-78-1A-N7
	Metric	Short Elbow	Ø4	SY30M-78-2A-L4
			Ø6	SY30M-78-2A-L6
			Ø5/32"	SY30M-78-2A-LN3
	Inch	Short Elbow	Ø1/4"	SY30M-78-2A-LN7
			Ø5/32"	SY30M-78-2A-LN3
Metric	Long Elbow	Ø4	SY30M-78-3A-L4	
		Ø6	SY30M-78-3A-L6	
		Ø5/32"	SY30M-78-3A-LN3	
	Inch	Long Elbow	Ø1/4"	SY30M-78-3A-LN7
			Ø5/32"	SY30M-78-3A-LN3
			Ø1/4"	SY30M-78-3A-LN7
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Straight	Ø2	SY30M-79-1A-C2
			Ø3	SY30M-79-1A-C3
			Ø4	SY30M-79-1A-C4
			Ø6	SY30M-79-1A-C6
	Inch	Straight	Ø1/8"	SY30M-79-1A-N1
			Ø5/32"	SY30M-79-1A-N3
			Ø1/4"	SY30M-79-1A-N7
	Metric	Short Elbow	Ø4	SY30M-79-2A-L4
			Ø6	SY30M-79-2A-L6
			Ø5/32"	SY30M-79-2A-LN3
	Inch	Short Elbow	Ø1/4"	SY30M-79-2A-LN7
			Ø5/32"	SY30M-79-2A-LN3
Metric	Long Elbow	Ø4	SY30M-79-3A-L4	
		Ø6	SY30M-79-3A-L6	
		Ø5/32"	SY30M-79-3A-LN3	
	Inch	Long Elbow	Ø1/4"	SY30M-79-3A-LN7
			Ø5/32"	SY30M-79-3A-LN3
			Ø1/4"	SY30M-79-3A-LN7
SUP blocking disk			SY30M-40-1A	
EXH Blocking Disk			SY30M-40-2A	
Label for Blocking Disk			SJ3000-155-1A	
Back Pressure Check Valve Assembly			SY30M-24-1A	

Power Supply Cable Type	Length	Part Number	
M12 Connector	Straight	1m	EX500-AP010-S
		5m	EX500-AP050-S
	Right Angle	1m	EX500-AP010-A
		5m	EX500-AP050-A
M12 SPEEDCON Type	Straight	1.5m	PCA-1401804
		3m	PCA-1401805
		5m	PCA-1401806
Power Supply for CC-Link	Straight	1m	EX9-AC010-1
		3m	EX9-AC030-1
		5m	EX9-AC050-1
	Right Angle	1.5m	PCA-1401807
		3m	PCA-1401808
		5m	PCA-1401809