





SY3000 Accessory Components

Replacement One Touch Fittings				
Port Size		Type	Part Number	
A, B Port	Metric Size	Straight Type	Ø2	VVQ1000-50A-C2
			Ø3.2	VVQ1000-50A-C3
			Ø4	VVQ1000-50A-C4
			Ø6	VVQ1000-50A-C6
		Elbow Type	Ø4	SZ3000-73-1A-L4
			Ø6	SZ3000-73-1A-L6
	Inch Size	Straight Type 	Ø1/8"	VVQ1000-50A-N1
			Ø5/32"	VVQ1000-50A-N3
			Ø1/4"	VVQ1000-50A-N7
		Elbow Type	Ø5/32"	KJL03-95-X224
			Ø1/4"	KJL07-95-X224
		Long Elbow Type 	Ø5/32"	KJL03-95-X225
	Ø1/4"	KJL07-95-X225		
P, E Port	Metric Size	Straight Type	Ø8	VVQ1000-51A-C8
		Elbow Type	Ø8	SZ3000-74-1A-L8
		Long Elbow Type	Ø8	SZ3000-74-2A-L8
	Inch Size	Straight Type	Ø5/16"	VVQ1000-51A-N9
		Elbow Type	Ø5/16"	KQ2L09-14-X224
		Long Elbow Type	Ø5/16"	KQ2L09-14-X225
A, B Port			VVQ0000-58A	
P, E Port			VVQ1000-58A	

Manifold Options	Port Size		Type	Part Number		
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Ø2	Straight	SY30M-78-1A-C2		
		Ø3		SY30M-78-1A-C3		
		Ø4		SY30M-78-1A-C4		
		Ø6		SY30M-78-1A-C6		
		Inch		Ø1/8"	SY30M-78-1A-N1	
				Ø5/32"	SY30M-78-1A-N3	
	Metric	Ø4	Short Elbow	SY30M-78-1A-N7		
		Ø6		SY30M-78-2A-L4		
		Ø6		SY30M-78-2A-L6		
		Inch		Ø5/32"	SY30M-78-2A-LN3	
				Ø1/4"	SY30M-78-2A-LN7	
		Metric		Ø4	Long Elbow	SY30M-78-3A-L4
Ø6	SY30M-78-3A-L6					
Inch	Ø5/32"		SY30M-78-3A-LN3			
	Ø1/4"		SY30M-78-3A-LN7			
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric		Ø2	Straight		SY30M-79-1A-C2
			Ø3			SY30M-79-1A-C3
		Ø4	SY30M-79-1A-C4			
		Ø6	SY30M-79-1A-C6			
		Inch	Ø1/8"		SY30M-79-1A-N1	
			Ø5/32"		SY30M-79-1A-N3	
	Metric	Ø4	Short Elbow	SY30M-79-1A-N7		
		Ø6		SY30M-79-2A-L4		
		Ø6		SY30M-79-2A-L6		
		Inch		Ø5/32"	SY30M-79-2A-LN3	
				Ø1/4"	SY30M-79-2A-LN7	
		Metric		Ø4	Long Elbow	SY30M-79-3A-L4
Ø6	SY30M-79-3A-L6					
Inch	Ø5/32"		SY30M-79-3A-LN3			
	Ø1/4"		SY30M-79-3A-LN7			
SUP blocking disk				SY30M-40-1A		
EXH Blocking Disk				SY30M-40-2A		
Label for Blocking Disk				SJ3000-155-1A		
Back Pressure Check Valve Assembly				SY30M-24-1A		

Cable Type	Length	Part Number
D-SUB	1.5 m	AXT100-DS25-015
	3 m	AXT100-DS25-030
	5 m	AXT100-DS25-050
IP67 D-SUB	1.5 m	SY30M-DS25-015
	3 m	SY30M-DS25-030
	5 m	SY30M-DS25-050
Flat Ribbon 26 Pin	1.5 m	AXT100-FC26-1
	3 m	AXT100-FC26-2
	5 m	AXT100-FC26-3
Flat Ribbon 20 Pin	1.5 m	AXT100-FC20-1
	3 m	AXT100-FC20-2
	5 m	AXT100-FC20-3
Flat Ribbon 10 Pin	1.5 m	AXT100-FC10-1
	3 m	AXT100-FC10-2
	5 m	AXT100-FC10-3

SY5000 Accessory Components

Replacement One Touch Fittings				
Port Size		Part Number		
A, B Port	Metric Size	Straight Type	Ø4	VVQ1000-51A-C4
			Ø6	VVQ1000-51A-C6
			Ø8	VVQ1000-51A-C8
		Elbow Type	Ø4	SZ3000-74-1A-L4
			Ø6	SZ3000-74-1A-L6
			Ø8	SZ3000-74-1A-L8
		Long Elbow Type	Ø4	SZ3000-74-2A-L4
			Ø6	SZ3000-74-2A-L6
			Ø8	SZ3000-74-2A-L8
	Inch Size	Straight Type 	Ø5/32"	VVQ1000-51A-N3
			Ø1/4"	VVQ1000-51A-N7
			Ø5/16"	VVQ1000-51A-N9
		Elbow Type	Ø1/4"	KQ2L07-14-X224
			Ø5/16"	KQ2L09-14-X224
Long Elbow Type 		Ø1/4"	KQ2L07-14-X225	
Ø5/16"	KQ2L09-14-X225			
P, E Port	Metric Size	Ø10	VVQ2000-51A-C10	
		Ø10	SZ3000-83-1A-L10	
		Ø10	SZ3000-83-2A-L10	
	Inch Size	Ø3/8"	VVQ2000-51A-N11	
		Ø3/8"	KQ2L11-14-X224	
		Ø3/8"	KQ2L11-14-X225	
Plug Assembly	A, B Port	VVQ1000-58A		
	P, E Port	VVQ2000-58A		

Manifold Options	Port Size		Type	Part Number	
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Ø4	Straight	SY50M-78-1A-C4	
		Ø6		SY50M-78-1A-C6	
		Ø8		SY50M-78-1A-C8	
	Inch	Ø1/4"		SY50M-78-1A-N3	
		Ø5/32"		SY50M-78-1A-N7	
		Ø1/4"		SY50M-78-1A-N9	
	Metric	Ø4		Short Elbow	SY50M-78-2A-L4
		Ø6			SY50M-78-2A-L6
		Ø8			SY50M-78-2A-L8
	Inch	Ø1/4"	SY50M-78-2A-LN7		
		Ø5/16"	SY50M-78-2A-LN9		
		Ø1/4"	SY50M-78-3A-L4		
Metric	Ø6	Long Elbow	SY50M-78-3A-L6		
	Ø8		SY50M-78-3A-L8		
	Ø1/4"		SY50M-78-3A-LN7		
Inch	Ø5/16"		SY50M-78-3A-LN9		
	Metric		Ø4	Straight	SY50M-79-1A-C4
			Ø6		SY50M-79-1A-C6
Ø8			SY50M-79-1A-C8		
Inch	Ø1/4"		SY50M-79-1A-N3		
	Ø5/32"		SY50M-79-1A-N7		
	Ø1/4"	SY50M-79-1A-N9			
Individual Exhaust Block Assembly Includes 4pcs Blocking Disks	Metric	Ø4	Short Elbow		SY50M-79-2A-L4
		Ø6			SY50M-79-2A-L6
		Ø8			SY50M-79-2A-L8
	Inch	Ø1/4"		SY50M-79-2A-LN7	
		Ø5/16"		SY50M-79-2A-LN9	
		Ø4		Long Elbow	SY50M-79-3A-L4
	Metric	Ø6	SY50M-79-3A-L6		
		Ø8	SY50M-79-3A-L8		
		Inch	Ø1/4"		SY50M-79-3A-LN7
	Ø5/16"		SY50M-79-3A-LN9		
	SUP blocking disk				SY50M-40-1A
	EXH Blocking Disk				SY50M-40-1A
Label for Blocking Disk			SJ3000-155-1A		
Back Pressure Check Valve Assembly			SY50M-24-1A		

Cable Type	Length	Part Number
D-SUB	1.5 m	AXT100-DS25-015
	3 m	AXT100-DS25-030
	5 m	AXT100-DS25-050
IP67 D-SUB	1.5 m	SY30M-DS25-015
	3 m	SY30M-DS25-030
	5 m	SY30M-DS25-050
Flat Ribbon 26 Pin	1.5 m	AXT100-FC26-1
	3 m	AXT100-FC26-2
	5 m	AXT100-FC26-3
Flat Ribbon 20 Pin	1.5 m	AXT100-FC20-1
	3 m	AXT100-FC20-2
	5 m	AXT100-FC20-3
Flat Ribbon 10 Pin	1.5 m	AXT100-FC10-1
	3 m	AXT100-FC10-2
	5 m	AXT100-FC10-3

SY7000 Accessory Components

Replacement One Touch Fittings				
Port Size	Type	SY7000		
A, B Port	Straight Type	Ø6	VVQ2000-51A-C6	
		Ø8	VVQ2000-51A-C8	
		Ø10	VVQ2000-51A-C10	
		Ø12	KQ2H12-17-X224	
		Elbow Type	Ø6	SZ3000-83-1A-L6
			Ø8	SZ3000-83-1A-L8
	Ø10		SZ3000-83-1A-L10	
	Long Elbow Type	Ø6	SZ3000-83-2A-L6	
		Ø8	SZ3000-83-2A-L8	
		Ø10	SZ3000-83-2A-L10	
	Inch Size	Straight Type	Ø1/4"	VVQ2000-51A-N7
			Ø5/16"	VVQ2000-51A-N9
Ø3/8"			VVQ2000-51A-N11	
Elbow Type		Ø3/8"	KQ2L11-14-X224	
		Long Elbow Type	Ø3/8"	KQ2L11-14-X225
P, E Port	Metric Size	Ø12	VVQ4000-50B-C12	
		Ø12	KQ2L12-19N-X224	
		Ø12	KQ2W12-19N-X224	
	Inch Size	Ø1/2	VVQ4000-50B-N13	
		Ø1/2	KQ2L13-19N-X224	
		Ø1/2	KQ2W13-19N-X224	
Plug Assembly	A, B Port	VVQ2000-58A		
	P, E Port	SY9000-62-1A		

Manifold Options	Port Size	Type	Part Number	
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Straight	Ø6	SY70M-78-1A-C6
			Ø8	SY70M-78-1A-C8
			Ø10	SY70M-78-1A-C10
			Ø12	SY70M-78-1A-C12
	Inch	Straight	Ø1/4"	SY70M-78-1A-N7
			Ø5/16"	SY70M-78-1A-N9
			Ø3/8"	SY70M-78-1A-N11
	Metric	Short Elbow	Ø6	SY70M-78-2A-L6
			Ø8	SY70M-78-2A-L8
			Ø10	SY70M-78-2A-L10
	Inch	Short Elbow	Ø12	SY70M-78-2A-L12
			Ø3/8"	SY70M-78-2A-LN11
	Metric	Long Elbow	Ø6	SY70M-78-3A-L6
			Ø8	SY70M-78-3A-L8
			Ø10	SY70M-78-3A-L10
Ø12			SY70M-78-3A-L12	
Inch	Ø3/8"	SY70M-78-3A-LN11		
Individual Exhaust Block Assembly Includes 4pcs Blocking Disks	Metric	Straight	Ø6	SY70M-79-1A-C6
			Ø8	SY70M-79-1A-C8
			Ø10	SY70M-79-1A-C10
			Ø12	SY70M-79-1A-C12
	Inch	Straight	Ø1/4"	SY70M-79-1A-N7
			Ø5/16"	SY70M-79-1A-N9
			Ø3/8"	SY70M-79-1A-N11
	Metric	Short Elbow	Ø6	SY70M-79-2A-L6
			Ø8	SY70M-79-2A-L8
			Ø10	SY70M-79-2A-L10
	Inch	Short Elbow	Ø12	SY70M-79-2A-L12
			Ø3/8"	SY70M-79-2A-LN11
	Metric	Long Elbow	Ø6	SY70M-79-3A-L6
			Ø8	SY70M-79-3A-L8
			Ø10	SY70M-79-3A-L10
Ø12			SY70M-79-3A-L12	
Inch	Ø3/8"	SY70M-79-3A-LN11		
SUP blocking disk			SY70M-40-1A	
EXH Blocking Disk			SY70M-40-1A	
Label for Blocking Disk			SJ3000-155-1A	
Back Pressure Check Valve Assembly			SY70M-24-1A	

Cable Type	Length	Part Number
D-SUB	1.5 m	AXT100-DS25-015
	3 m	AXT100-DS25-030
	5 m	AXT100-DS25-050
IP67 D-SUB	1.5 m	SY30M-DS25-015
	3 m	SY30M-DS25-030
	5 m	SY30M-DS25-050
Flat Ribbon 26 Pin	1.5 m	AXT100-FC26-1
	3 m	AXT100-FC26-2
	5 m	AXT100-FC26-3
Flat Ribbon 20 Pin	1.5 m	AXT100-FC20-1
	3 m	AXT100-FC20-2
	5 m	AXT100-FC20-3
Flat Ribbon 10 Pin	1.5 m	AXT100-FC10-1
	3 m	AXT100-FC10-2
	5 m	AXT100-FC10-3

All data on this page current as of October, 2015. Please see New SY catalog on www.smcusa.com for current specifications