



SY5000 D-SUB, Flat Ribbon Accessory Components

Replacement One Touch Fittings				
Port Size		Fitting Type	Part Number	
A, B Port	Metric	Straight	Ø4	VVQ1000-51A-C4
			Ø6	VVQ1000-51A-C6
			Ø8	VVQ1000-51A-C8
		Elbow	Ø4	SZ3000-74-1A-L4
			Ø6	SZ3000-74-1A-L6
			Ø8	SZ3000-74-1A-L8
	Long Elbow	Ø4	SZ3000-74-2A-L4	
		Ø6	SZ3000-74-2A-L6	
		Ø8	SZ3000-74-2A-L8	
	Inch	Straight 	Ø5/32"	VVQ1000-51A-N3
			Ø1/4"	VVQ1000-51A-N7
			Ø5/16"	VVQ1000-51A-N9
Elbow		Ø1/4"	KQ2L07-14-X224	
		Ø5/16"	KQ2L09-14-X224	
Long Elbow 		Ø1/4"	KQ2L07-14-X225	
Ø5/16"	KQ2L09-14-X225			
P, E Port	Metric	Ø10	Straight	VVQ2000-51A-C10
			Elbow	SZ3000-83-1A-L10
			Long Elbow	SZ3000-83-2A-L10
	Inch	Ø3/8"	Straight	VVQ2000-51A-N11
			Elbow	KQ2L11-14-X224
			Long Elbow	KQ2L11-14-X225
Plug Assembly		For A, B Port	VVQ1000-58A	
		For P, E Port	VVQ2000-58A	

Manifold Options	Port Size	Type	Part Number	
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Straight	Ø4	SY50M-78-1A-C4
			Ø6	SY50M-78-1A-C6
			Ø8	SY50M-78-1A-C8
	Inch		Ø1/4"	SY50M-78-1A-N3
			Ø5/32"	SY50M-78-1A-N7
			Ø1/4"	SY50M-78-1A-N9
	Metric	Short Elbow	Ø4	SY50M-78-2A-L4
			Ø6	SY50M-78-2A-L6
			Ø8	SY50M-78-2A-L8
	Inch		Ø1/4"	SY50M-78-2A-LN7
			Ø5/16"	SY50M-78-2A-LN9
			Metric	Long Elbow
Ø6	SY50M-78-3A-L6			
Ø8	SY50M-78-3A-L8			
Inch	Ø1/4"	SY50M-78-3A-LN7		
	Ø5/16"	SY50M-78-3A-LN9		
	Individual Exhaust Block Assembly Includes 4pcs Blocking Disks	Metric	Straight	
Ø6				SY50M-79-1A-C6
Ø8				SY50M-79-1A-C8
Inch		Ø1/4"		SY50M-79-1A-N3
		Ø5/32"		SY50M-79-1A-N7
		Ø1/4"		SY50M-79-1A-N9
Metric		Short Elbow	Ø4	SY50M-79-2A-L4
			Ø6	SY50M-79-2A-L6
			Ø8	SY50M-79-2A-L8
Inch			Ø1/4"	SY50M-79-2A-LN7
			Ø5/16"	SY50M-79-2A-LN9
			Metric	Long Elbow
Ø6	SY50M-79-3A-L6			
Ø8	SY50M-79-3A-L8			
Inch	Ø1/4"	SY50M-79-3A-LN7		
	Ø5/16"	SY50M-79-3A-LN9		
	SUP blocking disk		SY50M-40-1A	
EXH Blocking Disk		SY50M-40-1A		
Label for Blocking Disk		SJ3000-155-1A		
Back Pressure Check Valve Assembly		SY50M-24-1A		

Cable Type	Length	Part Number
D-SUB	1.5 m	AXT100-DS25-015
	3 m	AXT100-DS25-030
	5 m	AXT100-DS25-050
IP67 D-SUB	1.5 m	SY30M-DS25-015
	3 m	SY30M-DS25-030
	5 m	SY30M-DS25-050
Flat Ribbon 26 Pin	1.5 m	AXT100-FC26-1
	3 m	AXT100-FC26-2
	5 m	AXT100-FC26-3
Flat Ribbon 20 Pin	1.5 m	AXT100-FC20-1
	3 m	AXT100-FC20-2
	5 m	AXT100-FC20-3
Flat Ribbon 10 Pin	1.5 m	AXT100-FC10-1
	3 m	AXT100-FC10-2
	5 m	AXT100-FC10-3