



## SY5000 EX250 Accessory Components

Replacement One Touch Fittings				
Port Size		Fitting Type	Part Number	
A, B Port	Metric	Straight	Ø4	VVQ1000-51A-C4
			Ø6	VVQ1000-51A-C6
			Ø8	VVQ1000-51A-C8
		Elbow	Ø4	SZ3000-74-1A-L4
			Ø6	SZ3000-74-1A-L6
			Ø8	SZ3000-74-1A-L8
		Long Elbow	Ø4	SZ3000-74-2A-L4
			Ø6	SZ3000-74-2A-L6
			Ø8	SZ3000-74-2A-L8
	Inch	Straight 	Ø5/32"	VVQ1000-51A-N3
			Ø1/4"	VVQ1000-51A-N7
			Ø5/16"	VVQ1000-51A-N9
		Elbow	Ø1/4"	KQ2L07-14-X224
			Ø5/16"	KQ2L09-14-X224
Long Elbow 		Ø1/4"	KQ2L07-14-X225	
		Ø5/16"	KQ2L09-14-X225	
P, E Port	Metric	Straight	VVQ2000-51A-C10	
		Elbow	SZ3000-83-1A-L10	
		Long Elbow	SZ3000-83-2A-L10	
	Inch	Straight	VVQ2000-51A-N11	
		Elbow	KQ2L11-14-X224	
		Long Elbow	KQ2L11-14-X225	
Plug Assembly		For A, B Port	VVQ1000-58A	
		For P, E Port	VVQ2000-58A	

Fieldbus Communication Cable (M12, 5m)	Part Number
DeviceNet™ Communication Cable (SPEEDCON)	PCA-1557633
DeviceNet™ Communication Cable	EX500-AC050-DN
PROFIBUS-DP Communication Cable (Socket)	PCA-1557688
PROFIBUS-DP Communication Cable (Plug)	PCA-1557691
CC-Link Communication Cable (Socket)	PCA-1567720
CC-Link Communication Cable (Plug)	PCA-1567717
Other accessories	Part Number
PROFIBUS-DP Terminating Resistor	PCA-1557727
DeviceNet™ Terminating Resistor	PCA-1557675
CC-Link Communication Bus Adapter	EX9-ACY00-MJ
Replacement Fuse for input block	EX9-FU05

Communication Cable for EtherNet/IP™	Part Number
Cable with Ethernet Connector (D-Coded, 1m, RJ45)	EX9-AC010EN-PSRJ
Cable with Ethernet Connector (D-Coded, 2m, RJ45)	EX9-AC020EN-PSRJ
Cable with Ethernet Connector (D-Coded, 3m, RJ45)	EX9-AC030EN-PSRJ
Cable with Ethernet Connector (D-Coded, 5m, RJ45)	EX9-AC050EN-PSRJ
Cable with Ethernet Connector (D-Coded, 10m, RJ45)	EX9-AC100EN-PSRJ

Manifold Options	Port Size	Type	Part Number		
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Straight	Ø4	SY50M-78-1A-C4	
			Ø6	SY50M-78-1A-C6	
			Ø8	SY50M-78-1A-C8	
	Inch		Ø1/4"	SY50M-78-1A-N3	
			Ø5/32"	SY50M-78-1A-N7	
			Ø1/4"	SY50M-78-1A-N9	
	Metric		Short Elbow	Ø4	SY50M-78-2A-L4
				Ø6	SY50M-78-2A-L6
				Ø8	SY50M-78-2A-L8
	Inch	Ø1/4"		SY50M-78-2A-LN7	
		Ø5/16"		SY50M-78-2A-LN9	
		Metric		Long Elbow	Ø4
Ø6	SY50M-78-3A-L6				
Ø8	SY50M-78-3A-L8				
Inch	Ø1/4"	SY50M-78-3A-LN7			
	Ø5/16"	SY50M-78-3A-LN9			
	Individual Exhaust Block Assembly Includes 4pcs Blocking Disks	Metric	Straight		Ø4
Ø6					SY50M-79-1A-C6
Ø8					SY50M-79-1A-C8
Inch		Ø1/4"			SY50M-79-1A-N3
		Ø5/32"		SY50M-79-1A-N7	
		Ø1/4"		SY50M-79-1A-N9	
Metric		Short Elbow		Ø4	SY50M-79-2A-L4
				Ø6	SY50M-79-2A-L6
				Ø8	SY50M-79-2A-L8
Inch			Ø1/4"	SY50M-79-2A-LN7	
			Ø5/16"	SY50M-79-2A-LN9	
			Metric	Long Elbow	Ø4
Ø6	SY50M-79-3A-L6				
Ø8	SY50M-79-3A-L8				
Inch	Ø1/4"	SY50M-79-3A-LN7			
	Ø5/16"	SY50M-79-3A-LN9			
	SUP blocking disk		SY50M-40-1A		
EXH Blocking Disk		SY50M-40-1A			
Label for Blocking Disk		SJ3000-155-1A			
Back Pressure Check Valve Assembly		SY50M-24-1A			

Power Supply Cable Type	Length	Part Number
Power Supply cable for DeviceNet, CC-Link, ControlNet, CANopen,	1m	EX9-AC010-1
	3m	EX9-AC030-1
	5m	EX9-AC050-1
Power Supply cable for Profibus, EtherNet/IP	1m	EX500-AP010-S
	5m	EX500-AP050-S
M12 SPEEDCON type for EtherNet/IP	1.5m	PCA-1401804
	3m	PCA-1401805
	5m	PCA-1401806

Seal cap for unused M12 Connector (10pcs)	EX9-AWTS
Seal cap for unused M8 Connector (10pcs)	EX9-AWES