



SY7000 Accessory Components

Replacement One Touch Fittings			
Port Size	Type	SY7000	
A, B Port	Straight Type	Ø6	VVQ2000-51A-C6
		Ø8	VVQ2000-51A-C8
		Ø10	VVQ2000-51A-C10
		Ø12	KQ2H12-17-X224
	Elbow Type	Ø6	SZ3000-83-1A-L6
		Ø8	SZ3000-83-1A-L8
		Ø10	SZ3000-83-1A-L10
		Ø12	KQ2L12-17N-X224
	Long Elbow Type	Ø6	SZ3000-83-2A-L6
		Ø8	SZ3000-83-2A-L8
		Ø10	SZ3000-83-2A-L10
		Ø12	KQ2W12-17N-X224
Inch Size	Straight Type 	Ø1/4"	VVQ2000-51A-N7
		Ø5/16"	VVQ2000-51A-N9
		Ø3/8"	VVQ2000-51A-N11
	Elbow Type 	Ø3/8"	KQ2L11-14-X224
		Ø3/8"	KQ2L11-14-X225
P, E Port	Metric Size	Ø12	VVQ4000-50B-C12
		Ø12	KQ2L12-19N-X224
		Ø12	KQ2W12-19N-X224
	Inch Size	Ø1/2	VVQ4000-50B-N13
		Ø1/2	KQ2L13-19N-X224
		Ø1/2	KQ2W13-19N-X224
Plug Assembly	A, B Port	VVQ2000-58A	
	P, E Port	SY9000-62-1A	

Manifold Options	Port Size	Type	Part Number	
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Straight	Ø6	SY70M-78-1A-C6
			Ø8	SY70M-78-1A-C8
			Ø10	SY70M-78-1A-C10
			Ø12	SY70M-78-1A-C12
	Inch	Straight	Ø1/4"	SY70M-78-1A-N7
			Ø5/16"	SY70M-78-1A-N9
			Ø3/8"	SY70M-78-1A-N11
	Metric	Short Elbow	Ø6	SY70M-78-2A-L6
			Ø8	SY70M-78-2A-L8
			Ø10	SY70M-78-2A-L10
	Inch	Short Elbow	Ø12	SY70M-78-2A-L12
Ø3/8"			SY70M-78-2A-LN11	
Metric	Long Elbow	Ø6	SY70M-78-3A-L6	
		Ø8	SY70M-78-3A-L8	
		Ø10	SY70M-78-3A-L10	
		Ø12	SY70M-78-3A-L12	
		Ø3/8"	SY70M-78-3A-LN11	
Individual Exhaust Block Assembly Includes 4pcs Blocking Disks	Metric	Straight	Ø6	SY70M-79-1A-C6
			Ø8	SY70M-79-1A-C8
			Ø10	SY70M-79-1A-C10
			Ø12	SY70M-79-1A-C12
	Inch	Straight	Ø1/4"	SY70M-79-1A-N7
			Ø5/16"	SY70M-79-1A-N9
			Ø3/8"	SY70M-79-1A-N11
	Metric	Short Elbow	Ø6	SY70M-79-2A-L6
			Ø8	SY70M-79-2A-L8
			Ø10	SY70M-79-2A-L10
	Inch	Short Elbow	Ø12	SY70M-79-2A-L12
Ø3/8"			SY70M-79-2A-LN11	
Metric	Long Elbow	Ø6	SY70M-79-3A-L6	
		Ø8	SY70M-79-3A-L8	
		Ø10	SY70M-79-3A-L10	
		Ø12	SY70M-79-3A-L12	
		Ø3/8"	SY70M-79-3A-LN11	
SUP blocking disk			SY70M-40-1A	
EXH Blocking Disk			SY70M-40-1A	
Label for Blocking Disk			SJ3000-155-1A	
Back Pressure Check Valve Assembly			SY70M-24-1A	

Cable Type	Length	Part Number
D-SUB	1.5 m	AXT100-DS25-015
	3 m	AXT100-DS25-030
	5 m	AXT100-DS25-050
IP67 D-SUB	1.5 m	SY30M-DS25-015
	3 m	SY30M-DS25-030
	5 m	SY30M-DS25-050
Flat Ribbon 26 Pin	1.5 m	AXT100-FC26-1
	3 m	AXT100-FC26-2
	5 m	AXT100-FC26-3
Flat Ribbon 20 Pin	1.5 m	AXT100-FC20-1
	3 m	AXT100-FC20-2
	5 m	AXT100-FC20-3
Flat Ribbon 10 Pin	1.5 m	AXT100-FC10-1
	3 m	AXT100-FC10-2
	5 m	AXT100-FC10-3

All data on this page current as of October, 2015. Please see New SY catalog on www.smcusa.com for current specifications