

SY7000 EX250 Accessory Components

Replacement One Touch Fittings				
Port Size	Fitting Type	SY7000		
A, B Port	Straight	Ø6	VVQ2000-51A-C6	
		Ø8	VVQ2000-51A-C8	
		Ø10	VVQ2000-51A-C10	
		Ø12	KQ2H12-17-X224	
	Elbow	Ø6	SZ3000-83-1A-L6	
		Ø8	SZ3000-83-1A-L8	
		Ø10	SZ3000-83-1A-L10	
		Ø12	KQ2L12-17N-X224	
	Long Elbow	Ø6	SZ3000-83-2A-L6	
		Ø8	SZ3000-83-2A-L8	
		Ø10	SZ3000-83-2A-L10	
		Ø12	KQ2W12-17N-X224	
Inch	Straight	Ø1/4"	VVQ2000-51A-N7	
		Ø5/16"	VVQ2000-51A-N9	
		Ø3/8"	VVQ2000-51A-N11	
	Elbow	Ø3/8"	KQ2L11-14-X224	
	Long Elbow	Ø3/8"	KQ2L11-14-X225	
P, E Port	Metric	Ø12	Straight	VVQ4000-50B-C12
			Elbow	KQ2L12-19N-X224
			Long Elbow	KQ2W12-19N-X224
	Inch	Ø1/2"	Straight	VVQ4000-50B-N13
		Elbow	KQ2L13-19N-X224	
		Long Elbow	KQ2W13-19N-X224	
Plug Assembly	For A,B Port	VVQ2000-58A		
	For P, E Port	SY9000-62-1A		

Fieldbus Communication Cable (M12, 5m)	Part Number
DeviceNet™ Communication Cable (SPEEDCON)	PCA-1557633
DeviceNet™ Communication Cable	EX500-AC050-DN
PROFIBUS-DP Communication Cable (Socket)	PCA-1557688
PROFIBUS-DP Communication Cable (Plug)	PCA-1557691
CC-Link Communication Cable (Socket)	PCA-1567720
CC-Link Communication Cable (Plug)	PCA-1567717
Other accessories	Part Number
PROFIBUS-DP Terminating Resistor	PCA-1557727
DeviceNet™ Terminating Resistor	PCA-1557675
CC-Link Communication Bus Adapter	EX9-ACY00-MJ
Replacement Fuse for input block	EX9-FU05

Communication Cable for EtherNet/IP™	Part Number
Cable with Ethernet Connector (D-Coded, 1m, RJ45)	EX9-AC010EN-PSRJ
Cable with Ethernet Connector (D-Coded, 2m, RJ45)	EX9-AC020EN-PSRJ
Cable with Ethernet Connector (D-Coded, 3m, RJ45)	EX9-AC030EN-PSRJ
Cable with Ethernet Connector (D-Coded, 5m, RJ45)	EX9-AC050EN-PSRJ
Cable with Ethernet Connector (D-Coded, 10m, RJ45)	EX9-AC100EN-PSRJ

Manifold Options	Port Size	Type	Part Number	
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Straight	Ø6	SY70M-78-1A-C6
			Ø8	SY70M-78-1A-C8
			Ø10	SY70M-78-1A-C10
			Ø12	SY70M-78-1A-C12
	Inch	Straight	Ø1/4"	SY70M-78-1A-N7
			Ø5/16"	SY70M-78-1A-N9
			Ø3/8"	SY70M-78-1A-N11
	Metric	Short Elbow	Ø6	SY70M-78-2A-L6
			Ø8	SY70M-78-2A-L8
			Ø10	SY70M-78-2A-L10
	Inch	Short Elbow	Ø12	SY70M-78-2A-L12
			Ø3/8"	SY70M-78-2A-LN11
Metric	Long Elbow	Ø6	SY70M-78-3A-L6	
		Ø8	SY70M-78-3A-L8	
		Ø10	SY70M-78-3A-L10	
		Ø12	SY70M-78-3A-L12	
	Inch	Long Elbow	Ø3/8"	SY70M-78-3A-LN11
Individual Exhaust Block Assembly Includes 4pcs Blocking Disks	Metric	Straight	Ø6	SY70M-79-1A-C6
			Ø8	SY70M-79-1A-C8
			Ø10	SY70M-79-1A-C10
			Ø12	SY70M-79-1A-C12
	Inch	Straight	Ø1/4"	SY70M-79-1A-N7
			Ø5/16"	SY70M-79-1A-N9
			Ø3/8"	SY70M-79-1A-N11
	Metric	Short Elbow	Ø6	SY70M-79-2A-L6
			Ø8	SY70M-79-2A-L8
			Ø10	SY70M-79-2A-L10
	Inch	Short Elbow	Ø12	SY70M-79-2A-L12
			Ø3/8"	SY70M-79-2A-LN11
Metric	Long Elbow	Ø6	SY70M-79-3A-L6	
		Ø8	SY70M-79-3A-L8	
		Ø10	SY70M-79-3A-L10	
		Ø12	SY70M-79-3A-L12	
Inch	Long Elbow	Ø3/8"	SY70M-79-3A-LN11	
SUP blocking disk			SY70M-40-1A	
EXH Blocking Disk			SY70M-40-1A	
Label for Blocking Disk			SJ3000-155-1A	
Back Pressure Check Valve Assembly			SY70M-24-1A	

Power Supply Cable Type	Length	Part Number
Power Supply cable for DeviceNet, CC-Link, ControlNet, CANopen,	1m	EX9-AC010-1
	3m	EX9-AC030-1
	5m	EX9-AC050-1
Power Supply cable for Profibus, EtherNet/IP	1m	EX500-AP010-S
	5m	EX500-AP050-S
M12 SPEEDCON type for EtherNet/IP	1.5m	PCA-1401804
	3m	PCA-1401805
	5m	PCA-1401806

Seal cap for unused M12 Connector (10pcs)	EX9-AWTS
Seal cap for unused M8 Connector (10pcs)	EX9-AWES