



SY7000 EX600 Accessory Components

Replacement One Touch Fittings			
Port Size		Fitting Type	SY7000
A, B Port	Metric	Straight	Ø6 VVQ2000-51A-C6
			Ø8 VVQ2000-51A-C8
			Ø10 VVQ2000-51A-C10
			Ø12 KQ2H12-17-X224
		Elbow	Ø6 SZ3000-83-1A-L6
			Ø8 SZ3000-83-1A-L8
	Ø10 SZ3000-83-1A-L10		
	Ø12 KQ2L12-17N-X224		
	Long Elbow	Ø6 SZ3000-83-2A-L6	
		Ø8 SZ3000-83-2A-L8	
		Ø10 SZ3000-83-2A-L10	
		Ø12 KQ2W12-17N-X224	
Inch		Straight 	Ø1/4" VVQ2000-51A-N7
			Ø5/16" VVQ2000-51A-N9
	Ø3/8" VVQ2000-51A-N11		
	Elbow	Ø3/8" KQ2L11-14-X224	
		Long Elbow 	Ø3/8" KQ2L11-14-X225
P, E Port	Metric		Ø12
		Elbow KQ2L12-19N-X224	
		Long Elbow KQ2W12-19N-X224	
	Inch	Ø1/2"	Straight VVQ4000-50B-N13
			Elbow KQ2L13-19N-X224
			Long Elbow KQ2W13-19N-X224
Plug Assembly		For A, B Port VVQ2000-58A	For P, E Port SY9000-62-1A

Fieldbus Communication Cable (M12, 5m)	Part Number
DeviceNet™ Communication Cable (Socket)	PCA-1557633
DeviceNet™ Communication Cable (Plug)	PCA-1557646
PROFIBUS-DP Communication Cable (Socket)	PCA-1557688
PROFIBUS-DP Communication Cable (Plug)	PCA-1557691
CC-Link Communication Cable (Socket)	PCA-1567720
CC-Link Communication Cable (Plug)	PCA-1567717
Fieldwireable Connector (M12)	Part Number
Fieldwireable connector for DeviceNet™ (Plug)	PCA-1557659
Fieldwireable connector for DeviceNet™ (Socket)	PCA-1557662
Fieldwireable connector for PROFIBUS-DP (Plug)	PCA-1557701
Fieldwireable connector for PROFIBUS-DP (Socket)	PCA-1557714
Fieldwireable connector for DeviceNet™ (Plug)	PCA-1557617
Fieldwireable connector for DeviceNet™ (Socket)	PCA-1557620

Communication Cable for EtherNet/IP™, EtherCAT®, and PROFINET	Part Number
Cable with Connector (D-Coded, 5m, Cable)	PCA-1446566
Fieldwireable connector (D-Coded)	PCA-1446553
Cable with Ethernet Connector (D-Coded, 1m, RJ45)	EX9-AC010EN-PSRJ
Cable with Ethernet Connector (D-Coded, 2m, RJ45)	EX9-AC020EN-PSRJ
Cable with Ethernet Connector (D-Coded, 3m, RJ45)	EX9-AC030EN-PSRJ
Cable with Ethernet Connector (D-Coded, 5m, RJ45)	EX9-AC050EN-PSRJ
Cable with Ethernet Connector (D-Coded, 10m, RJ45)	EX9-AC100EN-PSRJ

Manifold Options	Port Size	Type	Part Number
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Straight	Ø6 SY70M-78-1A-C6
			Ø8 SY70M-78-1A-C8
			Ø10 SY70M-78-1A-C10
			Ø12 SY70M-78-1A-C12
	Inch	Straight	Ø1/4" SY70M-78-1A-N7
			Ø5/16" SY70M-78-1A-N9
			Ø3/8" SY70M-78-1A-N11
			Ø6 SY70M-78-2A-L6
	Metric	Short Elbow	Ø8 SY70M-78-2A-L8
			Ø10 SY70M-78-2A-L10
			Ø12 SY70M-78-2A-L12
			Ø3/8" SY70M-78-2A-LN11
Metric	Long Elbow	Ø6 SY70M-78-3A-L6	
		Ø8 SY70M-78-3A-L8	
		Ø10 SY70M-78-3A-L10	
		Ø12 SY70M-78-3A-L12	
Inch	Ø3/8"	SY70M-78-3A-LN11	
Individual Exhaust Block Assembly Includes 4pcs Blocking Disks	Metric	Straight	Ø6 SY70M-79-1A-C6
			Ø8 SY70M-79-1A-C8
			Ø10 SY70M-79-1A-C10
			Ø12 SY70M-79-1A-C12
	Inch	Straight	Ø1/4" SY70M-79-1A-N7
			Ø5/16" SY70M-79-1A-N9
			Ø3/8" SY70M-79-1A-N11
			Ø6 SY70M-79-2A-L6
	Metric	Short Elbow	Ø8 SY70M-79-2A-L8
			Ø10 SY70M-79-2A-L10
			Ø12 SY70M-79-2A-L12
			Ø3/8" SY70M-79-2A-LN11
Metric	Long Elbow	Ø6 SY70M-79-3A-L6	
		Ø8 SY70M-79-3A-L8	
		Ø10 SY70M-79-3A-L10	
		Ø12 SY70M-79-3A-L12	
Inch	Ø3/8"	SY70M-79-3A-LN11	
SUP blocking disk			SY70M-40-1A
EXH Blocking Disk			SY70M-40-1A
Label for Blocking Disk			SJ3000-155-1A
Back Pressure Check Valve Assembly			SY70M-24-1A

Power Supply Cable Type	Length	Part Number
M12 Connector	Straight	2m PCA-1564927
		6m PCA-1564930
	Right Angle	2m PCA-1564943
		6m PCA-1564969
7/8" Connector	Straight	2m PCA-1558810
		6m PCA-1558823
	Right Angle	2m PCA-1558836
		6m PCA-1558849
Fieldwireable 7/8" Connector (Plug)		PCA-1578078
Fieldwireable 7/8" Connector (Socket)		PCA-1578081

Seal cap for unused M12 Connector (10pcs)	EX9-AWTS
Seal cap for unused M8 Connector (10pcs)	EX9-AWES