

SMC Goes To Great Lengths

- ✓ Standard stocked lengths at 66ft, 100ft, 500ft, 1000ft, and 1640ft.
- ✓ Other lengths available based on minimum order quantity

SMC Tubing Accessories

- ✓ TK-1 Tube Cutter (Tubing 13mm or less)
- ✓ TK-2 Tube Cutter (Tubing 18mm or less)
- ✓ TK-3 Tube Cutter (Low Cost)
- ✓ TG-1 Tube Release Tool (ø4, ø6mm tube)
- ✓ TG-2 Tube Release Tool (ø1/8", ø1/4" tube)



SMC Offers a Rainbow of "Standard" color choices

TIUB 05 BU 33

Polyurethane Tubing

Size

Symbol	Tube size
01	1/8"
05	3/16"
07	1/4"
11	3/8"
13	1/2"

Color indication

Symbol	Color
01	Black
BU	Blue
C	Clear
G	Green
R	Red
W	White
Y	Yellow
YR	Orange

See Color Chart Below.

Length per roll

Symbol	Roll size
20	66 ft.
33	100 ft.
153	500 ft.
305	1000 ft.
500 [†]	1640 ft.

[†] 1/8", 3/16", 1/4"
Longer lengths available upon request.

TU 0425 BU 20

Polyurethane Tubing

Size

Symbol	Tube size
0425	4mm (5/32")
0604	6mm
0805	8mm (5/16")
1065	10mm
1208	12mm

Color indication

Symbol	Color
G4	Dark Green
GR1	Gray (solid)
GR2	Lt. Gray (solid)
P1	Neon Pink
PU1	Purple (solid)
PU2	TR Purple
R1	Red (solid)
R2	TR Red
S1	Silver
Y1	Yellow (solid)
Y2	TR Yellow
Y3	Neon Yellow
YR1	TR Orange
YR2	Neon Orange

See Color Chart Below.

Length per roll

Symbol	Roll size
20	20m
33*	100 ft.
100	100m
153*	500 ft.
305*	1000 ft.
500 [†]	500m

[†] 4mm, 6mm, 8mm
* Standard for 4mm (5/32") & 8mm (5/16") tube size.
Longer lengths available upon request.

	Color	Tube Sample
B	Black	
BU	Blue	
C	Clear	
G	Green	
R	Red	
W	White	
Y	Yellow	
YR	Orange	
BU1	Blue (solid)	
BU2	TR Blue	
BU3	Med. Blue	
BR1	Brown (solid)	
G1	Green (solid)	
G2	TR Green	
G3	Neon Green	

	Color	Tube Sample
G4	Dark Green	
GR1	Gray (solid)	
GR2	Lt. Gray (solid)	
P1	Neon Pink	
PU1	Purple (solid)	
PU2	TR Purple	
R1	Red (solid)	
R2	TR Red	
S1	Silver	
Y1	Yellow (solid)	
Y2	TR Yellow	
Y3	Neon Yellow	
YR1	TR Orange	
YR2	Neon Orange	

Note: Quick ship colors include: Black, Blue, Clear, Green, Red, White, Yellow and Orange.