

# S070 Series (Base Mounted) Certification: UL 429



**S070**

Body Type	Rated Voltage	Power / Pressure / Flow	Electrical Entry	Port Size	X-Option
A	5	A	C	Nil	Nil
B	6	B	CO	M3	X50
	V	C	G	M5	X62
	S	D			
	R	E			
		F			