

S070 Series (Body Ported) Certification: UL 429



Certified Options

S070

Body Type	Rated Voltage	Power / Pressure / Flow	Electrical Entry	Port Size	X-Option
C	5	A	C	32	Nil
M	6	B	CO	40	X50
	V	C	G		X62
	S	D			
	R	E			
		F			