

VQC4000 ACCESSORY COMPONENTS

Replacement One Touch Fittings			
Port Size		Part Number	
A, B Port	Metric	Ø8	VVQ4000-50B-C8
		Ø10	VVQ4000-50B-C10
		Ø12	VVQ4000-50B-C12
		Ø1/4"	VVQ4000-50B-N7
		Ø5/16"	VVQ4000-50B-N9
		Ø3/8"	VVQ4000-50B-N11

End Plate Options		
Side	Kit Type	Part Number
D	2	VVQC4000-3A-2-S
		VVQC4000-3A-2F-S
		VVQC4000-3A-2T-S
		VVQC4000-3A-2N-S
D	3	VVQC4000-3A-3-S
		VVQC4000-3A-3F-S
		VVQC4000-3A-3T-S
		VVQC4000-3A-3N-S
U		VVQC4000-2A-1-S
		VVQC4000-2A-1F-S
		VVQC4000-2A-1T-S
		VVQC4000-2A-1N-S

Pilot Valve Assembly	
Part Numbers	Wattage
VQZ111P-5-A	1 W
VQZ111P-5-B	
VQZ111P-5-E	
VQZ111P-5-A	
VQZ111P-5-B	
VQZ111P-5-E	
VQZ111PY-5-A	0.5 W
VQZ111PY-5-B	
VQZ111PY-5-E	
VQZ111PY-5-A	
VQZ111PY-5-B	
VQZ111PY-5-E	

Manifold Options	Port Size	Part Number
Individual SUP Spacer	Ø2	VVQ4000-P-1-02
	Ø3	VVQ4000-P-1-03
Individual EXH Spacer	Ø2	VVQ4000-R-1-02
	Ø3	VVQ4000-R-1-03
Blanking Plate Assembly		VVQ4000-10A-1
SUP/EXH block plate		VVQ4000-16A
Throttle Valve Spacer		VVQ4000-20A-1
Residual Pressure Release Valve Perfect Spacer		VVQ4000-25A-1
SUP Stop Valve Spacer		VVQ4000-37A-1
Interface Regulator		ARBQ4000-00-A-1
		ARBQ4000-00-B-1
		ARBQ4000-00-P-1

Cable Type	Length	Part Number
D-SUB	1.5 m	AXT100-DS25-015
	3 m	AXT100-DS25-030
	5 m	AXT100-DS25-050
Flat Ribbon (26 Pin)	1.5 m	AXT100-FC26-1
	3 m	AXT100-FC26-2
	5 m	AXT100-FC26-3
Flat Ribbon (20 Pin)	1.5 m	AXT100-FC20-1
	3 m	AXT100-FC20-2
	5 m	AXT100-FC20-3
Lead Wire (See Note 1)	0.6 m	VV5QC41-08C12LD0
	1.5 m	VV5QC41-08C12LD1
	3.0 m	VV5QC41-08C12LD2
Circular Connector Kit	1.5 m	AXT100-MC26-015
	3 m	AXT100-MC26-030
	5 m	AXT100-MC26-050

Note 1: Lead wire how to order includes manifold blocks, fittings, endplates, and housing unit in part number.