

VQC5000 ACCESSORY COMPONENTS

| End Plate Options | |
|-------------------|-------------------|
| Side | Part Number |
| D | VVQC5000-3A-2 |
| | VVQC5000-3A-2F |
| | VVQC5000-3A-2T |
| | VVQC5000-3A-2N |
| U | VVQ5000-2A-1-L-W |
| | VVQ5000-2A-1F-L-W |
| | VVQ5000-2A-1T-L-W |
| | VVQ5000-2A-1N-L-W |

| Pilot Valve Assembly | |
|----------------------|---------|
| Part Numbers | Wattage |
| V118-A | 0.95 W |
| V118-B | |
| V118-C | |
| V118Y-A | 0.4 W |
| V118Y-B | |
| V118Y-C | |

| Manifold Options | Type | Port Size | Part Number |
|--|-----------------|-----------------|-----------------|
| Individual SUP spacer | Plug-in type | Ø3/8" | VVQ5000-P-1-03 |
| | | Ø1/2" | VVQ5000-P-1-04 |
| | Plug Lead type | Ø3/8" | VVQ5000-P-5-03 |
| | | Ø1/2" | VVQ5000-P-5-04 |
| Individual EXH spacer | Plug Lead type | Ø | VVQ5000-R-5-03 |
| | | Ø | VVQ5000-R-5-04 |
| | Plug-in type | Ø3/8" | VVQ5000-R-1-03 |
| | | Ø1/2" | VVQ5000-R-1-04 |
| Blanking plate assembly | Plug Lead type | | VVQ5000-10A-5 |
| | Plug-in type | | VVQ5000-10A-1 |
| EXH/SUP Block plate | SUP block plate | | VVQ5000-16A-1 |
| | EXH block plate | | VVQ5000-16A-2 |
| Restrictor spacer | Plug Lead type | | VVQ5000-20A-5 |
| | Plug-in type | | VVQ5000-20A-1 |
| SUP stop valve spacer | Plug-in type | | VVQ5000-37A-1 |
| | Plug Lead type | | VVQ5000-37A-5 |
| Double check spacer with residual pressure exhaust | Plug-in type | | VVQ5000-25A-1 |
| | Plug Lead type | | VVQ5000-25A-5 |
| Interface regulator | Plug-in type | | ARBQ5000-00-A-1 |
| | | | ARBQ5000-00-B-1 |
| | | | ARBQ5000-00-P-1 |
| | Plug Lead type | | ARBQ5000-00-A-5 |
| | | ARBQ5000-00-B-5 | |
| | | ARBQ5000-00-P-5 | |

| Housing Assembly | Kit | Part Number |
|----------------------|-----------------------------|------------------|
| Terminal block plate | For EX126 SI Unit mounting | VVQC1000-74A-2 |
| D-sub connector | F kit, 25 Pins | VVQC1000-F26-1 |
| Flat Ribbon | P kit, 20 Pins | VVQC1000-P20-1 |
| | P kit, 26 Pins | VVQC1000-P26-1 |
| Terminal block box | T kit | VVQC1000-T0-1 |
| Lead wire | L, kit with 0.6 m lead wire | VVQC1000-L25-0-1 |
| | L, kit with 1.5 m lead wire | VVQC1000-L25-1-2 |
| | L, kit with 3.0 m lead wire | VVQC1000-L25-2-3 |
| Circular connector | M kit, 26 pin | VVQC1000-M26-1 |