

HRR Certification (Listed): UL 61010-1, CSA C22.2#61010-1-12

Certification Mark



Certified Options

HRR

Cooling Capacity
012
018
024
030

-

Cooling Method	Thread
W	(nil)
	F
	N

-20

Option(s)
(nil)
-DM
-M
-T
-T1

U

Option(s)
(nil)
Y
Z
Z1