

HRSH090

Certification Mark



Certified Options

-	<table><tr><th>Cooling Method</th><th>Option(s)</th></tr><tr><td>A</td><td>(nil)</td></tr><tr><td>W</td><td>F</td></tr><tr><td></td><td>N</td></tr></table>	Cooling Method	Option(s)	A	(nil)	W	F		N	-	<table><tr><th>Power Supply</th></tr><tr><td>20</td></tr></table>	Power Supply	20	-	<table><tr><th>Option(s)</th></tr><tr><td>(nil)</td></tr><tr><td>B</td></tr><tr><td>J</td></tr><tr><td>M</td></tr><tr><td>S</td></tr><tr><td>W</td></tr></table>	Option(s)	(nil)	B	J	M	S	W
Cooling Method	Option(s)																					
A	(nil)																					
W	F																					
	N																					
Power Supply																						
20																						
Option(s)																						
(nil)																						
B																						
J																						
M																						
S																						
W																						