

## ISE30 Certification: UL 508 and CSA 22.2 No.14



### Certified Options

| ISE30 | - | Piping Specifications | - | Output Specifications | - | Unit Specification | Option 1 | Option 2 |
|-------|---|-----------------------|---|-----------------------|---|--------------------|----------|----------|
|       |   | 1                     |   | 25                    |   | Nil                | Nil      | Nil      |
|       |   | T1                    |   | 26                    |   | M                  | L        | A        |
|       |   | N3H                   |   | 28                    |   |                    |          | B        |
|       |   | C4H                   |   | 65                    |   |                    |          | D        |
|       |   | C6H                   |   |                       |   |                    |          |          |
|       |   | N7H                   |   |                       |   |                    |          |          |
|       |   | N3L                   |   |                       |   |                    |          |          |
|       |   | C4L                   |   |                       |   |                    |          |          |
|       |   | 6CL                   |   |                       |   |                    |          |          |
|       |   | N7L                   |   |                       |   |                    |          |          |