

ISE35 Certification: UL 508 and CSA 22.2 No.14



Certified Options

ISE35	-	<table><tr><th>Piping Specifications</th></tr><tr><td>N</td></tr><tr><td>R</td></tr></table>	Piping Specifications	N	R	-	<table><tr><th>Output Specifications</th></tr><tr><td>25</td></tr><tr><td>26</td></tr><tr><td>28</td></tr><tr><td>65</td></tr></table>	Output Specifications	25	26	28	65	-	<table><tr><th>Unit Specification</th><th>Option 1</th><th>Option 2</th><th>Option 3</th></tr><tr><td>Nil</td><td>Nil</td><td>Nil</td><td>Nil</td></tr><tr><td>M</td><td>L</td><td>A</td><td>S</td></tr><tr><td>P</td><td></td><td>B</td><td></td></tr></table>	Unit Specification	Option 1	Option 2	Option 3	Nil	Nil	Nil	Nil	M	L	A	S	P		B	
	Piping Specifications																													
	N																													
	R																													
	Output Specifications																													
25																														
26																														
28																														
65																														
Unit Specification	Option 1	Option 2	Option 3																											
Nil	Nil	Nil	Nil																											
M	L	A	S																											
P		B																												