

CAUS

Certification Mark

Certified Options					Certified Options				
LE Y	Size	Motor Mounting	Motor type	Lead	Stroke	Motor Option	Rod End Thread	Mounting	Actuator Cable Type/Length
	25	Nil	Nil	A	30	Nil	Nil	Nil	Nil
	32	R	A	B	50	C	M	L	S1
		L		C	100	B		F	S3
		D			150	W		G	S5
					200			D	R1
					250				R3
					300				R5
					350				R8
					400				RA
					450				RB
					500				RC

LEY	Accuracy	Size	Motor Mounting	Motot type	Lead
	Nil	63	Nil	S4	A
			R	S8	B
			L	T8	C
			D		L
-	Stroke	Dust-tight	Motor Option	Rod End Thread	Mounting
	30	Nil	Nil	Nil	Nil
	50	P	B	M	L
	100				F
	150				G
	200				D
	250				
	300				
	350				
	400				
	450				
	500				
	600				
	700				
	800				
-	Cable Type	Cable Length	Driver Type	I/O Cable Length	
	Nil	Nil	Nil	Nil	
	S	2	A2	H	
	R	5	B2	1	
		A	C2		
			S2		
			N2		
			E2		
			92		
			P2		