

PF2M7 Certification: UL 508 and CSA C22.2 No.14



Certified Options

Special Order Number
*Up to 3 alphanumeric characters

PF2M7

Rated Flow Range	Flow Adjustment Valve	Port Size	Output Specification	Option 1
0 1	Nil	0 1	A	Nil
0 2	L	0 2	B	N
0 5	S	C4	C	Q
10	W	C6	D	W
11		C8	E	
21		F1	F	
25		F2	L	
50		N1	L2	
		N2	L3	
		N7	L4	

-

Unit Specification	Option 2	Calibration Certificate	Custom Modification Code
Nil	Nil	Nil	Nil
M	R	A	*additional suffix
	S		
	T		
	V		