

PF3A7 H-L Certification: UL 508 and CSA No.14

Certification Mark



Certified Options

Special Order #1
Nil
Up to 3 Alphanumeric Characters

- PF3A7

Rate Flow Range
0 1
0 2
0 4
0 8
R5

H

Output Specification	Option
L	Nil
L3	N
L4	Q

Unit Specification
Nil
M

Calibration Certificate
Nil
A

Flow Direction
Nil
R

Special Order #2
Nil
Additional Suffix(es)