

PFG20 Certification: UL 508 and CSA No.14

Certification Mark



Certified Options

Special Order #1
Up to 3 Alphanumeric Characters

- PFG20

Input/Output Specifications
0
1
2
3

-

Unit Specification	Option 1	Option 2	Option 3
Nil	A	4C	Nil
M	B	4D	N

-

Special Order #2
Nil
Any alphanumeric characters