

PFM7 Certification: UL 508 and CSA 22.2 No.14-13



Certification Mark

Certified Options

PFM7

Flow Measurement Range	Flow Value
P5	Nil
0 1	S
10	
25	
50	
11	

Thread Type	Piping Inlet
0 1	Nil
0 2	L
N01	
N02	
F01	
F02	
C4	
C6	
C8	
N7	
Any other two digit combination	

1

Output Type
A
B
C
D
E
F
G
H

1

Unit Switching	Manual
Nil	Nil
M	C
	N

1

Certificate	Special Order Number
Nil	Nil
A	Additional Suffix
B	