


PFMB7 or PFMC7 Certification: UL 508 and CSA C22.2 No.14



Certified Options

PFMB7
PFMC7

Rated Flow Range	-	Piping Port Size	-	Output Specification	Lead Wire	Unit Specification	Bracket	Calibration Certificate	-	Special Order Number	Special Order Number
501		0 4		A	Nil	Nil	Nil	Nil		Nil	Nil
102		N04		B	N	M	R	A			*additional suffix
202		F04		C							
		0 6		D							
		N06		E							
		F06		F							
				G							
				H							

PFMB7
PFMC7

Rated Flow Range	-	Thread Type	Port Size	-	Output Specification	Lead Wire	Unit Specification	Bracket	Calibration Certificate	-	Special Order Number	Special Order Number
501		Nil	0 4		A	Nil	Nil	Nil	Nil		Nil	Nil
102		N	0 6		B	N	M	R	A			*additional suffix
202		F			C							
					D							
					E							
					F							
					G							
					H							