

PFMV5 Certification: UL 508 and CSA 22.2 No.14-13



Certified Options

PFMV5	Flow Measurement Range	Output Type	Manual	Option	Special Order Number
	0 5	1	Nil	Nil	Nil
	10	2	C	A	Additional Suffix
	30	3	N		
	05F				
	10F				
	30F				