

PSE56 Certification: UL 508 and CSA 22.2 No.14



Certified Options

PSE56	Option 1	Option 2	-	Option 3	-	Option 4
	0	01		Nil		Nil
	1	02				C1
	3	NO1		28		C2
	4	NO2				
		C01				
		F02				
		A2				
		B2				