

Accessories (Spacers/Brackets)

Spacer



Model	A	B	C	D	Applicable model
Y100-A	6	17.9	9	35.4	**AC10□-A**
Y200-A	3.2	31.2	15.6	44.9	**AC20□-B**
Y300-A	4.2	43.4	21.7	57.9	**AC25□-B, AC30□-B**
Y400-A	5.2	53	26.5	68.5	**AC40□-B**
Y500-A	5.2	57	28.5	75.6	**AC40□-06-B**
Y600-A	6.2	67.6	33.8	92.5	**AC50□-B, AC55□-B, AC60□-B**




Y200-A **Y400-A**

Replacement Parts


Description	Material	Part no.					
		Y100-A	**Y200-A**	**Y300-A**	**Y400-A**	**Y500-A**	**Y600-A**
Seal	HNBR (NBR) Note 1)	Y120P-050AS Note 2)	Y220P-050S	Y320P-050S	Y420P-050S	Y520P-050S	Y620P-050S

Note 1) ( ): Size 10
Note 2) Assembly of 2 O-rings

Spacer with Bracket



Model	A	B	C	D	E	EE	F	G	H	J	K	Applicable model
Y100T-A	6	56	24.5	43.6	20	27	6.8	4.5	13	3	25	**AC10□-A**
Y200T-A	3.2	67	29	53.4	24	33	12	5.5	15.5	3.5	30	**AC20□-B**
Y300T-A	4.2	82	41	71.5	35	—	14	7	19	4	41	**AC25□-B, AC30□-B**
Y400T-A	5.2	96	48	86.1	40	—	18	9	26	5	50	**AC40□-B**
Y500T-A	5.2	96	48	89.6	40	—	18	9	26	5	50	**AC40□-06-B**
Y600T-A	6.2	120	60	118	50	—	20	11	31.2	6	70	**AC50□-B, AC55□-B, AC60□-B**



Y200T-A **Y400T-A**


Replacement Parts

Description	Material	Part no.					
		Y100T-A	**Y200T-A**	**Y300T-A**	**Y400T-A**	**Y500T-A**	**Y600T-A**
Seal	HNBR (NBR) Note 1)	Y120P-050AS Note 2)	Y220P-050S	Y320P-050S	Y420P-050S	Y520P-050S	Y620P-050S

Note 1) ( ): Size 10
Note 2) Assembly of 2 O-rings

Piping Adapter: M5 x 0.8, 1/8, 1/4, 3/8, 1/2, 3/4, 1

A piping adapter allows installation/removal of the component without removing the piping and thus makes maintenance easier.



Model Note)	Port size	A	B	D	Applicable model
E100-M5-A	M5 x 0.8	10	14	14	AC10□-A
E200-□01-A	1/8	29.8	23.5	28	AC20□-B
E200-□02-A	1/4				
E200-□03-A	3/8				
E300-□02-A	1/4	31.8	30	30	AC25□-B, AC30□-B
E300-□03-A	3/8				
E300-□04-A	1/2				
E400-□02-A	1/4	31.8	36	36	AC40□-B
E400-□03-A	3/8				
E400-□04-A	1/2				
E400-□06-A	3/4				
E500-□06-A	3/4	31.8	40	44	AC40□-06-B
E600-□06-A	3/4	35	48	53	AC50-B, AC55-B, AC60-B, AC50A-B, AC60A-B, AC50B-B, AC55B-B, AC60B-B
E600-□10-A	1				

Note) □ in model numbers indicates a pipe thread type. No indication is necessary for Rc; however, indicate N for NPT, and F for G.
* Separate interfaces are required for modular unit.
* Factory mounting of a piping adapter on the AC models is available as a special order.


Pressure Switch with Piping Adapter

Note) For detailed specifications on the IS10 series, refer to the section of our website IS10 series, http://www.smcworld.com

* Separate spacers are required for modular unit.

T-Spacer: (T) M5 x 0.8, 1/8, 1/4, 3/8, 1/2

Using a T-spacer facilitates the branching of air flow.



Model Note)	Port size	A	B	C	D	E	Applicable model
Y110-M5-A	M5 x 0.8	11.2	19	12	14	8	AC10-A, AC10B-A
Y210-□01-A	1/8	14.6	41.8	32	28	19	AC20-B, AC20B-B AC20C-B
Y210-□02-A	1/4						
Y310-□01-A	1/8	14.6	52.7	38.7	30	19	AC25-B, AC25B-B AC25C-B, AC30C-B
Y310-□02-A	1/4						
Y410-□02-A	1/4	18.6	62	44	36	24	AC40-B, AC40B-B AC40C-B
Y410-□03-A	3/8						
Y510-□02-A	1/4	18.6	66	46	44	24	AC40-06-B, AC40B-06-B AC40C-06-B
Y510-□03-A	3/8						
Y610-□03-A	3/8	22	81	57	53	30	AC50-B, AC55-B, AC60-B, AC50B-B, AC55B-B, AC60B-B
Y610-□04-A	1/2						

Note) □ in model numbers indicates a pipe thread type. No indication is necessary for Rc; however, indicate N for NPT, and F for G.
* Separate interfaces are required for modular unit.
* Refer to the attachment table on page 34 for standard port sizes when using with the AC.

Caution on Mounting

If a T-spacer is used on the inlet side of the lubricator, lubricant may be mixed. Use the AKM series check valve to avoid such possibility.