

DWG NO Ⓐ AC60X-F06-6-D-X2106





SPECIFICATIONS
1. REFER TO PRODUCT SPECIFICATION FOR EACH PRODUCT.

CAUTION FOR PRODUCTION
1. SILENCER IS PACKAGED TOGETHER.
2. PRESSURE GAUGE WITH SEALANT IS PACKAGED TOGETHER.
3. NO NEED PLUG FOR THE GAUGE PORT OF FILTER REGULATOR.
4. BARREL NIPPLE AND REDUCING NIPPLE SHOULD BE APPLIED SEALANT AND INSTALLED BEFORE SHIPMENT.
5. CHECK VALVE AND DIGITAL PRESSURE SWITCH SHOULD BE INSTALLED BEFORE SHIPMENT.

BE SURE TO REFER "CATALOG" AND "OPERATING MANUAL" FOR F.R.L. PRECAUTION BEFORE HANDLING.

UNLESS OTHERWISE NOTED ALONG WITH A SEPARATE CONTRACT OR AGREEMENT WITHIN THE PRODUCT SPECIFICATIONS, THE SAFETY INSTRUCTIONS SPECIFIED IN THE PRODUCT CATALOG ARE APPLIED. PLEASE CONTACT YOUR LOCAL SMC SALES OFFICE FOR FURTHER DETAILS.

PARTS PACKAGED TOGETHER




| ITEM | PART NO | PART NAME | MATERIAL | QTY | REMARKS |
|---|---|---|---|---|---|
| 14 | Y340P-070 | PRODUCT LABEL | PET | 1 | COMPLETE PRODUCT NO. INDICATED |
| 13 | VA00179 | REDUCING NIPPLE | CAST IRON | 1 | R3/8×R1/4 Zn.CHROMATE TREATMENT |
| 12 | VA00029 | BARREL NIPPLE | STEEL | 1 | R3/4 Zn.CHROMATE TREATMENT |
| 11 | Y600-D | SPACER | - | 2 | |
| 10 | Y600T-D | SPACER WITH BRACKET | - | 2 | |
| 9 | ANA1-04 | SILENCER | - | 1 | |
| 8 | ISE70-F02-L2 | DIGITAL PRESSURE SWITCH | - | 1 | |
| 7 | G36-P10-01-L-X30 | PRESSURE GAUGE | - | 1 | |
| 6 | E600-F06-D | PIPING ADAPTER | - | 1 | |
| 5 | Y610-F03-1-D | T-SPACER | - | 1 | |
| 4 | AM60-F10-L-D | MIST SEPARATOR | - | 1 | |
| 3 | AW60K-F06-6-D | FILTER REGULATOR | - | 1 | |
| 2 | VHS50-F06-M-D | PRESSURE RELIEF 3 PORT VALVE | - | 1 | |
| 1 | AK6000-F06 | CHECK VALVE | - | 1 | |

| REV | QTY | DESCRIPTION | DATE | PREPARED | REV NO |
|---|---|---|---|---|---|
| A | - | INITIAL RELEASE | 2023-02-15 | K.Sugihara | - |

| | |
|---|---|
| FINISH | - |
| PAINT | - |
| MASS | - |
| PACKING | - |
| MATERIAL | - |
| MATERIAL SIZE | - |

MODEL QTY

THIRD ANGLE

TOLERANCES JIS B 0405

| RANGE(mm) | GRADE f (+) | GRADE m (+) | GRADE c (+) |
|---|---|---|---|
| 0.5≤D≤3 | 0.05 | 0.1 | 0.2 |
| 3<D≤6 | 0.05 | 0.1 | 0.3 |
| 6<D≤30 | 0.1 | 0.2 | 0.5 |
| 30<D≤120 | 0.15 | 0.3 | 0.8 |
| 120<D≤400 | 0.2 | 0.5 | 1.2 |
| 400<D≤1000 | 0.3 | 0.8 | 2 |
| 1000<D≤2000 | 0.5 | 1.2 | 3 |

| | | |
|---|---|---|
| DRAWN | DATE | |
| DESIGNED | K.Sugihara | 2023-02-15 |
| CHECKED | G.Mimura | 2023-02-16 |
| APPROVED | K.Matsushita | 2023-02-17 |

SCALE FREE

DWG NAME AIR COMBINATION

DWG NO Ⓐ AC60X-F06-6-D-X2106

REVISION H

DWG NAME

DWG REC

DWG ID GC10832100

SMC Corporation

SW-A1-V06

FINISH:表面処理 / PAINT:塗装 / MASS:質量
PACKING:包装区分 / MATERIAL:材質
MATERIAL SIZE:材料寸法