ATEX Compliant

Rotary Actuator: Vane Type

Series 55-CRB2

Sizes: 10, 15, 20, 30, 40

CE Ex II 2Gc 130°C (T4) Ta 5°C to 40°C
150°C (T3) Ta 40°C to 60°C

How to Order

Standard **55 – CRB2 B W ☐ – 180 S E Z**

ATEX category 2

Mounting

B	Basic type
F	Flange type

∗ F: Except size 40

Size

10
15
20
30
40

Connecting port position

Nil	Side ports
E	Axial ports

Shaft type

W	Double shaft with single flat (sizes 10 to 30)
	Long shaft key, Short shaft with single flat (size 40)
S	Single shaft (Long shaft) with single flat (sizes 10 to 30)
	Long shaft with key (size 40)

Vane type

S	Single vane
D	Double vane

Rotation

Single vane	90	90°
	180	180°
	270	270°
Double vane	90	90°
	100	100°

All other specifications are the same as the standard products Series CRB2.
For details, refer to **the WEB catalog** or Best Pneumatics No. 4.