ATEX Compliant

Rotary Actuator: Vane Type

Series 56-CRB2

Sizes: 10, 15, 20, 30, 40

CE Ex II 3G 100°C (T5) Ta 5°C to 40°C
120°C (T4) Ta 40°C to 60°C

How to Order

Without magnet 56 – CRB2 B W ☐ – 180 S E Z

With magnet 56 – CDRB2 B W ☐ – 180 S Z

Connecting port position

Nil	Side ports
E	Axial ports

ATEX category 3

With auto switch unit Built-in magnet

Size

10
15
20
30
40

Mounting

B	Basic
F	Flange

∗ F: Except size 40

Vane type

S	Single vane
D	Double vane

Shaft type

W	Double shaft with single flat (sizes 10 to 30)
	Long shaft with key, short shaft with single flat (size 40)
S∗	Single shaft (Long shaft) with single flat (sizes 10 to 30)
	Long shaft with key (size 40)

∗ Cannot be selected when mounting an auto switch

Rotation

Single vane	90	90°
	180	180°
	270	270°
Double vane	90	90°
	100	100°

All other specifications are the same as the standard products Series CRB2.
For details, refer to **the WEB catalog** or Best Pneumatics No. 4.

Refer to page 69 for applicable auto switches.