ATEX Compliant

# Rotary Actuator: Free Mount Type

# *Series 55-CRBU2*

## Sizes: 10, 15, 20, 30, 40

CE Ex II 2Gc 130°C (T4) Ta 5°C to 40°C
150°C (T3) Ta 40°C to 60°C

## How to Order

**Standard**

**55 − CRBU2 W [ ] − 180 S E Z**

- **55**: ATEX category 2
- **CRBU2**: Free mount type
- **W**: Shaft type
- **[ ]**: Size
- **180**: Rotation
- **S**: Vane type
- **E**: Connecting port position

**Size**

| |
|---|
| 10 |
| 15 |
| 20 |
| 30 |
| 40 |

**Shaft type**

| | |
|---|---|
| W | Double shaft with single flat (sizes 10 to 30) |
| | Long shaft with key, short shaft with single flat (size 40) |
| S | Single shaft (Long shaft) with single flat (sizes 10 to 30) |
| | Long shaft with key (size 40) |

**Vane type**

| | |
|---|---|
| S | Single vane |
| D | Double vane |

**Rotation**

| | | |
|---|---|---|
| Single vane | 90 | 90° |
| | 180 | 180° |
| | 270 | 270° |
| Double vane | 90 | 90° |
| | 100 | 100° |

**Connecting port position**

| | |
|---|---|
| Nil | Side ports |
| E | Axial ports |

All other specifications are the same as the standard products Series CRBU2.
For details, refer to **the WEB catalog** or Best Pneumatics No. 4.