


DWG NO Ⓐ AC50X-F06-6-D-X2113







SPECIFICATIONS
1. REFER TO PRODUCT SPECIFICATION ABOUT EACH PRODUCT.

CAUTION FOR PRODUCTION
1. FITTINGS AND SILENCER SHOULD BE INSTALLED BEFORE SHIPMENT.
2. T-SPACER IS MOUNTED DOWNWARDS.
3. No.1-1: L-PIPING ADAPTER SHALL BE ASSEMBLED SO THAT THE PIPING PORT FACE UPWARD.
   No.1-2: L-PIPING ADAPTER SHALL BE ASSEMBLED SO THAT THE PIPING PORT FACE DOWNWARD.

NOTE
AVOID EXCESSIVE TORSIONAL MOMENT OR BENDING MOMENT OTHER THAN THOSE CAUSED BY THE EQUIPMENT'S OWN WEIGHT AS THIS CAN CAUSE DAMAGE.

BE SURE TO REFER "CATALOG" AND "OPERATING MANUAL" FOR F.R.L. PRECAUTION BEFORE HANDLING.

UNLESS OTHERWISE NOTED ALONG WITH A SEPARATE CONTRACT OR AGREEMENT WITHIN THE PRODUCT SPECIFICATIONS, THE SAFETY INSTRUCTIONS SPECIFIED IN THE PRODUCT CATALOG ARE APPLIED. PLEASE CONTACT YOUR LOCAL SMC SALES OFFICE FOR FURTHER DETAILS.

ITEM	PART NO	PART NAME	MATERIAL	QTY	REMARKS
10	Y340P-070	PRODUCT LABEL	PET	1	COMPLETE PRODUCT NO. INDICATED
9	Y600T-D	SPACER WITH BRACKET	-	2	
8	Y600-D	SPACER	-	2	
7	KRP-08	PLUG	-	1	
6	KRK08-G03-X73	45° MALE ELBOW	-	1	
5	AN402-04	SILENCER	-	1	
4	Y610-F03-1-D	T-SPACER	-	1	
3	AF50-F06-6-D	AIR FILTER	-	1	
2	VHS50-F06-M-D	PRESSURE RELIEF 3 PORT VALVE	-	1	
1-2 1-1	E600L-F06-D	L-PIPING ADAPTER	-	2	

REV	QTY	DESCRIPTION	DATE	PREPARED	REV NO
0	-	INITIAL RELEASE	2024-08-23	Y.Ishikawa	-

TOLERANCES JIS B 0405			
RANGE(mm)	GRADE f +/-	m +/-	c +/-
0.5≦D≦3	0.05	0.1	0.2
3<D≦6	0.05	0.1	0.3
6<D≦30	0.1	0.2	0.5
30<D≦120	0.15	0.3	0.8
120<D≦400	0.2	0.5	1.2
400<D≦1000	0.3	0.8	2
1000<D≦2000	0.5	1.2	3

DRAWN	A.Tsukada
DATE	2024-08-23
DESIGNED	Y.Ishikawa
DATE	2024-08-23
CHECKED	G.Mimura
DATE	2024-08-27
APPROVED	G.Endo
DATE	2024-08-27

FINISH	-
PAINT	-
MASS	-
PACKING	-
MATERIAL	-
MATERIAL SIZE	-

SCALE FREE

THIRD ANGLE

MODEL | QTY

DWG NAME
AIR COMBINATION

DWG NO
Ⓐ AC50X-F06-6-D-X2113

REVISION △ H

FINISH:表面処理 / PAINT:塗装 / MASS:質量
PACKING:包装区分 / MATERIAL:材質
MATERIAL SIZE:材料寸法

DWG NAME | DWG REC | DWG ID GC14876100 | SMC Corporation

SW-A2-V06