
DWG NO A AC40X-F04-6-D-X2251



SPECIFICATIONS
1. REFER TO PRODUCT SPECIFICATION FOR EACH PRODUCT.

CAUTION FOR PRODUCTION
1. DIGITAL PRESSURE SWITCH AND SILENCER SHOULD BE INSTALLED BEFORE SHIPMENT.
2. BARREL NIPPLE SHOULD BE APPLIED SEALANT AND INSTALLED BEFORE SHIPMENT.
3. INSTALL HEXAGON SOCKET HEAD PLUG TO THE CHECK VALVE.
4. PRESSURE GAUGE WITH SEALANT IS PACKAGED TOGETHER.
5. NO NEED PLUG FOR THE GAUGE PORT OF FILTER REGULATOR.

BE SURE TO REFER "CATALOG" AND "OPERATING MANUAL" FOR F.R.L. PRECAUTION BEFORE HANDLING.

UNLESS OTHERWISE NOTED ALONG WITH A SEPARATE CONTRACT OR AGREEMENT WITHIN THE PRODUCT SPECIFICATIONS, THE SAFETY INSTRUCTIONS SPECIFIED IN THE PRODUCT CATALOG ARE APPLIED. PLEASE CONTACT YOUR LOCAL SMC SALES OFFICE FOR FURTHER DETAILS.

ITEM	PART NO	PART NAME	MATERIAL	QTY	REMARKS
14	Y340P-070	PRODUCT LABEL	PET	1	COMPLETE PRODUCT NO. INDICATED
13	VA00034	BARREL NIPPLE	STEEL	1	R1/4 Zn.CHROMATE TREATMENT
12	TB00185	HEXAGON SOCKET HEAD PLUG	STEEL	1	R3/8 Zn.CHROMATE TREATMENT
11	Y400-D	SPACER	-	3	
10	Y400T-D	SPACER WITH BRACKET	-	3	
9	ISE70-F02-L2	DIGITAL PRESSURE SWITCH	-	1	
8	G36-P10-01-L-X30	PRESSURE GAUGE	-	1	
7	ANA1-03	SILENCER	-	1	
6	Y410-F02-1-D	T-SPACER	-	1	
5	AFM40-F04-6-D	MIST SEPARATOR	-	1	
4	AW40K-F04-6-D	FILTER REGULATOR	-	1	
3	VHS40-F04-M-D	PRESSURE RELIEF 3 PORT VALVE	-	1	
2	AKM4000-F03-A	CHECK VALVE	-	1	
1	E400-F04-D	PIPING ADAPTER	-	2	

REV	QTY	DESCRIPTION	DATE	PREPARED	REV NO
0	-	INITIAL RELEASE	2023-02-15	K.Sugihara	-

TOLERANCES JIS B 0405			
RANGE(mm)	GRADE f ±	m ±	c + -
0.5≤D≤3	0.05	0.1	0.2
3<D≤6	0.05	0.1	0.3
6<D≤30	0.1	0.2	0.5
30<D≤120	0.15	0.3	0.8
120<D≤400	0.2	0.5	1.2
400<D≤1000	0.3	0.8	2
1000<D≤2000	0.5	1.2	3

DRAWN		
DATE		
DESIGNED	K.Sugihara	
DATE	2023-02-15	
CHECKED	G.Mimura	
DATE	2023-02-16	
APPROVED	K.Matsushita	
DATE	2023-02-17	

FINISH	-
PAINT	-
MASS	-
PACKING	-
MATERIAL	-
MATERIAL SIZE	-

MODEL QTY

THIRD ANGLE

SCALE FREE

DWG NAME AIR COMBINATION

DWG NO A AC40X-F04-6-D-X2251

REVISION H

DWG NAME | DWG REC | DWG ID GC10824000

SMC Corporation

SW-A2-V06

FINISH:表面処理 / PAINT:塗装 / MASS:質量
PACKING:包装区分 / MATERIAL:材質
MATERIAL SIZE:材料寸法