
DWG NO Ⓐ AC40X-F04-6-D-X2344 1



SPECIFICATIONS
1. REFER TO PRODUCT SPECIFICATION FOR EACH PRODUCT.

CAUTION FOR PRODUCTION
1. SILENCER SHOULD BE INSTALLED BEFORE SHIPMENT.
2. PRESSURE GAUGE WITH SEALANT IS PACKAGED TOGETHER.
3. DIGITAL PRESSURE SWITCH AND REDUCING NIPPLE ARE PACKAGED TOGETHER.
4. NO NEED PLUG FOR THE GAUGE PORT OF FILTER REGULATOR AND SOFT START-UP VALVE.
5. NO NEED SEALANT FOR REDUCING NIPPLE.
6. NO NEED RESIN PLUG FOR THE FRONT AND BACK PORT OF CROSS SPACER.
7. ⑬⑭HEXAGON SOCKET HEAD PLUG SHOULD BE INSTALLED BEFORE SHIPMENT.

NOTE
PRESSURE GAUGE AND DIGITAL PRESSURE SWITCH ARE FOR OVERSEAS USE ONLY ACCORDING TO THE NEW MEASUREMENT ACT.
(THE SI UNIT TYPE IS PROVIDED FOR USE IN JAPAN.)

ITEM	PART NO	PART NAME	MATERIAL	QTY	REMARKS
15	Y340P-070	PRODUCT LABEL	PET	1	COMPLETE PRODUCT NO. INDICATED
14	TB00179	HEXAGON SOCKET HEAD PLUG	STEEL	2	R1/2 Zn.CHROMATE TREATMENT
13	TB00004	HEXAGON SOCKET HEAD PLUG	STEEL	2	R1/8 Zn.CHROMATE TREATMENT
12	VA00179	REDUCING NIPPLE	STEEL	1	R3/8×R1/4 Zn.CHROMATE TREATMENT
11	Y400-D	SPACER	-	2	
10	Y400T-D	SPACER WITH BRACKET	-	4	
9	ISE70-F02-L2	DIGITAL PRESSURE SWITCH	-	1	
8	ANA1-04	SILENCER	-	1	
7	G36-P10-01-L-X30	PRESSURE GAUGE	-	2	
6	Y410-F03-1-D	T-SPACER	-	1	
5	AVL4000-F04-A	SOFT START-UP VALVE	-	1	
4	Y44-F04-D	CROSS SPACER	-	1	
3	AM40-F04-6L-D	MIST SEPARATOR	-	1	
2	AW40K-F04-6-D	FILTER REGULATOR	-	1	
1	E400-F04-D	PIPING ADAPTER	-	2	

REV	QTY	DESCRIPTION	DATE	PREPARED	REV NO
1	1	AM40-F04-L-D→AM40-F04-6L-D	2023-12-14	Y.Ishikawa	DOC1064010
0	-	INITIAL RELEASE	2023-11-06	Y.Ishikawa	-

TOLERANCES JIS B 0405			
RANGE(mm)	GRADE f	m	c
0.5≤D≤3	0.05	0.1	0.2
3<D≤6	0.05	0.1	0.3
6<D≤30	0.1	0.2	0.5
30<D≤120	0.15	0.3	0.8
120<D≤400	0.2	0.5	1.2
400<D≤1000	0.3	0.8	2
1000<D≤2000	0.5	1.2	3

DRAWN	
DATE	
DESIGNED	Y.Ishikawa
DATE	2023-12-14
CHECKED	G.Mimura
DATE	2023-12-15
APPROVED	K.Matsushita
DATE	2023-12-15

FINISH	-
PAINT	-
MASS	-
PACKING	-
MATERIAL	-
MATERIAL SIZE	-

MODEL / QTY

THIRD ANGLE

SCALE: FREE

DWG NAME: AIR COMBINATION

DWG NO: Ⓐ AC40X-F04-6-D-X2344

REVISION: 1

H

BE SURE TO REFER "CATALOG" AND "OPERATING MANUAL" FOR F.R.L. PRECAUTION BEFORE HANDLING.

UNLESS OTHERWISE NOTED ALONG WITH A SEPARATE CONTRACT OR AGREEMENT WITHIN THE PRODUCT SPECIFICATIONS, THE SAFETY INSTRUCTIONS SPECIFIED IN THE PRODUCT CATALOG ARE APPLIED. PLEASE CONTACT YOUR LOCAL SMC SALES OFFICE FOR FURTHER DETAILS.

FINISH:表面処理 / PAINT:塗装 / MASS:質量
PACKING:包装区分 / MATERIAL:材質
MATERIAL SIZE:材料寸法

DWG NAME | DWG REC | DWG ID GC12646801 | SMC Corporation

SW-A2-V06