

DWG NO Ⓐ AC50X-F06~F10-6-D-X2249





SPECIFICATIONS
1. REFER TO PRODUCT SPECIFICATION FOR EACH PRODUCT.

CAUTION FOR PRODUCTION
1. SILENCER SHOULD BE INSTALLED BEFORE SHIPMENT.
2. DIGITAL PRESSURE SWITCH AND REDUCING NIPPLE ARE PACKAGED TOGETHER.
3. NO NEED SEALANT FOR REDUCING NIPPLE.

BE SURE TO REFER "CATALOG" AND "OPERATING MANUAL" FOR F.R.L. PRECAUTION BEFORE HANDLING.

UNLESS OTHERWISE NOTED ALONG WITH A SEPARATE CONTRACT OR AGREEMENT WITHIN THE PRODUCT SPECIFICATIONS, THE SAFETY INSTRUCTIONS SPECIFIED IN THE PRODUCT CATALOG ARE APPLIED. PLEASE CONTACT YOUR LOCAL SMC SALES OFFICE FOR FURTHER DETAILS.

ITEM	PART NO	PART NAME	MATERIAL	QTY	REMARKS
10	Y340P-070	PRODUCT LABEL	PET	1	COMPLETE PRODUCT NO. INDICATED
9	VA00179	REDUCING NIPPLE	IRON	1	R3/8×R1/4 Zn.CHROMATE TREATMENT
8	Y600-D	SPACER	-	1	
7	Y600T-D	SPACER WITH BRACKET	-	2	
6	AN402-04	SILENCER	-	1	
5	ISE70-F02-L2	DIGITAL PRESSURE SWITCH	-	1	
4	E600-F06~F10-D	PIPING ADAPTER	-	1	
3	Y610-F03-1-D	T-SPACER	-	1	
2	AF50-F06~F10-6-D	AIR FILTER	-	1	
1	VHS50-F06~F10-M-D	PRESSURE RELIEF 3 PORT VALVE	-	1	

REV	QTY	DESCRIPTION	DATE	PREPARED	REV NO
0	-	INITIAL RELEASE	2023-02-14	Y.Ishikawa	-

FINISH	-
PAINT	-
MASS	-
PACKING	-
MATERIAL	-
MATERIAL SIZE	-

MODEL	QTY

THIRD ANGLE

TOLERANCES JIS B 0405

RANGE(mm)	GRADE f ±	m ±	c ±
0.5≤D≤3	0.05	0.1	0.2
3<D≤6	0.05	0.1	0.3
6<D≤30	0.1	0.2	0.5
30<D≤120	0.15	0.3	0.8
120<D≤400	0.2	0.5	1.2
400<D≤1000	0.3	0.8	2
1000<D≤2000	0.5	1.2	3

DRAWN		
DATE		
DESIGNED	Y.Ishikawa	
DATE	2023-02-14	
CHECKED	G.Mimura	
DATE	2023-02-15	
APPROVED	K.Matsushita	
DATE	2023-02-16	

SCALE FREE

DWG NAME AIR COMBINATION

DWG NO Ⓐ AC50X-F06~F10-6-D-X2249

REVISION △ H

FINISH:表面処理 / PAINT:塗装 / MASS:質量
PACKING:包装区分 / MATERIAL:材質
MATERIAL SIZE:材料寸法

DWG NAME | DWG REC | DWG ID GC10812700 | SMC Corporation

SW-A2-V06