



SY7000 D-SUB, Flat Ribbon Accessory Components

Replacement One Touch Fittings					
Port Size		Fitting Type	SY7000		
A, B Port	Metric	Straight	Ø6	VVQ2000-51A-C6	
			Ø8	VVQ2000-51A-C8	
			Ø10	VVQ2000-51A-C10	
			Ø12	KQ2H12-17-X224	
		Elbow	Ø6	SZ3000-83-1A-L6	
			Ø8	SZ3000-83-1A-L8	
			Ø10	SZ3000-83-1A-L10	
			Ø12	KQ2L12-17N-X224	
		Long Elbow	Ø6	SZ3000-83-2A-L6	
			Ø8	SZ3000-83-2A-L8	
			Ø10	SZ3000-83-2A-L10	
			Ø12	KQ2W12-17N-X224	
	Inch	Metric	Straight 	Ø1/4"	VVQ2000-51A-N7
				Ø5/16"	VVQ2000-51A-N9
				Ø3/8"	VVQ2000-51A-N11
Ø3/8"				KQ2L11-14-X224	
Inch		Ø3/8"	Long Elbow 	KQ2L11-14-X225	
P, E Port	Metric	Ø12	Straight	VVQ4000-50B-C12	
			Elbow	KQ2L12-19N-X224	
			Long Elbow	KQ2W12-19N-X224	
	Inch	Ø1/2"	Straight	VVQ4000-50B-N13	
			Elbow	KQ2L13-19N-X224	
			Long Elbow	KQ2W13-19N-X224	
Plug Assembly		For A,B Port	VVQ2000-58A		
		For P, E Port	SY9000-62-1A		

Manifold Options	Port Size	Type	Part Number		
Individual Supply Block Assembly Includes 2pcs Blocking Disks	Metric	Straight	Ø6	SY70M-78-1A-C6	
			Ø8	SY70M-78-1A-C8	
			Ø10	SY70M-78-1A-C10	
			Ø12	SY70M-78-1A-C12	
	Inch	Ø1/4"	Straight	Ø5/16"	SY70M-78-1A-N7
				Ø3/8"	SY70M-78-1A-N9
				Ø3/8"	SY70M-78-1A-N11
	Metric	Short Elbow	Ø6	SY70M-78-2A-L6	
			Ø8	SY70M-78-2A-L8	
			Ø10	SY70M-78-2A-L10	
			Ø12	SY70M-78-2A-L12	
	Inch	Ø3/8"	Short Elbow	SY70M-78-2A-LN11	
Metric	Long Elbow	Ø6	SY70M-78-3A-L6		
		Ø8	SY70M-78-3A-L8		
		Ø10	SY70M-78-3A-L10		
		Ø12	SY70M-78-3A-L12		
Inch	Ø3/8"	Long Elbow	SY70M-78-3A-LN11		
Individual Exhaust Block Assembly Includes 4pcs Blocking Disks	Metric	Straight	Ø6	SY70M-79-1A-C6	
			Ø8	SY70M-79-1A-C8	
			Ø10	SY70M-79-1A-C10	
			Ø12	SY70M-79-1A-C12	
	Inch	Ø1/4"	Straight	Ø5/16"	SY70M-79-1A-N7
				Ø3/8"	SY70M-79-1A-N9
				Ø3/8"	SY70M-79-1A-N11
	Metric	Short Elbow	Ø6	SY70M-79-2A-L6	
			Ø8	SY70M-79-2A-L8	
			Ø10	SY70M-79-2A-L10	
			Ø12	SY70M-79-2A-L12	
	Inch	Ø3/8"	Short Elbow	SY70M-79-2A-LN11	
Metric	Long Elbow	Ø6	SY70M-79-3A-L6		
		Ø8	SY70M-79-3A-L8		
		Ø10	SY70M-79-3A-L10		
		Ø12	SY70M-79-3A-L12		
Inch	Ø3/8"	Long Elbow	SY70M-79-3A-LN11		
SUP blocking disk			SY70M-40-1A		
EXH Blocking Disk			SY70M-40-1A		
Label for Blocking Disk			SJ3000-155-1A		
Back Pressure Check Valve Assembly			SY70M-24-1A		

Cable Type	Length	Part Number
D-SUB	1.5 m	AXT100-DS25-015
	3 m	AXT100-DS25-030
	5 m	AXT100-DS25-050
IP67 D-SUB	1.5 m	SY30M-DS25-015
	3 m	SY30M-DS25-030
	5 m	SY30M-DS25-050
Flat Ribbon 26 Pin	1.5 m	AXT100-FC26-1
	3 m	AXT100-FC26-2
	5 m	AXT100-FC26-3
Flat Ribbon 20 Pin	1.5 m	AXT100-FC20-1
	3 m	AXT100-FC20-2
	5 m	AXT100-FC20-3
Flat Ribbon 10 Pin	1.5 m	AXT100-FC10-1
	3 m	AXT100-FC10-2
	5 m	AXT100-FC10-3