

Certificate of Compliance

Certificate Number(s):

UL-US-L001101-6

Report Reference:

MH11419-20081002

Issue Date:

2025-10-30

Issued to:

SMC CORP

1-5-5 Kyobashi, Chuo-ku, Tokyo, 104-0031, JP

This certificate confirms that representative samples of:

YIOZ2 - Valves, Electrically Operated - Component

See Addendum Page for Product Designation(s).

Have been evaluated by UL in accordance with the component requirements in the Standard(s) indicated on this Certificate. UL Recognized components are incomplete in certain constructional features or restricted in performance capabilities and are intended for installation in complete equipment submitted for investigation to UL LLC.

UL 429, 7th Ed., Issue Date: 2013-11-6, Revision Date: 2021-3-19

Additional Information:

See UL Product iQ® at <https://iq.ulprospector.com> for additional information.

This Certificate of Compliance indicates that representative samples of the product described in the certification report have met the requirements for UL certification. It does not provide authorization to apply the UL Recognized Component Mark. Only the Authorization Page that references the Follow-Up Services Procedure for ongoing surveillance provides authorization to apply the UL Mark.

Only those products bearing the UL Recognized Component Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Recognized Component Mark on the product.



David Piecuch

UL Mark Certification Program Manager



Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact UL Solutions Customer Service at <https://www.ul.com/contact-us>.

CERTIFICATE OF COMPLIANCE

Certificate number(s): UL-US-L001101-6
Report reference: MH11419-20081002
Issue Date: 2025-10-30

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

General-purpose valve

Model(s): SS3J or 10-SS3J , followed by 3, followed by V, followed by 60, followed by G, followed by D, followed by 01 through 08, followed by B, D, M, or U, with or without B or L, with or without 2 through 8.

Model(s): SS3J or 10-SS3J, followed by 3 , followed by V, followed by 60S, followed by 0, Q, Q1, Q2, Q3, V, or V2, with or without A, with or without N, with or without D, followed by 01 through 16, followed by B, D, M, or U, with or without B or L, with or without 2 through 16.

Model(s): SS3J or 10-SS3J, followed by 3, followed by V, followed by 60S6B, with or without N, followed by D, followed by 01 through 08, followed by B, D, M, or U, with or without B or L, with or without 2 through 08.

Model(s): SS5J or 10-SS5J, followed by 1, 2 or 3, with or without M, followed by 60S6B, with or without N, followed by D, followed by 01 through 16, followed by B, D, M, or U, with or without R, RS, or S, with or without B or L, with or without 2 through 16.

Model(s): SJ or 10-SJ followed by 3, followed by 1 or 2, followed by 60, followed by A, with or without R, with or without T, followed by 5 or 6, with or without N, followed by C, M, MN, or MO, followed by U or Z, followed by J, with or without D or F, followed by C4, C6, L4, L6, B4, B6, N3, N7, LN3, LN7, BN3, BN7, M5, with or without D .

Model(s): SS5J or 10-SS5J, followed by 4, with or without M, followed by 60, followed by F, P, PG, or PH, followed by D, followed by 1 or 2, followed by 01 through 24, followed by B, D, M, or U, with or without 2 through 24.

Model(s): SJ or 10-SJ followed by 1, 2 or 3, followed by 1, 2, 3, 4, 5, A, B or C, followed by 60, with or without R, with or without E, K or P, with or without T, with or without N, followed by 5 or 6, with or without N, followed by C, F, M, MN or MO, followed by U or Z, with or without J, with or without D or F, followed by B2, B4, B6, BN1, BN3, BN7, C0, C2, C4, C6, L2, L4, L6, LN1, LN3, LN7, M3, M5, N1, N3 or N7, with or without D.

Model(s): SS5J or 10-SS5J followed by 1, 2 or 3, with or without M, followed by 60, followed by 01 through 20, followed by B, D, M, or U, with or without R, RS, or S, with or without B or L, with or without 2 through 20.

Model(s): SS5J or 10-SS5J followed by 1, 2 or 3, with or without M, followed by 60, followed by G, followed by D, followed by 01 through 16, followed by B, D, M, or U, with or without R, RS, or S, with or without B or L, with or without 2 through 16.

Model(s): SS5J, 10-SS5J followed by 1, 2 or 3, with or without M, followed by 60, with or without L, followed by F, P, PG, J or PH, followed by D followed by 1 or 2, followed by 01 through 24, followed by B, D, M, or U, with or without R, RS, or S, with or without B or L, with or without 2 through 24.

Model(s): SS5J or 10-SS5J, followed by 1, 2 or 3, with or without M, followed by 60S, followed by 0, Q, Q1, Q2, Q3, V or V2, with or without A, with or without N, with or without D, followed by 01 through 32, followed by B, D, M, or U, with or without R, RS, or S, with or without B or L, with or without 2 through 32.

Model(s): SJ4 or 10-SJ4 followed by 1, 2, 3, 4, 5, A, B or C, followed by 60, with or without R, with or without T, followed by 5, with or without N, followed by C, followed by U or Z, with or without D, followed by C6 or C8, with or without D.

Model(s): SJ, 10-SJ followed by 3, followed by A6, with or without T, with or without N, followed by 5 or 6, with or without N, followed by C, F, M, MN or MO, followed by U or Z, with or without J, with or without D, with or without D, with or without P.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact UL Solutions Customer Service at <https://www.ul.com/contact-us>.



CERTIFICATE OF COMPLIANCE

Report reference: MH11419 -VOL3
Certificate Generation Date: 2025-10-30

Model(s): SS3J, 10-SS3J followed by 3, followed by V, followed by 60, followed by 01 through 20, followed by B, D, M, or U, with or without B or L, with or without 2 through 20.

Model(s): SS3J or 10-SS3J, followed by 3, followed by V, followed by 60, with or without L, followed by F, P, PG, J, or PH, followed by D, followed by 1 or 2, followed by 01 through 12, followed by B, D, M, or U, with or without B or L, with or without 2 through 12.

Model(s): One-Touch Fittings, : KQSY31 followed by C10, with X1336.

Model(s): One-Touch Fittings, : KQSY10 followed by C2, or C4, with or without X1336.

Model(s): One-Touch Fittings, : KQSY30 followed by C8.

Model(s): One-Touch Fittings, : KJ followed by H, L, or W, followed by 01 through 07, followed by C1 or C2.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact UL Solutions Customer Service at <https://www.ul.com/contact-us>.

