# Speed Controller: Standard Type Elbow Type (Metal Body)

# AS Series



# Minimizes installation time and cost

Fittings and tubing are not necessary because this type screws directly into the actuator. Thus, piping labor and cost can be eliminated.

## Body swivels 360°

Swivel type allows free setting of piping.

Speed may be accurately controlled even at low speeds.

Able to control and set a constant speed easily.

Retainer prevents accidental loss of needle.









Symbol	Specifications
-X12	Lubricant: Vaseline
-X21	Grease-free (Seal: Fluorine-coated) + Throttle valve (Without check valve)
-X214	Throttle valve (Without check valve)

#### **Specifications**


Specifications Model		AS1400-M3	AS12[]0-M5	AS12[]0-U10/32	AS22[]0-01	AS22∏0-02	AS32∏0-03	AS42∏0-04		
Port size		0.5	M5 x 0.8	10-32 UNF	1/8	1/4	3/8	1/2		
	Air									
essure	1.05	1.05 MPa 1.5 MPa								
rating pressure	0.71	MРа			1 M	IPa				
Min. operating pressure		MРа		0.1 MPa						
Ambient and fluid temperature		−5 to 60°C (No freezing)								
Option		-	Round lock nut With seal, Round lock nut, Nickel plated							
Weight (g)		6	1	0	29	64	106	181		
Flow rate L/min (ANR)	20		1	05	230	460	920	1700		
Sonic conductance dm3/(s-bar)	0.06		0.	32	0.7 1.4		2.8	5.2		
Controlled flow	0.2		0	.2	0.25 0.3		0.25	0.25		
Free flow	0.4		0	.4	0.2 0.3 0.2			0.3		
	essure rating pressure rating pressure d fluid temperature  j) Flow rate L/min (ANR) Sonic conductance dm <sup>2</sup> (star) Controlled flow	M3	M3 x 0.5	M3 x 0.5   M5 x 0.8	M3 x 0.5   M5 x 0.8   10-32 UNF	M3 x 0.5   M5 x 0.8   10.32 UNF   1/8	M3 x 0.5   M5 x 0.8   10.32 UNF   1/8   1/4	M3 x 0.5   M5 x 0.8   10·32 UNF   1/8   1/4   3/8		

- Note 1) Flow rate values are measured at 0.5 MPa and 20°C.
- Note 2) Meter-in type not available on AS1200-M3, AS1400-M3.
- Note 3) Distinction between meter-out/meter-in types by appearance.

Those are distinguished by the lock nut. The meter-out type is zinc chromated (the round lock nut is electroless nickel plated), while the meter-in type is black zinc chromate plated.

Note 4) AS12□0, AS1400, AS22□0, AS32□0: Brass parts are electroless nickel plated, provided as standard. (N specifications)





R Rc
Metric thread (M3, M5)

\*1 When using a G female thread, be sure to select the option with a seal (S) as the thread requires sealant. Also, if a G thread is required for on the cylinder side, it will need to be special ordered, so please contact SMC separately for details.

Unified thread (10-32 UNF

\*2 The R thread can be screwed into the G female thread.

# necessary. Bore size

Symbol	Bore size	Applicable series						
МЗ	M3 x 0.5	AS1200-M3 AS1400-M3						
M5	M5 x 0.8	AS12□0-M5						
U10/32	10-32 UNF	AS12□0-U10/32						
01	1/8	AS22□0-01						
02	1/4	AS22□0-02						
03	3/8	AS32□0-03						
04	1/2	AS42□0-04						





N F


# Speed Controller: Standard Type Elbow Type (Metal Body) **AS** Series


## Needle Valve/Flow Rate Characteristics


Note) The flow rate characteristics are representative values.














## **∆**Caution

Be sure to read this before handling the products.

Refer to back page 50 for Safety Instructions and pages 543 to 546 for Flow Control Equipment Precautions.

Made to Order

Made to Order

**Lubricant: Vaseline** 

X12

Throttle Valve (Without Check Valve)
Ex.) AS2200-01-X21

X21

Ex.) AS2200-01-X12

Ne

Note 1) Not particle-free

Note 2) Throttle valve is only compatible with the part no. of the meter-out type.

Grease-free (Seal: Fluorine Coated) +

Throttle Valve (Without Check Valve) X2

Ex.) AS2200-01-X214

Note) Throttle valve is only compatible with the part no. of the meter-out type.

647

AS-F

ASD AS

AS-FE KE

AS-FG

AS-FM

AS-D

ASP

ASN AQ

ASV


AK

VCHC

ASR ASQ

# AS Series

## Construction: AS1400-M3



## **Component Parts**

No.	Description	Material	Note
1	Body B	Brass	Electroless nickel plated
2	Body A	Brass	Electroless nickel plated
3	Needle	Brass	Electroless nickel plated
4	Lock nut	Steel (1)	Zinc chromated (1)
5	Handle	Brass	Electroless nickel plated
6	U seal	HNBR	
7	Needle guide	Brass	Electroless nickel plated
8	O-ring	NBR	
9	O-ring	NBR	
10	Steel ball	Chromium bearing steel	
11	Gasket	PVC	
12	Joint	Brass	Electroless nickel plated


Note 1) The material and surface treatment of the lock nut option-J (round type) is brass and electroless nickel plating, respectively.


# Construction: AS1200-M3, AS12□0-M5, AS22□0/32□0/42□0


## Meter-out type


AS1200-M3, M5, U10/32

AS2200, 3200, 4200











# Meter-in type

AS1210-M5, U10/32







## **Component Parts**

••••	.ponone i a						
No.	Description	Material	Note				
1	Body A	Zinc alloy					
2	Handle	Brass	Electroless nickel plated				
3	Body B	Brass	Electroless nickel plated				
4	Needle	Brass	Electroless nickel plated				
5	Needle guide	Brass	Electroless nickel plated				
6	Seat ring	Brass	Electroless nickel plated (1)				
7	Lock nut	Steel (2)	Meter-out	Zinc chromate plated (3)			
′		Steer	Meter-in	Black zinc chromate plated			
8	U seal	HNBR					
9	O-ring	NBR					
10	O-ring	NBR					
11	O-ring	NBR					
12	Bushing	PBT	01 to 04 type				
13	O-ring	NBR	01 to 04 type				
14	Gasket	PVC	M3 type				
14	Gasket	NBR, Stainless steel	M5, U10/32 type				

Note 1) For the AS42\(\subseteq\$0 type only, the electroless nickel plating specification is available for option N.
Note 2) The material of the lock nut option-J (round type) is brass. However,
note that only the AS22\(\subseteq\$0 uses steel.


Note 3) The surface treatment of the lock nut option-J (round type) is electroless nickel plated.



# Speed Controller: Standard Type Elbow Type (Metal Body) AS Series


Dimensions: AS-1200-M3, AS12□0-M5,

AS22□0/32□0/42□0




\* Reference dimensions

Dimensions: AS1400-M3



AS22□0, 32□0, 42□0



#### Dimensions

Dimensions											
Model	T1	T1 T2 H (1) L	L1	L1 L2		2 L3		D2	<b>A</b> (2)		
Wodei	٠.,	12	H (1)		Max.	Min.	LJ	D1	02	Max.	Min.
AS1200-M3	M3 x 0.5	M3 x 0.5	4.5	6.6	23.5	21.5	8	5	5	20.5	18.5
AS12□0-M5	M5 x 0.8	M5 x 0.8	8	10	20.2	25.5	10.0	9	9	25	22.2
AS12 0-U10/32	10-32UNF	10-32UNF	l <sup>8</sup>	10	20.3	25.5	10.3	9	9	25	22.2
AS22□0-01	1/8	1/8	12 (12.7)	18	35.5	30.5	13.2	14.3	14.6	32.4	27.4
AS22□0-02	1/4	1/4	17 (17.5)	27.2	40.3	35.3	17.5	18	19.5	34.8	29.8
AS32□0-03	3/8	3/8	19	30	45.8	40.8	19.7	22.5	24.3	40.6	35.6
AS42□0-04	1/2	1/2	24 (23.8)	38.5	54.7	49.7	25.8	27.5	28.5	47.4	42.4

Note 1) ( ) are the dimensions of "NPT" thread. Note 2) Reference thread dimensions after installation.

Note 3) L2: Reference dimensions

**SMC** 

AS-F TMH

ASD

AS

AS-FE KE

AS-FG

AS-FP

AS-FM AS-D

AS-T

ASP ASN

AQ

ASV

AK

VCHC ASR ASQ