

# Modular Type Air Filter *AF Series*


Air Filter AF Series   p. 74 to 83	Model	Port size	Filtration [μm]	Options
	AF20-D	1/8, 1/4	5	Bracket  Float type auto drain
	AF30-D	1/4, 3/8		
	AF40-D	1/4, 3/8, 1/2		
	AF40-06-D	3/4		
	AF50-D	3/4, 1		
	AF60-D	1		

# Air Filter



# AF20-D to AF60-D

## Symbol

Air Filter



Air Filter with Auto Drain



AF30-D

## How to Order

**AF** **30** - **03** **BD** - **D**

① ② ③ ④ ⑤

## Option and Semi-standard Symbol Selection

- Select one each for a to g.
- When more than one specification is required, indicate in alphanumeric order.

Example) AF30-F03BD-2LR-D

		Symbol	Description	1									
				Body size									
				20	30	40	50	60					
2	Pipe thread type	Nil	Rc	●	●	●	●	●					
		N	NPT	●	●	●	●	●					
		F	G	●	●	●	●	●					
+													
3	Port size	01	1/8	●	—	—	—	—					
		02	1/4	●	●	●	—	—					
		03	3/8	—	●	●	—	—					
		04	1/2	—	—	●	—	—					
		06	3/4	—	—	●	●	—					
		10	1	—	—	—	●	●					
+													
4	Option	a	Mounting	Nil	Without mounting option				●	●	●	●	●
				B*1	With bracket				●	●	●	●	●
	+												
	b	Float type auto drain*2	Nil	Without auto drain				●	●	●	●	●	
			C*3	N.C. (Normally closed) Drain port is closed when pressure is not applied.				●	●	●	●	●	
			D*4	N.O. (Normally open) Drain port is open when pressure is not applied.				—	●	●	●	●	
+													
5	Semi-standard	c	Bowl <sup>1</sup> *5	Nil	Polycarbonate bowl				●	●	●	●	●
				2	Metal bowl				●	●	●	●	●
				6	Nylon bowl				●	●	●	●	●
				8	Metal bowl with level gauge				—	●	●	●	●
				C	With bowl guard				●	—*6	—*6	—*6	—*6
				6C	With bowl guard (Nylon bowl)				●	—*7	—*7	—*7	—*7
		+											
		d	Indicator	Nil	Without indicator				●	●	●	●	●
				L	With element service indicator*14				●	●	●*12	●	●
		+											
		e	Drain port*8	Nil	With drain cock				●	●	●	●	●
				J*9	Drain guide 1/8				●	—	—	—	—
					Drain guide 1/4				—	●	●	●	●
				W*10	Drain cock with barb fitting				—	●	●	●	●
		+											
		f	Flow direction	Nil	Flow direction: Left to right				●	●	●	●	●
R	Flow direction: Right to left				●	●	●	●	●				
+													
g	Unit	Nil	Unit on product label: MPa, °C				●	●	●	●	●		
		Z*11	Unit on product label: psi, °F				○*13	○*13	○*13	○*13	○*13		

\*1 Option B is included in the package with the product but does not come assembled. The assembly consists of 2 types of the bracket and 2 mounting screws.

\*2 The auto drain port is ø10 One-touch fitting (② Pipe thread type: Rc, G) or ø3/8" One-touch fitting (② Pipe thread type: NPT)

\*3 When pressure is not applied, condensate which does not start the auto drain mechanism will be left in the bowl. Releasing the residual condensate before ending operations for the day is recommended.

\*4 If the compressor is small (0.75 kW, discharge flow is less than 100 L/min (ANR)), air leakage from the drain cock may occur during the start of operations. N.C. type is recommended.

\*5 Refer to chemical data on page 83 for chemical resistance of the bowl.

\*6 A bowl guard is provided as standard equipment (polycarbonate).

\*7 A bowl guard is provided as standard equipment (nylon).

\*8 The combination of float type auto drain C and D is not available.

\*9 Without a valve function. The mounting screws are the same as the thread of ②.

\*10 The combination of metal bowl 2 and 8 is not available.

\*11 For the pipe thread type: NPT. This product is for overseas use only according to the New Measurement Act. (The SI unit type is provided for use in Japan.)

\*12 Excludes port size "06"

\*13 ○: For the pipe thread type: NPT only

\*14 A special body type is required to mount the element service indicator. It cannot be mounted on a standard body.

AC

AF + AR + AL

AW + AL

AW + AR

AF + AR

AF + AFM + AR

AW + AFM

Attachments

AF

AFM / AFD

AR

AL

AW

# AF20-D to AF60-D Series

## Standard Specifications

Model		AF20-D	AF30-D	AF40-D	AF40-06-D	AF50-D	AF60-D
Port size		1/8, 1/4	1/4, 3/8	1/4, 3/8, 1/2	3/4	3/4, 1	1
Fluid		Air					
Ambient and fluid temperatures		-5 to 60°C (No freezing)					
Proof pressure		1.5 MPa					
Max. operating pressure		1.0 MPa					
Auto drain minimum operating pressure	N.C.	0.1 MPa	0.15 MPa				
	N.O.	—	0.1 MPa				
Nominal filtration rating*1		5 µm					
Compressed air purity class*2		ISO 8573-1:2010 [ 6 : 8 : 4 ]*3					
Drain capacity		8 cm <sup>3</sup>	25 cm <sup>3</sup>	45 cm <sup>3</sup>			
Bowl material		Polycarbonate					
Bowl guard		Semi-standard (Steel)	Standard (Polycarbonate)				
Weight		0.09 kg	0.17 kg	0.35 kg	0.39 kg	0.85 kg	0.92 kg

\*1 For the following conditions in accordance with [Test condition: ISO 8573-4:2001 compliant, Test method ISO 12500-3:2009 compliant]

Conditions: When a new element is used, and the flow capacity, inlet pressure, and the amount of solid bodies on the filter inlet side are stable

\*2 The compressed air purity class is indicated based on ISO 8573-1:2010 Compressed air – Part 1: Contaminants and purity classes.

For details on this standard, refer to page 131.

\*3 The compressed air quality class on the inlet side is [ 7 : 9 : 4 ].

## Bowl Assembly/Part Nos.

Bowl material	Drain discharge mechanism	Drain port	Other	Model					
				AF20-D	AF30-D	AF40-D	AF40-06-D	AF50-D	AF60-D
Polycarbonate	Manual	With drain cock	—	C2SF-D	—	—			
		With bowl guard	With bowl guard	C2SF-C-D	C3SF-D	C4SF-D			
		Drain cock with barb fitting	With bowl guard	—	C3SF-W-D	C4SF-W-D			
		With drain guide (without valve function)	—	C2SF□-J-D	—	—			
	Automatic*1 (Auto drain)	Normally closed (N.C.)	—	AD27-D	—	—			
		With bowl guard	With bowl guard	AD27-C-D	AD37□-D	AD47□-D			
Nylon	Manual	With drain cock	—	C2SF-6-A	—	—			
		With bowl guard	With bowl guard	C2SF-6C-A	C3SF-6-A	C4SF-6-A			
		Drain cock with barb fitting	With bowl guard	—	C3SF-6W-A	C4SF-6W-A			
		With drain guide (without valve function)	—	C2SF□-6J-A	—	—			
	Automatic*1 (Auto drain)	With bowl guard	With bowl guard	C2SF□-6CJ-A	C3SF□-6J-A	C4SF□-6J-A			
		Normally closed (N.C.)	—	AD27-6-A	—	—			
		With bowl guard	With bowl guard	AD27-6C-A	AD37□-6-A	AD47□-6-A			
		Normally open (N.O.)	—	AD38□-6-A	—	AD48□-6-A			
		With bowl guard	With bowl guard	AD38□-6-A	AD48□-6-A	AD48□-6-A			
		With level gauge	With level gauge	AD38□-8-A	AD48□-8-A	AD48□-8-A			
Metal	Manual	With drain cock	—	C2SF-2-A	C3SF-2-A	C4SF-2-A			
		With bowl guard	With bowl guard	—	C3LF-8-A	C4LF-8-A			
		With drain guide (without valve function)	—	C2SF□-2J-A	C3SF□-2J-A	C4SF□-2J-A			
		With level gauge	With level gauge	—	C3LF□-8J-A	C4LF□-8J-A			
	Automatic*1 (Auto drain)	Normally closed (N.C.)	—	AD27-2-A	AD37□-2-A	AD47□-2-A			
		With level gauge	With level gauge	—	AD37□-8-A	AD47□-8-A			
		Normally open (N.O.)	—	AD38□-2-A	AD48□-2-A	AD48□-2-A			
		With level gauge	With level gauge	—	AD38□-8-A	AD48□-8-A			

\*1 The bowl assembly comes with a bowl seal.

□ in bowl assembly part numbers indicates a pipe thread type (applicable tubing for auto drain).

No indication is necessary for Rc thread; however, indicate N for NPT thread, and F for G thread. (For auto drain, Nil: ø10, N: ø3/8")

Please contact SMC separately for psi and °F unit display specifications.

## Option/Part Nos.


Optional specifications	Model					
	AF20-D	AF30-D	AF40-D	AF40-06-D	AF50-D	AF60-D
Bracket assembly*1	AF24P-070AS	AF34P-070AS	AF44P-070AS	AF49P-070AS	AF54P-070AS	
Auto drain	Refer to "Bowl Assembly/Part Nos."					

\*1 The assembly consists of a bracket A/B and 2 mounting screws.

## Replacement Parts

Description	Part no.					
	AF20-D	AF30-D	AF40-D	AF40-06-D	AF50-D	AF60-D
Filter element	AF20P-060S	AF30P-060S	AF40P-060S		AF50P-060S	AF60P-060S
Baffle	AF24P-040S	AF34P-040S	AF44P-040S		AF54P-040S	AF64P-040S
Bowl seal	C2SFP-260S	C32FP-260S	C42FP-260S			
Bowl assembly*1, *2	Refer to “Bowl Assembly/Part Nos.”					

\*1 The bowl assembly comes with a bowl seal.




# Air Filter **AF20-D to AF60-D Series**

## Flow Rate Characteristics (Representative values)


**AF20-D**

Rc1/4




**AF30-D**

Rc3/8




**AF40-D**

Rc1/2




**AF40-06-D**

Rc3/4




**AF50-D**

Rc1



**AF60-D**

Rc1



AC

AF + AR + AL

AW + AL

AF + AR

AF + AFM + AR

AW + AFM

Attachments

AF

AFM / AFD

AR


AL

AW

# AF20-D to AF60-D Series

## Working Principle: Float Type Auto Drain

N.O. type: AD38-D, AD48-D



- **When pressure inside the bowl is released:**

When pressure is released from the bowl ①, the piston ⑦ is lowered by the spring ⑥. The sealing action of the seal ⑩ is interrupted, and the outside air flows inside the bowl ① through the housing hole ⑨ and the drain cock ⑪.

Therefore, if there is an accumulation of condensate in the bowl ①, it will drain out through the drain cock.

- **When pressure is applied inside the bowl:**

When pressure is 0.1 MPa or more, the force of the piston ⑦ surpasses the force of the spring ⑥, and the piston goes up.

This pushes seal ⑩ up so that it creates a seal, and the inside of the bowl ①, is shut off from the outside air.


If there is no accumulation of condensate in the bowl ① at this time, the float ② will be pulled down by its own weight, causing the valve ④, which is connected to the lever ③, to seal the valve seat ⑤.

- **When there is an accumulation of condensate in the bowl:**

The float ② rises due to its own buoyancy and the seal at the valve seat ⑤ is interrupted. This allows the pressure inside the bowl ① to enter the chamber ⑧. The result is that the combined pressure inside the chamber ⑧ and the force of the spring ⑥ lowers the piston ⑦. This causes the sealing action of the seal ⑩ to be interrupted, and the accumulated condensate in the bowl ① drains out through the drain cock ⑪.

Turning the drain cock ⑪ manually counterclockwise lowers the piston ⑦, and causes the seal created by the seal ⑩ to be interrupted

N.C. type: AD37-D, AD47-D



- **When pressure inside the bowl is released:**

Even when pressure inside the bowl ① is released, spring ⑥ keeps the piston ⑦ in its upward position.

This keeps the seal created by the seal ⑩ in place; thus, the inside of the bowl ① is shut off from the outside air.

Therefore, even if there is an accumulation of condensate in the bowl ①, it will not drain out.

- **When pressure is applied inside the bowl:**

Even when pressure is applied inside the bowl ①, the combined force of the spring ⑥ and the pressure inside the bowl ① keeps the piston ⑦ in its upward position.

This maintains the seal created by the seal ⑩ in place; thus, the inside of the bowl ① is shut off from the outside air.

If there is no accumulation of condensate in the bowl ① at this time, the float ② will be pulled down by its own weight, causing the valve ④, which is connected to the lever ③, to seal the valve seat ⑤.

- **When there is an accumulation of condensate in the bowl:**


The float ② rises due to its own buoyancy and the seal at the valve seat ⑤ is interrupted. This allows the pressure inside the bowl ① to enter the chamber ⑧.

The result is that the pressure inside the chamber ⑧ surpasses the force of the spring ⑥ and pushes the piston ⑦ downward.

This causes the sealing action of the seal ⑩ to be interrupted and the accumulated condensate in the bowl ① drains out through the drain cock ⑪.

Turning the drain cock ⑪ manually counterclockwise lowers the piston ⑦, and causes the seal created by the seal ⑩ to be interrupted

Compact auto drain N.C. type: AD27-D



- **When pressure inside the bowl is released:**

Even when pressure inside the bowl ① is released, the weight of the float ② causes the valve ④, which is connected to the lever ③, to seal the valve seat ⑤. As a result, the inside of the bowl ① is shut off from the outside air.

Therefore, even if there is an accumulation of condensate in the bowl ①, it will not drain out.

- **When pressure is applied inside the bowl:**

Even when pressure is applied inside the bowl ①, the weight of the float ② and the differential pressure that is applied to the valve ④ cause the valve ④ to seal the valve seat ⑤, and the outside air is shut off from the inside of the bowl ①.







- **When there is an accumulation of condensate in the bowl:**

The float ② rises due to its own buoyancy and the seal at the valve seat ⑤ is interrupted. The condensate inside the bowl ① drains out through the knob ⑥.


Turning the knob ⑥ manually counterclockwise lowers it and causes the sealing action of the valve seat ⑤ to be interrupted, which allows the condensate to drain out.



# Air Filter **AF20-D to AF60-D Series**

## Operating State and Proper Use of Float Type Auto Drain

Auto drain	When pressure is not applied (After exhausting residual pressure)	When pressure is applied		Minimum operating pressure
		Before condensate accumulates	When condensate accumulates	
N.O. Normally open	Condensate discharged (Open) 	Condensate not discharged (Close) 	Condensate discharged (Open) 	<b>0.1 MPa or more</b> AF30-D to AF60-D
N.C. Normally closed	Condensate not discharged (Close) 			<b>0.1 MPa or more</b> AF20-D <b>0.15 MPa or more</b> AF30-D to AF60-D

◆ For both N.O. and N.C., the condensate can be discharged manually by turning the drain cock to the “O” position.



Proper Use		
Compressor	When pressure is not applied (After exhausting residual pressure)	Cold climates
<b>0.75 kW or more</b> 	<b>Condensate not accumulated</b> Do not want to accumulate condensate generated at the inlet side when pressure is not applied.	<b>Want to prevent troubles caused by freezing.</b>
<b>Less than 0.75 kW</b> 	<b>Condensate accumulated</b>	—



Recommended auto drain
N.O.* <sup>1</sup> Normally open
N.C. Normally closed

\*<sup>1</sup> For N.O. (Normally open) type, the condensate discharge passage is open when pressure is not applied. For this reason, the drain port is not closed completely in a compressor with a small supply amount (less than 0.75 kW) and

AC

AF + AR + AL

AW + AL

AF + AR

AF + AFM + AR

AW + AFM

Attachments

AF

AFM / AFD

AR


AL

AW


# AF20-D to AF60-D Series

## Dimensions


### AF20-D



















### AF30-D to AF40-06-D



### AF50-D to AF60-D



# Air Filter **AF20-D to AF60-D Series**

Applicable model	Optional specifications	Semi-standard						
	With auto drain	PC/PA bowl		Metal bowl		Metal bowl with level gauge		With element service indicator
		Drain cock with barb fitting	With drain guide	With drain cock	With drain guide	With drain cock	With drain guide	
<b>AF20-D</b>	 M5 x 0.8		 1/8 Width across flats 14		 1/8 Width across flats 14			 C1
<b>AF30-D to AF60-D</b>	 N.O.: Black N.C.: Gray Thread type/Rc, G: ø10 One-touch fitting Thread type/NPT: ø3/8" One-touch fitting	 Barb fitting applicable tubing: T0604	 1/4 Width across flats 17		 1/4 Width across flats 17		 1/4 Width across flats 17	 C1

Model	Standard specifications										Optional specifications						
											Bracket mount						With auto drain
	P	A	B	C	D	E	G	J	M	N	Q	R	S	T	U	V	B
<b>AF20-D</b>	1/8, 1/4	40	87.6	17.5	21	—	25	21	30	27	22	5.4	8.4	60	2.3	28	104.9
<b>AF30-D</b>	1/4, 3/8	53	115.4	21.5	26.5	30	35	26.5	41	35	25	6.5	13	71	2.3	32	157.1
<b>AF40-D</b>	1/4, 3/8, 1/2	70	147.1	25.5	35.5	38.4	40	35.5	50	52	30	8.5	12.5	88	2.3	39	186.9
<b>AF40-06-D</b>	3/4	75	149.1	27	35.5	38.4	40	35.5	50	52	34	8.5	12.5	88	2.3	43	188.9
<b>AF50-D</b>	3/4, 1	90	220.1	32	45	—	30	45	70	66	40.5	11	13	113	3.2	52.5	259.9
<b>AF60-D</b>	1	95	234.1	32	45	—	30	45	70	66	40.5	11	13	113	3.2	52.5	273.9

Model	Semi-standard specifications							
	PC/PA bowl		Metal bowl		Metal bowl with level gauge		With element service indicator	
	With barb fitting	With drain guide	With drain cock	With drain guide	With drain cock	With drain guide		
	B	B	B	B	B	B	A	C1
<b>AF20-D</b>	—	91.4	87.4	93.9	—	—	40	50.6
<b>AF30-D</b>	123.9	122.2	117.8	122.3	137.8	142.3	53	54.3
<b>AF40-D</b>	155.6	153.9	149.5	154	169.5	174	70	58.3
<b>AF40-06-D</b>	157.6	155.9	151.5	156	171.5	176	—	—
<b>AF50-D</b>	228.6	226.9	222.5	227	242.5	247	90	64.3
<b>AF60-D</b>	242.6	240.9	236.5	241	256.5	261	90*1	64.3

\*1 For the type with an element service indicator, the A dimension differs from that of the standard specification.

AC

AF + AR + AL

AW + AL

AF + AR

AF + AFM + AR

AF + AFM

AW + AFM

Attachments

AF

AFM / AFD

AR

AL

AW



# Air Filter/AF20-D to AF60-D

## Made to Order

Please contact SMC for detailed dimensions, specifications, and lead times.



### ① Long Bowl

Drain capacity is greater than that of standard models.

#### Applicable Models/Drain Capacity

Model	AF20-D	AF30-D	AF40-D	AF40-06-D	AF50-D	AF60-D
Port size	1/8, 1/4	1/4, 3/8	1/4, 3/8, 1/2	3/4	3/4, 1	1
Drain capacity [cm <sup>3</sup> ]	19	43	88			
B dimension [mm]*1	108.1	137.4	167.2	169.2	240.2	254.2


\*1 For polycarbonate bowls. Please contact SMC for other bowl materials.

AF **30** - **03** - **D** - **X64**


① ② ③ ④ ⑤

Long bowl

AF20-D



AF30 to 60-D



#### Semi-standard Symbol Selection

- Select one each for **a** to **d**.
  - When more than one specification is required, indicate in alphanumeric order.
- Example) AF30-F03B-2JR-D-X64

		Symbol	Description	①						
				Body size						
				20	30	40	50	60		
②	Pipe thread type	Nil	Rc	●	●	●	●	●		
		N	NPT	●	●	●	●	●		
		F	G	●	●	●	●	●		
+										
③	Port size	01	1/8	●	—	—	—	—		
		02	1/4	●	●	●	—	—		
		03	3/8	—	●	●	—	—		
		04	1/2	—	—	●	—	—		
		06	3/4	—	—	●	●	—		
		10	1	—	—	—	●	●		
+										
④	Option (Mounting)	Nil	Without mounting option	●	●	●	●	●		
		B*1	With bracket	●	●	●	●	●		
+										
⑤	Semi-standard	a	Bowl*2	Nil	Polycarbonate bowl	●	●	●	●	●
				2	Metal bowl	●	●	●	●	●
				6	Nylon bowl	●	●	●	●	●
				C	With bowl guard	●	—*3	—*3	—*3	—*3
				6C	With bowl guard (Nylon bowl)	●	—*4	—*4	—*4	—*4
		+								
		b	Drain port	Nil	With drain cock	●	●	●	●	●
				J*5	Drain guide 1/8	●	—	—	—	—
					Drain guide 1/4	—	●	●	●	●
				W*6	Drain cock with barb fitting	—	●	●	●	●
		+								
		c	Flow direction	Nil	Flow direction: Left to right	●	●	●	●	●
				R	Flow direction: Right to left	●	●	●	●	●
+										
d	Unit	Nil	Unit on product label: MPa, °C	●	●	●	●	●		
		Z*7	Unit on product label: psi, °F	○*8	○*8	○*8	○*8	○*8		

\*1 Option B is included in the package with the product but does not come assembled. The assembly consists of 2 types of the bracket and 2 mounting screws.

\*2 Refer to chemical data on page 83 for chemical resistance of the bowl.

\*3 A bowl guard is provided as standard equipment (polycarbonate).

\*4 A bowl guard is provided as standard equipment (nylon).

\*5 Without a valve function. The mounting screws are the same as the thread of ②.

\*6 The combination of metal bowl 2 is not available.

\*7 For the pipe thread type: NPT. This product is for overseas use only according to the New Measurement Act. (The SI unit type is provided for use in Japan.)

\*8 ○: For the pipe thread type: NPT only

# Air Filter/*AF20-D to AF60-D*

## Made to Order

Please contact SMC for detailed dimensions, specifications, and lead times.



### ② Clean Series

For details, refer to the Clean Series/Low Particle Generation section of the **Web Catalog**.

**10** - **Standard model no.**

- Clean Series

### ③ Copper, Fluorine and Silicone-free + Low Particle Generation

For details, refer to the Clean Series/Low Particle Generation section of the **Web Catalog**.

**21** - **Standard model no.**

- Copper, fluorine and silicone-free + Low particle generation

AC

AF + AR + AL

AW + AL

AF + AR

AF + AFM + AR

AW + AFM

Attachments

AF

AFM / AFD

AR

AL

AW



## AF-D Series

# Specific Product Precautions

Be sure to read this before handling the products. Refer to the back cover for safety instructions. For F.R.L. units precautions, refer to the “Handling Precautions for SMC Products” and the “Operation Manual” on the SMC website: <https://www.smcworld.com>

### Design / Selection

#### Warning

1. The bowl material of the standard air filter is polycarbonate. Do not use in an environment where they are exposed to or come in contact with organic solvents, chemicals, cutting oil, synthetic oil, alkali, and thread lock solutions.

#### Chemical resistance of polycarbonate or nylon bowl

Type	Chemical name	Application examples	Material	
			Polycarbonate	Nylon
Acid	Hydrochloric acid	Acid washing liquid for metals	△	×
	Sulfuric acid			
	Phosphoric acid			
	Chromic acid			
Alkaline	Sodium hydroxide (Caustic soda)	Degreasing of metals Industrial salts Water-soluble cutting oil	×	○
	Potash			
	Calcium hydroxide (Slack lime)			
	Ammonia water			
	Sodium carbonate			
Inorganic salts	Sodium sulfide	—	×	△
	Potassium nitrate			
	Sodium sulfate			
Chlorine solvents	Carbon tetrachloride	Cleansing liquid for metals Printing ink Dilution	×	△
	Chloroform			
	Ethylene chloride			
	Methylene chloride			
Aromatic series	Benzene	Coatings Dry cleaning	×	△
	Toluene			
	Paint thinner			
Ketone	Acetone	Photographic film Dry cleaning Textile industries	×	×
	Methyl ethyl ketone			
	Cyclohexane			
Alcohol	Ethyl alcohol	Antifreeze Adhesives	△	×
	IPA			
	Methyl alcohol			
Oil	Gasoline	—	×	○
	Kerosene			
Ester	Phthalic acid dimethyl	Synthetic oil Anti-rust additives	×	○
	Phthalic acid diethyl			
	Acetic acid			
Ether	Methyl ether	Brake oil additives	×	○
	Ethyl ether			
Amino	Methyl amino	Cutting oil Brake oil additives Rubber accelerator	×	×
Others	Thread-lock fluid	—	×	△
	Seawater			
	Leak tester			

○: Essentially safe △: Some effects may occur. ×: Effects will occur.

\* When the above factors are present, or there is some doubt, use a metal bowl for safety.

\* The display window material for the semi-standard type with an element service indicator is nylon.

### Maintenance


#### Warning

1. Replace the element every 2 years or when the pressure drop becomes 0.1 MPa, whichever comes first, to prevent damage to the element.

### Mounting / Adjustment

#### Caution

1. When the bowl is installed on the air filter (AF30-D to AF60-D), install them so that the lock button lines up to the groove of the front (or the back) of the body to avoid drop or damage of the bowl.



### Handling

#### Caution

1. The element service indicator (Semi-standard: L) is used to check the pressure differential between the IN and OUT sides. When operating at a flow rate with a pressure differential exceeding 0.025 MPa, the element service indicator may operate even when the element is in its initial state.
2. For models with an element service indicator, adjust the flow rate in the direction that increases the flow rate. If the designated flow rate is exceeded, reset the flow rate to zero and readjust it until the designated flow rate is reached.
3. For models with an element service indicator, as the element becomes more clogged, the indicator will display an increasing level of red. Be sure to replace the element before the level of red reaches the top of the indicator.