


| REV. | ECN | DESCRIPTION | DATE | BY | APP |
|------|-----|--------------------------------|-----------|-------|-----|
| 1 | C | ADDED C06 PRODUCT LABEL TO BOM | 12/5/2012 | J.D.H | DS |
| 2 | F | CHANGED PROOF PRESSURE SPEC | 5/27/2014 | J.D.H | RJB |

| SPECIFICATIONS | |
|--------------------------|---------------------|
| MAXIMUM WORKING PRESSURE | 1.0 MPa (150 psig) |
| PROOF PRESSURE | 1.56 MPa (227 psig) |
| MATERIAL | PLAIN CARBON STEEL |

| 2 | FAPP-T06-A01-DUP01534 | 3/4 NPTF DRIP LEG ASSEMBLY DRAWING | 1 |
|-------------------------------|---|------------------------------------|---|
| 1 | FAPP-T06-C06-DUP01534 | PRODUCT LABEL | 1 |
| ITEM NO | PART NUMBER | DESCRIPTION | QTY |
| UNITS mm |  | SCALE 1:4 | SMC Corporation of America <small>THIS DRAWING CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO SMC CORPORATION OF AMERICA. IT MUST NOT BE REPRODUCED OR DISCLOSED TO OTHERS OR USED IN ANY OTHER WAY, IN PART OR IN WHOLE, EXCEPT AS AUTHORIZED IN WRITING BY SMC CORPORATION OF AMERICA.</small> |
| BY D. SHULER | | DATE 7/15/2011 | |
| CHECKED | | DATE | |
| APPROVED STEVE SPERRY | | DATE 7/22/2011 | |
| CAD FILE FAPP-T06-DUP01534 | | SIZE B | DRAWING/PART No. SHEET 1 OF 1 FAPP-T06-DUP01534 |
| REFERENCE NUMBER: US95225 | | | REVISION 2 |