



REV.	ECN	DESCRIPTION	DATE	BY	APP
1	C	ADDED C06 PRODUCT LABEL TO BOM	12/6/2012	J.D.H	DS
2	F	CHANGED PROOF PRESSURE SPEC	5/27/2014	J.D.H	RJB
3	H	UPDATED TO CURRENT BORDER	3/20/2017	J.D.H	NMB

SPECIFICATIONS	
MAXIMUM WORKING PRESSURE	1.0 MPa (150 psig)
PROOF PRESSURE	1.56 MPa (227 psig)
MATERIAL	PLAIN CARBON STEEL

2	FAPP-T14-A01-DUP01536	1-1/2 NPTF DRIP LEG ASSEMBLY	1
1	FAPP-T14-C06-DUP01536	PRODUCT LABEL	1
ITEM NO	PART NUMBER	DESCRIPTION	QTY

UNITS mm		SCALE 1:5	<b>SMC Corporation of America</b> <small>THIS DRAWING CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO SMC CORPORATION OF AMERICA. IT MUST NOT BE REPRODUCED OR DISCLOSED TO OTHERS OR USED IN ANY OTHER WAY, IN PART OR IN WHOLE, EXCEPT AS AUTHORIZED IN WRITING BY SMC CORPORATION OF AMERICA.</small>	
DRAWN BY D. SHULER		DATE 7/18/2011	DESCRIPTION 1-1/2 NPTF DRIP LEG	
<div>REFER TO PLM BUSINESS PROCESS FOR APPROVALS</div>			DRAWING/PART No. FAPP-T14-DUP01536	REVISION <div>3</div>
CHECKED APPROVED STEVE SPERRY		DATE 7/22/2011	CAD FILE FAPP-T14-DUP01536	SIZE B

CHECKED	DATE
APPROVED	DATE
STEVE SPERRY	7/22/2011

PRINTED DOCUMENTS ARE UNCONTROLLED  
REFER TO PLM FOR CONTROLLED DOCUMENT

REFERENCE NUMBER: US95228