Plug-in Connector Connecting Base


D-sub Connector

Type 10 Side Ported


25A-JSY1000/3000 Series

Internal Pilot


How to Order Manifolds



Side ported




3 Connector type



4 Connector entry direction

2 Type

10



5 Valve stations

F: D-sub connector (25 pins)						
Symbol	Symbol Stations Note					
02 2 stations						
	Image: Second					
12						
02	02 2 stations					
	÷	Specified layout*2 (Up to 16 solenoids available)				
16	16 stations	(Op to 16 solenoids available)				
 *1 Double wiring: 2-position single, double, 3-position, and 4-position valves can be used on all manifold stations. Use of a 2-position single solenoid will result in an 						

- Use of a 2-position single solenoid will result in an unused control signal. If this is not desired, order with a specified layout.
- *2 Specified layout: Indicate the wiring specifications on the manifold specification sheet. (Note that 2-position double, 3-position, and 4-position valves cannot be used where single wiring has been specified.)
- This also includes the number of blanking plates.

6 P, E port entry

U	U side (2 to 10 stations)
D	D side (2 to 10 stations)
В	Both sides (2 to 16 stations)

SUP/EXH block assembly

Nil	Internal pilot
s	Internal pilot,
3	Built-in silencer

* 3/5(E) port is plugged for the built-in silencer type.

8 A, B port size (Metric/One-touch fitting)

Symbol	A, B port	JSY1000	JSY3000

C4		ø4	●	—	
C6	Straight	ø6	•	•	
C8	Stra	ø8	—	•	
CM*1		Straight port, mixed sizes	•	•	- Contraction
P, E port size (One-touch fittings)			ø8	ø10	

*1 Indicate the sizes on the manifold specification sheet in the case of "CM."

* The JSY1000 manifold pitch for C4 is 6.5 mm, and 9 mm for C6. When CM is selected, the manifold pitch is different depending on the selected fitting.

9 Mounting and Option

Symbol	Mounting				
Nil		Direct mounting			
D		DIN rail mounting			
DIN Rail	DIN Rail Option				
Nil	DIN rail mounting (With DIN rail)				
0	DIN rail mounting (Without DIN rail)				
3	For 3 stations				
:	÷	Specify a longer rail than the standard length.			
16	For 16 stations	stanuaru ieriyth.			


Enter the number of stations inside when it is larger than the number of valve stations. (Refer to "DIN Rail Option" shown on the above.)

* Refer to the **Web Catalog** for the fixation of DIN rail mounting type manifold.

* The 25A- series specifications and dimensions are the same as those of the standard model.



How to Order Manifold Assembly



多SMC


Plug-in Connector Connecting Base

Terminal Block Box 🕽

Type 10 Side Ported **25A-JSY1000/3000** Series

Internal Pilot

How to Order Manifolds



- wiring has been specified.)
- *3 This also includes the number of blanking plates.

A, B port size (Metric/One-touch fitting)

Symbol	A, B port		J211000	J213000	
C4	Straight	ø4	•	—	
C6		ø6	•	•	
C8		ø8	—	•	
CM*1		Straight port, mixed sizes	•	•	O
P, E port size (One-touch fittings)		ø8	ø10		

*1 Indicate the sizes on the manifold specification sheet in the case of "CM."

The JSY1000 manifold pitch for C4 is 6.5 mm, and 9 mm for C6. When CM is selected, the manifold pitch is different depending on the selected fitting.

8 Mounting and Option

Symbol	Mounting
Nil	Direct mounting
D	DIN rail mounting

 * Enter the number of stations inside □ when it is larger than the number of valve stations. (Refer to "DIN Rail Option" shown below.)

 Refer to the Web Catalog for the fixation of DIN rail mounting type manifold.

DIN Rail Option

Nil	DIN rail mounting (With DIN rail)					
0	DIN rail	DIN rail mounting (Without DIN rail)				
3	For 3 stations	Specify a longer rail than the standard length.				
	:					
16	For 16 stations	the standard length.				


* The 25A- series specifications and dimensions are the same as those of the standard model.

RoHS





How to Order Manifold Assembly



Plug-in Connector Connecting Base

EX260

Type 10 Side Ported

25A-JSY1000/3000 Series RoHS

05

Δ

6

6

Internal Pilot

How to Order Manifolds

2 Туре

D P, E port entry

6 SUP/EXH block assembly

with water or other liquids.

10

U D

В

Nil

S

type

3

Side ported

U side (2 to 10 stations)

D side (2 to 10 stations)

Both sides (2 to 16 stations)

Internal pilot

Internal pilot, Built-in silencer 3/5(E) port is plugged for the built-in silencer

When the built-in silencer type is used, keep

the exhaust port from coming in direct contact



U Ser	ries
1	JSY1000
3	JSY3000



SI unit (Output polarity, Protocol, Number of outputs, Communication connector)

communication connectory				
Symbol (Output polarity) Positive common Negative common		Protocol	Number of	Communication
(NPN)	(PNP)		outputs	connector
0	*1	Without	SI unit	
QA	QAN	DeviceNet™	32	M12
QB	QBN	Devicemet	16	IVITZ
NA	NAN	PROFIBUS	32	M12
NB	NBN	DP	16	
VA	VAN	CC-Link	32	M12
VB	VBN	CC-LINK	16	
DA	DAN	EtherCAT	32	M12
DB	DBN	Elliercat	16	
FA	FAN	PROFINET	32	M12
FB	FBN	FNOPINET	16	10112
EA	EAN	EtherNet/IP™	32	M12
EB	EBN	Ethernet/IF ····	16	

Without SI unit, the output polarity is decided by the SI unit used. Ensure a match with the common

specification of the valves to be used.

DIN rail cannot be mounted without SI unit.

Symbol		A, B port	JSY1000	JSY3000	
C4	Straight	ø4	•	_	
C6		ø6	•	•	
C8		ø8	—	•	
CM *1		Straight port, mixed sizes	•	•	08
	P, E port size	(One-touch fittings)	ø8	ø10	

A, B port size (Metric/One-touch fitting)

*1 Indicate the sizes on the manifold specification sheet in the case of "CM."

The JSY1000 manifold pitch for C4 is 6.5 mm, and 9 mm for C6. When CM is selected, the manifold pitch is different depending on the selected fitting.

For details about the EX260 Integrated Type (For Input/Output) Serial Transmission System, refer to the Web Catalog and the Operation Manual. For details about part numbers of SI units to be mounted, refer to the Web Catalog. Please download the Operation Manual via SMC website, https://www.smcworld.com

4 Valve stations

In the case of the 32-output SI unit

C6

Symbol	Stations	Note			
02	2 stations				
:	÷	Double wiring*1			
16 16 stations					
In the case of the 16-output SI unit					

Symbol	Stations	Note				
02	2 stations					
:	÷	Double wiring ^{*1}				
08	8 stations					
02	2 stations	0				
:	:	Specified layout*2 (Up to 16 solenoids available)				
16	16 stations					

- *1 Double wiring: 2-position single, double, 3-position, and 4-position valves can be used on all manifold stations. Use of a 2-position single solenoid will result in an unused control signal. If this is not desired, order with a specified layout.
- *2 Specified layout: Indicate the wiring specifications on the manifold specification sheet. (Note that 2-position double, 3-position, and 4-position valves cannot be used where single wiring has been specified.)
- * This also includes the number of blanking plates.
- For the product without the SI unit (S0), note the maximum number of solenoids of the SI unit that will be mounted. If the lavout is specified, indicate it on the manifold specification sheet.

Mounting and Option

Symbol	Mounting
Nil	Direct mounting
D	DIN rail mounting

- ∗ Enter the number of stations inside □ when it is larger than the number of valve stations. (Refer to "DIN Rail Option" shown below.)
- Refer to the Web Catalog for the fixation of DIN rail mounting type manifold.
- DIN rail mounting (DD) is not available for the product without the SI unit (S0).

DIN Rail Option


Nil	DIN rail mounting (With DIN rail)				
0	DIN rail mounting (Without DIN rail)				
3	For 3 stations	Specify a longer rail than			
:	÷				
16	For 16 stations				

Befer to L3 of the dimensions for the DIN rail * length and order separately. (Refer to the Web Catalog for the DIN rail part number.)

* The 25A- series specifications and dimensions are the same as those of the standard model.



How to Order Manifold Assembly



Plug-in Connector Connecting Base


EX120

25A-JSY1000/3000 Series

Internal Pilot


Type 10 Side Ported

How to Order Manifolds



secondary batteries

1 Series				
1	JSY1000			
3	JSY3000			



3 SI unit

0	Without SI unit	
Q	DeviceNet [™] (Positive common NPN)	
V CC-Link (Positive common NPN)		

* Ensure a match with the common specification of the valve to be used.

4 Valve stations

Symbol	Stations	Note				
02	2 stations					
:	÷	Double wiring*1				
08	8 stations					
02	2 stations	Creatified laws #*?				
:	÷	Specified layout*2 (Up to 16 solenoids available)				
16	16 stations	(Op to 10 soleriolds available)				

- *1 Double wiring: 2-position single, double, 3-position, and 4-position valves can be used on all manifold stations. Use of a 2-position single solenoid will result in an unused control signal. If this is not desired, order with a specified layout.
- *2 Specified layout: Indicate the wiring specifications on the manifold specification sheet. (Note that 2-position double, 3-position, and 4-position valves cannot be used where single wiring has been specified.)
- This also includes the number of blanking plates.

8 Mounting and Option

Symbol	Mounting			
Nil	Direct mounting			
D	DIN rail mounting			

- * Enter the number of stations inside □ when it is larger than the number of valve stations. (Refer to "DIN Rail Option" shown below.)
- Refer to the Web Catalog for the fixation of DIN rail mounting type manifold.

DIN Rail Option

Nil	DIN rail mounting (With DIN rail)				
0	0 DIN rail mounting (Without DIN ra				
3	For 3 stations				
:	:	Specify a longer rail than the standard length.			
16	For 16 stations				

 If the DIN rail must be mounted without an SI unit, select D0. Refer to L3 of the dimensions for the DIN rail length and order separately. (Refer to the Web Catalog for the DIN rail part number.)

5 P, E port entry

U	U side (2 to 10 stations)					
D D side (2 to 10 stations)						
B Both sides (2 to 16 stations)						

6 SUP/EXH block

Nil	Internal pilot			
S	Internal pilot, Built-in silencer			

3/5(E) port is plugged for the built-in silencer type.

A, B port size (Metric/One-touch fitting)

<u> </u>							
Symbol		A, B port	JSY1000	JSY3000			
C4		ø4	•	—			
C6	Straight	ø6	•	•			
C8	Straight	ø8	—	•			
CM *1		Straight port, mixed sizes	•	•	08		
	P, E port size	(One-touch fittings)	ø8	ø10			

*1 Indicate the sizes on the manifold specification sheet in the case of "CM."


* The JSY1000 manifold pitch for C4 is 6.5 mm, and 9 mm for C6. When CM is selected, the manifold pitch is different depending on the selected fitting.

* The 25A- series specifications and dimensions are the same as those of the standard model.

Click here for details.

For details about the EX120 Integrated Type (For Output) Serial Transmission System, refer to the **Web Catalog** and the Operation Manual. For details about part numbers of SI units to be mounted, refer to the **Web Catalog**. Please download the Operation Manual via SMC website, https://www.smcworld.com

How to Order Manifold Assembly




多SMC

25A-JSY1000/3000 Series Manifold Options


Blanking plate assembly

(With two mounting screws)

Used when valve additions are expected or for maintenance. A structure is in place on the blanking plate to prevent the mounting screws from sliding.



How to Order Blanking Plate Assembly




SI Unit Part Nos.

Description	SI unit part no.	Note
	EX260-SPR1-X117	PROFIBUS DP M12 connector, 32 outputs, Negative common (PNP)
	EX260-SPR2-X117	PROFIBUS DP M12 connector, 32 outputs, Positive common (NPN)
	EX260-SPR3-X117	PROFIBUS DP M12 connector, 16 outputs, Negative common (PNP)
	EX260-SPR4-X117	PROFIBUS DP M12 connector, 16 outputs, Positive common (NPN)
	EX260-SDN1-X117	DeviceNet [™] M12 connector, 32 outputs, Negative common (PNP)
	EX260-SDN2-X117	DeviceNet [™] M12 connector, 32 outputs, Positive common (NPN)
	EX260-SDN3-X117	DeviceNet [™] M12 connector, 16 outputs, Negative common (PNP)
	EX260-SDN4-X117	DeviceNet [™] M12 connector, 16 outputs, Positive common (NPN)
	EX260-SEC1-X117	EtherCAT M12 connector, 32 outputs, Negative common (PNP)
	EX260-SEC2-X117	EtherCAT M12 connector, 32 outputs, Positive common (NPN)
	EX260-SEC3-X117	EtherCAT M12 connector, 16 outputs, Negative common (PNP)
EX260 SI unit	EX260-SEC4-X117	EtherCAT M12 connector, 16 outputs, Positive common (NPN)
	EX260-SMJ1-X117	CC-Link M12 connector, 32 outputs, Negative common (PNP)
	EX260-SMJ2-X117	CC-Link M12 connector, 32 outputs, Positive common (NPN)
	EX260-SMJ3-X117	CC-Link M12 connector, 16 outputs, Negative common (PNP)
	EX260-SMJ4-X117	CC-Link M12 connector, 16 outputs, Positive common (NPN)
	EX260-SPN1-X117	PROFINET M12 connector, 32 outputs, Negative common (PNP)
	EX260-SPN2-X117	PROFINET M12 connector, 32 outputs, Positive common (NPN)
	EX260-SPN3-X117	PROFINET M12 connector, 16 outputs, Negative common (PNP)
	EX260-SPN4-X117	PROFINET M12 connector, 16 outputs, Positive common (NPN)
	EX260-SEN1-X117	EtherNet/IP™ M12 connector, 32 outputs, Negative common (PNP)
	EX260-SEN2-X117	EtherNet/IP™ M12 connector, 32 outputs, Positive common (NPN)
	EX260-SEN3-X117	EtherNet/IP™ M12 connector, 16 outputs, Negative common (PNP)
	EX260-SEN4-X117	EtherNet/IP™ M12 connector, 16 outputs, Positive common (NPN)
EX120 SI unit	EX120-SMJ1-X220	CC-Link (Terminal block, 16 outputs, Positive common (NPN))
	EX120-SDN1-X220	DeviceNet TM (Terminal block, 16 outputs, Positive common (NPN))

One-touch Fittings Part Nos.

	Series	25A-JSY1000		25A-JSY3000	Note	
Port size		6.5 mm pitch	9 mm pitch	254-5515000	NOLE	
	ø4	25A-KQSY10-C4-X1336	—	—		
A, B port	ø6	—	25A-KQSY11-C6-X1336	25A-KQSY30-C6		
	ø8	_		25A-KQSY30-C8-X1336	The part number is for 1 piece. (Sales unit: 10 pcs.)	
B E port	ø8	25A-KQSY30-C8-X1336				
P, E port	ø10	-		25A-KQSY31-C10-X1336		

How to Order Individual SUP/EXH Spacer Assembly



Manifold Options 25A-JSY1000/3000 Series


Manifold Parts Nos./For the 25A-JJ5SY1-10, 25A-JJ5SY3-10

Description	25A-J\$	25A-JSY3000	
Description	6.5 mm pitch	9 mm pitch	25A-J513000
Tie-rod for additional stations	JSY11M-49P-4-1-A (6.5 mm pitch)	JSY11M-49P-3-1-A (9 mm pitch)	JSY31M-49P-2-1-A (11.5 mm pitch)
Tie-rod	JSY11M-49P-4-⊡-A (6.5 mm pitch)	JSY11M-49P-3-⊡-A (9 mm pitch)	JSY31M-49P-2-□-A (11.5 mm pitch)
Valve mounting screw	25 A-JSY (M1.4	25A-JSY31V-23-1A (M2 x 25)	
Clamp bracket (for connector connecting base)	25A-JSY11M-15P-1A 25A-JSY11M-15P-2A	25A-SY30M-15-1A	

Table. 25A-JSY1000 series clamp bracket

	Wiring (JSY1000 series)	25A-JSY11M-15P-1A	25A-JSY11M-15P-2A
F	D-sub connector	•	_
Т	Terminal block box	—	\bullet
S	EX260	•	—
S3	EX120	•	_

Manifold Parts Nos.



25A-JSY1000/3000 Series

Manifold Parts Nos.

B SUP/EXH end block assem	ıbly				
25A-JSY31M-3	P-1A	-C10			
• Series			• Mour	nting	g
1 JSY1000			Nil		Direct mounting
3 JSY3000			D0	DI	N rail mounting (Without DIN rail)
			D00*1	DII	N rail mounting (Without DIN rail)
			*1 Part	num	ber only for the 25A-JSY1000
	ilencer type		Part	num	ber is different depending on the wiring. Table 1.
Symbol Pilot type	Built-in silencer		Table 1. JSY1000 series DIN rail mounting		
Nil	_		Syn	nbol	Wiring
S •	●		D	00	D-sub connector (F type) EX260 (S □□ type) EX120 (S3 type)
P, E port siz	e (One-touch f	<u> </u>	D	00	Terminal block box (T type)
Symbol P, E port	JSY1000	JSY3000			

•

\mathbf{r}	00	~ ~	h.		ke	Ŀ.
ີ	dII	ID.	D	du	ке	L

C8

C10

00

Series		Part no.	
JSY1000	For D0	25A-JSY11M-15P-1A	
3511000	For D00	25A-JSY11M-15P-2A	
JSY3000		25A-SY30M-15-1A	

ø8 One-touch fitting

ø10 One-touch fitting

Plug

•

•


Cover, Silencer cover for SUP/EXH (end) block assembly




Cover (Internal pilot)




Silencer cover (Internal pilot, Built-in silencer)




Manifold Parts Nos.



For the terminal block box or EX260




Symbol	P, E port	JSY1000	JSY3000
C8	ø8 One-touch fitting	•	_
C10	ø10 One-touch fitting	—	
00	Plug	•	



* Refer to page 14-9-2 for part number of the clamp bracket.

25A-JSY1000/3000 Series

How to Order Pilot Valves



Pilot cover

25A-SY30V-25AS (For 25A-JSY3000)


* The pilot valve of the 25A-JSY1000 series cannot be replaced.

Type 40 Side Ported

Non Plug-in Metal Base 25A-JSY100/3000 Series


Internal Pilot

How to Order Manifolds




Click here for details.

How to Order Manifold Assembly



Non Plug-in Metal Base 25A-JSY1000/3000 Series




25A-JSY1000/3000 Series Manifold Options


Blanking plate assembly

(With two mounting screws)

Used when valve additions are expected or for maintenance. A structure is in place on the blanking plate to prevent the mounting screws from sliding.



How to Order Blanking Plate Assembly




Valve Mounting Screw Part No.

Description	Par	Nete	
Description	25A-JJ5SY1	25A-JJ5SY3	Note
Round head combination screw	25A-JSY11V-23-4A	25A-JSY31V-23-4A	Part numbers shown on the left are for 10 valves. (20 pcs.)


One-touch Fittings Part Nos.

	Port size		25A-JSY1000	25A-JSY3000
		ø4 One-touch fitting (Straight type)	25A-KQSY10-C4-X1336	—
A, B port	Metric size	ø6 One-touch fitting (Straight type)	25A-KQSY11-C6-X1336	25A-KQSY30-C6
		ø8 One-touch fitting (Straight type)	—	25A-KQSY30-C8-X1336

How to Order Individual SUP/EXH Spacer Assembly



How to Order Pilot Valves




* For the 25A-JSY1000, the pilot valve is the same as that of the standard model.





How to Order Manifold



Series compatible with secondary batteries

1 Series

5 SY5000


2 Туре

10	Side ported
11	Bottom ported


3 Connector type



Connector entry direction



5 Valve stations



*2 Specified layout: Indicate the wiring specifications on the manifold specification sheet. (Note that 2-position double, 3-position, and 4-position valves cannot be used where single wiring has been specified.)

 This also includes the number of the blanking plate assembly.

U	U side (2 to 10 stations)
D	D side (2 to 10 stations)
В	Both sides (2 to 24 stations)

0	SUP/EXH	block	assembly
---	---------	-------	----------

Nil	Internal pilot
s	Internal pilot,
3	Built-in silencer

* 3/5(E) port is plugged for the built-in silencer type.

8 A, B port size (Metric)

Symbol		A, B port	Type 10/ Side ported SY5000	Type 11/ Bottom ported SY5000	
C 4	÷	ø4 One-touch fitting	•	•	
C 6	igh	ø6 One-touch fitting		•	
C8	Stra	ø6 One-touch fitting ø8 One-touch fitting			
CM *1	0	Straight port, mixed sizes			A SUSSEE
P, E	ро	rt size (One-touch fittings)	ø10	ø10	

*1 Indicate the sizes on the manifold specification sheet in the case of "CM."

* The direction of P, E port fittings is the same as for the A, B port.

9 Mounting

	Symbol	Mounting	DIN rail option		
D□ DIN rail mounting 0 Will Div blacker (Whild Div rail 3 For 3 stations Specify a longer rail ⋮ ⋮ than the total length			Nil	Stanc	lard length
DIN rail mounting	Nil	Direct mounting	0		
DIN rail mounting			3	For 3 stations	Specify a longer rail
24 For 04 stations of specified stations	D□	DIN rail mounting	:	:	than the total length
24 For 24 stations of specified stations		2	24	For 24 stations	of specified stations.


* Enter the number of stations inside □. (Refer to "DIN Rail Option" above.)

* Only direct mounting is available for Type 11 (Bottom ported).

* The 25A- series specifications and dimensions are the same as those of the standard model.




Plug-in Connector Connecting Base D-sub Connector 25A-SY5000 Series




Type 12
op Ported Plug-in Connector Connecting Base Use Connector 25A-SY5000 Series


How to Order Manifold




with secondary batteries



2 Connector type



3 Connector entry direction



4 Valve stations

F: D-sub connector (25 pins)				
Symbol	Stations	Note		
02	2 stations			
:	:	Double wiring*1		
12	12 stations			
02	2 stations	Specified layout*2		
:	:	Specified layout*2 (Available up to		
24	24 stations	`24 solenoids)		

*1 Double wiring: 2-position single, double, 3-position, and 4-position valves can be used on all manifold stations.

Use of a 2-position single solenoid will result in an unused control signal. If this is not desired, order

with a specified layout.

- *2 Specified layout: Indicate the wiring specifications on the manifold specification sheet. (Note that 2-position double, 3-position, and 4-position valves cannot be used where single wiring has been specified.)
- This also includes the number of the blanking plate assembly.

5 P, E port entry

• ••,	<u> </u>	
U *1	U side (2 to 10 stations)	
D *1	D side (2 to 10 stations)	
В	Both sides (2 to 24 stations)	

*1 G For type "S," supply/exhaust block assembly with built-in silencer, choose "U" or "D" for P port entry.

6 SUP/EXH block assembly

Nil	Internal pilot	
S	Internal pilot, Built-in silencer	

* For built-in silencer type, P and E ports are available on U and D sides. 3/5(E) port is plugged. The silencer exhaust port is located on the opposite side of P, E port entry. (Example: When the P, E port entry is D side, the silencer exhaust port is U side.)


Mounting

Nil	Direct mounting		
D	DIN rail mounting (With DIN rail)		
D0	DIN rail m	ounting (Without DIN rail)	
D3	For 3 stations		
:	:	Specify a longer rail than th standard length.	
D24	For 24 stations	standard length.	

* The 25A- series specifications and dimensions are the same as those of the standard model.




Plug-in Connector Connecting Base D-sub Connector 25A-SY5000 Series





How to Order Manifold



Series compatible with secondary batteries

1 Se	ries
5	SY5000

4 P, E port entry

U	U side (2 to 10 stations)
D	D side (2 to 10 stations)
В	Both sides (2 to 20 stations)

SUP/EXH block assembly

- Nil Internal pilot
- S Internal pilot, Built-in silencer
 3/5(E) port is plugged for the built-in
 - 3/5(E) port is plugged for the built-in silencer type.
- When the built-in silencer type is used, keep the exhaust port from coming in direct contact with water or other liquids.

Mounting

Symbol	Mounting
Nil	Direct mounting
D	DIN rail mounting

- Enter the number of stations inside \Box . (Refer to "DIN Rail Option" below.)
- Only direct mounting is available for Type 11 (Bottom ported).

DIN rail option

Nil	Standard length	
0	With DIN bracket (Without DIN rail)	
3	For 3 stations	Specify a longer rail
÷	:	than the total length of
24	For 24 stations	specified stations.

6 A, B port size (Metric)

Symbol	A, B port		Type 10/ Side ported	Type 11/ Bottom ported	
			SY5000	SY5000	
C4	t	ø4 One-touch fitting			
C6	ຼອົ ø6 One-touch fitting			•	
C8	ø8 One-touch fitting				S. S. S.
CM*1	0)	Straight port, mixed sizes		•	A STATE
P, E port size (One-touch fittings)		ø10	ø10		

*1 Indicate the sizes on the manifold specification sheet in the case of "CM."

* The direction of P, E port fittings is the same as for the A, B port.

* The 25A- series specifications and dimensions are the same as those of the standard model.

Click here for details.


<u> </u>	P •
10	Side ported
11	Bottom ported

Over the stations

_	-	
Symbol	Stations	Note
02	2 stations	
:	:	Double wiring*1
10	10 stations	_
02	2 stations	Specified layout*2
:	:	(Available up to 20 solenoids)
20	20 stations	

- *1 Double wiring: 2-position single, double, 3-position, and 4-position valves can be used on all manifold stations.
 Use of a 2-position single solenoid will result in an unused control signal. If this is not desired, order with a specified layout.
- *2 Specified layout: Indicate the wiring specifications on the manifold specification sheet. (Note that 2-position double, 3-position, and 4-position valves cannot be used where single wiring has been specified.)
- This also includes the number of the blanking plate assembly.

Plug-in Connector Connecting Base Terminal Block Box 25A-SY5000 Series



Plug-in Connector Connecting Base Terminal Block Box (E IN) 25A-SY5000 Series (RoHS)

Type 12 Top Ported

How to Order Manifold



Series compatible with secondary batteries

1 Se	ries
5	SY5000

9 P, E port entry

<u> </u>		
U *1	U side (2 to 10 stations)	
D *1	D side (2 to 10 stations)	
В	Both sides (2 to 20 stations)	

*1 ④ For type "S," supply/exhaust block assembly with built-in silencer, choose "U" or "D" for P port entry.

2 Valve stations

-	T GI T	o otationo
Symbol	Stations	Note
02	2 stations	
:		Double wiring*1
10	10 stations	_
02	2 stations	Specified lavout*2
:	:	Specified layout*2
20	20 stations	(Available up to 20 solenoids)

 *1 Double wiring: 2-position single, double, 3-position, and 4-position valves can be used on all manifold stations.
 Use of a 2-position single solenoid will result in an unused control signal. If

this is not desired, order with a specified layout.*2 Specified layout: Indicate the wiring

- *2 Specified layout: Indicate the wiring specifications on the manifold specification sheet. (Note that 2-position double, 3-position, and 4-position valves cannot be used where single wiring has been specified.)
- * This also includes the number of the blanking plate assembly.

4 SUP/EXH block assembly

Nil	Internal pilot
S	Internal pilot, Built-in silencer

For built-in silencer type, P and E ports are available on U and D sides. 3/5(E) port is plugged. The silencer exhaust port is located on the opposite side of P, E port entry.

(Example: When the P, E port entry is D side, the silencer exhaust port is U side.)

When the built-in silencer type is used, keep the exhaust port from coming in direct contact with water or other liquids.


5 Mounting

•			
Nil	Direct mounting		
D	DIN rail mounting (With DIN rail)		
D0	DIN rail mounting (Without DIN rail)		
D3	For 3 stations	Specify a longer rail	
:	: than the standard		
D20	For 20 stations length.		

* The 25A- series specifications and dimensions are the same as those of the standard model.


Click here for details.

Plug-in Connector Connecting Base Terminal Block Box 25A-SY5000 Series





How to Order Manifold



Series compatible with secondary batteries



3 Number of cores

(Lead wire)	
L1	34 cores
L2	17 cores
L3	9 cores

0	Туре
----------	------

10	Side ported
11	Bottom ported

4 Lead wire length

1	0.6 m
2	1.5 m
3	3 m

5 Valve stations

(L1□)			(L3□)		
Symbol	Stations	Note	Symbol	Stations	Note
02	2 stations		02	2 stations	
:	:	Double wiring*1	:	:	Double wiring*1
16	16 stations		04	4 stations	
02	2 stations	Specified layout*2	02	2 stations	Specified layout*2
÷	:	Available up to	:	:	Available up to
24	24 stations	32 solenoids)	08	8 stations	8 solenoids)

1	1 0		۱ì
	. /		. 1
L		-	

Symbol	Stations	Note	
02	2 stations		
:	:	Double wiring*1	
08	8 stations		
02	2 stations	Specified layout*2	
:	:	Available up to	
16	16 stations	16 solenoids)	

- *1 Double wiring: 2-position single, double, 3-position, and 4-position valves can be used on all manifold stations. Use of a 2-position single solenoid will result in an unused control signal. If this is not desired, order with a specified layout.
- *2 Specified layout: Indicate the wiring specifications on the manifold specification sheet. (Note that 2-position double, 3-position, and 4-position valves cannot be used where single wiring has been specified.)
- * This also includes the number of the blanking plate assembly.

6 P, E port entry

U U side (2 to 10 stations)		
D D side (2 to 10 stations)		
В	Both sides (2 to 24 stations)	

SUP/EXH block assembly

<u> </u>		
Nil	Internal pilot	
S	Internal pilot, Built-in silencer	

- * 3/5(E) port is plugged for the built-in silencer type.
- When the built-in silencer type is used, keep the exhaust port from coming in direct contact with water or other liquids.

3 A, B port size (Metric)

Symbol		A, B port	Type 10/ Side ported SY5000	Type 11/ Bottom ported SY5000	
C4		ø4 One-touch fitting	•		
C6	ig	ø6 One-touch fitting			
C8	itra	ø6 One-touch fitting ø8 One-touch fitting			
CM *1	0	Straight port, mixed sizes			Salar Salar
Ρ, Ε	P, E port size (One-touch fittings)		ø10	ø10	

*1 Indicate the sizes on the manifold specification sheet in the case of "CM."

* The direction of P, E port fittings is the same as for the A, B port.

9 Mounting

Symbol	Mounting		
Nil	Direct mounting		
D	DIN rail mounting		

* Enter the number of stations inside
. (Refer to "DIN Rail Option" below.)


* Only direct mounting is available for Type 11 (Bottom ported). **DIN rail option**

Nil	Standard length		
0	With DIN bracket (Without DIN rail)		
3	For 3 stations Specify a longer rail than		
1		the total length of specified	
24	For 24 stations stations.		

* The 25A- series specifications and dimensions are the same as those of the standard model.




Plug-in Connector Connecting Base Lead Wire 25A-SY5000 Series



Plug-in Connector Connecting Base Lead Wire (E CALS 25A-SY5000 Series RoHS

How to Order Manifold



 Series compatible with secondary batteries

Series

5	SY5000

ype 12 op Ported

2 Number of cores

(Lead wire)		
L1	34 cores	
L2	17 cores	
L3	9 cores	

3 Lead wire length		
1	0.6 m	
2	1.5 m	
3	3 m	

4 Valve stations

(L1□) (L3□) Symbol Stations Note Symbol Stations Note 02 2 stations 02 2 stations : Double wiring*1 Double wiring*1 ÷ 16 I6 stations 04 4 stations 02 2 stations Specified layout*2 02 2 stations Specified layout*2 Available up to Available up to 32 solenoids) 8 solenoids) 24 stations 08 8 stations (L2□) Symbol Stations Note 02 2 stations ÷ Double wiring*1 ÷ 08 8 stations 02 2 stations Specified layout*2 (Available up to ÷ 16 solenoids) 16 16 stations

- *1 Double wiring: 2-position single, double, 3-position, and 4-position valves can be used on all manifold stations. Use of a 2-position single solenoid will result in an unused control signal. If this is not desired, order with a specified layout.
- *2 Specified layout: Indicate the wiring specifications on the manifold specification sheet. (Note that 2-position double, 3-position, and 4-position valves cannot be used where single wiring has been specified.)
- * This also includes the number of the blanking plate assembly.

9 P, E port entry

U *1	U side (2 to 10 stations)			
D *1	D side (2 to 10 stations)			
В	Both sides (2 to 24 stations)			

*1 **G** For type "S," supply/exhaust block assembly with built-in silencer, choose "U" or "D" for P port entry.

6 SUP/EXH block assembly

Nil	Internal pilot
0	


- S Internal pilot, Built-in silencer
- * For built-in silencer type, P and E ports are available on U and D sides. 3/5(E) port is plugged. The silencer exhaust port is located on the opposite side of P, E port entry. (Example: When the P, E port entry is D side, the silencer exhaust port is U side.)
- * When the built-in silencer type is used, keep the exhaust port from coming in direct contact with water or other liquids.

Mounting

Nil	Direct mounting		
D	DIN rail mounting (With DIN rail)		
D0	DIN rail mounting (Without DIN rail)		
D3	For 3 stations	Specify a longer rail	
	: than the standard		
D24	For 24 stations length.		


The 25A- series specifications and dimensions are the same as those of the standard model.

Plug-in Connector Connecting Base Lead Wire 25A-SY5000 Series



Type 10 Side Ported Type 11 Bottom Ported Plug-in Connector Connecting Base (EX260 **EX260 C EX260 C C EXEXC C EXC C E C E**

How to Order Manifold



Series compatible with secondary batteries

1 Series		
5	SY5000	

2 Туре		
10	Side ported	
11	Bottom ported	

SI unit specifications

Symbol	Protocol	Number of outputs	Communication connector
0	Wi	thout SI u	nit
QA	DeviceNet™	32	
QB	Devicenter	16	
NA	PROFIBUS	32	
NB	DP	16	
VA	CC-Link	32	
VB		16	M12
DA	EtherCAT	32	IVITZ
DB	EllerCAT	16	
FA	PROFINET	32	
FB	FNOPINET	16	
EA	EtherNet/IP™	32	
EB	Eulenvel/IP ····	16	

For SI unit part number, refer to page 35. DIN rail cannot be mounted without SI unit.

4 SI unit output polarity

Nil	Positive common	
Ν	Negative common	

- * Ensure a match with the common specifications of the value to be used.
- * Without SI unit, the symbol is nil.

5 Valve stations

-					
_		se of the 32-output SI unit			
Symbol	Stations	Note			
02	2 stations	Double wiring*1			
:	:				
16	16 stations				
02	2 stations	Specified layout*2 (Available up to 32 solenoids)			
:	:				
24	24 stations				

In the case of the 16-output SI unit

Symbol	Stations	Note		
02	2 stations			
÷	:	Double wiring*1		
08	8 stations			
02	2 stations			
:		Specified layout*2 (Available up to 16 solenoids)		
16	16 stations	(Available up to 16 soleholds		

*1 Double wiring: 2-position single, double, 3-position, and 4-position valves can be used on all manifold stations. Use of a 2-position single solenoid will

Use of a 2-position single solenoid will result in an unused control signal. If this is not desired, order with a specified layout.

- *2 Specified layout: Indicate the wiring specifications on the manifold specification sheet. (Note that 2-position double, 3-position, and 4-position valves cannot be used where single wiring has been specified.)
- This also includes the number of the blanking plate assembly.
 For the model without the SI unit (S0).
- For the model without the SI unit (S0), note the maximum number of solenoids of the SI unit that will be mounted. If the layout is specified, indicate it on the manifold specification sheet.

6 P, E port entry

U	U side (2 to 10 stations)		
D	D side (2 to 10 stations)		
В	Both sides (2 to 24 stations)		

SUP/EXH block assembly

- NilInternal pilotSInternal pilot, Built-in silencer
- 3/5(E) port is plugged for the built-in silencer type.
- When the built-in silencer type is used, keep the exhaust port from coming in direct contact with water or other liquids.

9 Mounting

Symbol	Mounting	
Nil	Direct mounting	
D	DIN rail mounting	

- Enter the number of stations inside □. (Refer to "DIN Rail Option" below.)
- Only direct mounting is available for Type "11" (Bottom ported).

DIN rail option

Nil	Direct mounting		
0	With DIN bracket (Without DIN rail)		
3	For 3 stations Specify a longer rail		
:	: than the total length		
24	For 24 stations of specified stations.		

* When it is necessary to mount a DIN rail without an SI unit, select "D0" and order DIN rail length separately, referring to L3 in the dimensions.

- 8 A, B port size (Metric) Type 10/ Type 11/ Side ported Bottom ported Symbol A, B port SY5000 SY5000 ø4 One-touch fitting C4 • ල් ø6 One-touch fitting C6 ø8 One-touch fitting **C8** • Straight port, mixed sizes CM*1 P, E port size (One-touch fittings) ø10 ø10
- *1 Indicate the sizes on the manifold specification sheet in the case of "CM."

* The 25A- series specifications and dimensions are the same as those of the standard model.


Click here for details.

For details about the EX260 Integrated-type (For Output) Serial Transmission System, refer to the Web Catalog and the Operation Manual. For details about part numbers of SI units to be mounted, refer to page 35 in this catalog. Please download the Operation Manual via our website, https://www.smcworld.com

® 27




Plug-in Connector Connecting Base 25A-SY5000 Series



Plug-in Connector Connecting Base EX260 (C State of Connecting Base 25A-SY5000 Series (RoHS)

How to Order Manifold



Series compatible with secondary batteries

1 Series		ries
	5	SY5000

O SI unit specifications

ype 12 op Ported

Symbol	Protocol		Communication
Cymbol	11010001	outputs	connector
0	W	ithout SI u	nit
QA	DeviceNet™	32	
QB	Devicemet	16	
NA	PROFIBUS	32	
NB	DP	16	
VA	CC-Link	32	
VB	CC-LINK	16	M12
DA	EtherCAT	32	IVITZ
DB		16	
FA	PROFINET	32	
FB	PROFINET	16	
EA	EtherNet/IP™	32	
EB	Emennet/IP	16	

For SI unit part number, refer to page 35. DIN rail cannot be mounted without SI unit.

SI unit output polarity

Nil Positive common (NPN)		
N	Negative common (PNP)	
_		

 Ensure a match with the common specifications of the value to be used.
 Without SI upit the symbol is pill

Without SI unit, the symbol is nil.

4 Valve stations

T valve stations				
In th	ie cas	se of the 32-output SI unit		
Symbol	Stations	Note		
02	2 stations			
:	:	Double wiring*1		
16	16 stations			
02	2 stations	Creating loveut*2		
:	:	Specified layout*2 (Available up to 32 solenoids)		
24	24 stations			

In the case of the 16-output SI unit

	ine ca	se of the to-output of unit
Symb	ol Stations	Note
02	2 2 stations	
:	1	Double wiring*1
30	8 stations	
02	2 2 stations	
:	1	Specified layout*2
16	16 stations	(Available up to 16 solenoids)

*1 Double wiring: 2-position single, double, 3-position, and 4-position valves can be used on all manifold stations.

Use of a 2-position single solenoid will result in an unused control signal. If this is not desired, order with a specified layout.

- *2 Specified layout: Indicate the wiring specifications on the manifold specification sheet.
 (Note that 2-position double, 3-position, and 4-position valves cannot be used where single wiring has been specified.)
- This also includes the number of the blanking plate assembly.
- For the model without the SI unit (S0), note the maximum number of solenoids of the SI unit that will be mounted. If the layout is specified, indicate it on the manifold specification sheet.

9 P, E port entry

\mathbf{v} ,	
U *1	U side (2 to 10 stations)
D *1	D side (2 to 10 stations)
В	Both sides (2 to 24 stations)

*1 G For type "S," supply/exhaust block assembly with built-in silencer, choose "U" or "D" for P port entry.

6 SUP/EXH block assembly

Nil	Internal pilot	
S	Internal pilot, Built-in silencer	

- * For built-in silencer type, P and E ports are available on U and D sides. 3/5(E) port is plugged. The silencer exhaust port is located on the opposite side of P, E port entry. (Example: When the P, E port entry is D side, the silencer exhaust port is U side.)
- When the built-in silencer type is used, keep the exhaust port from coming in direct contact with water or other liquids.

Mounting

Nil	Direct mounting		
D	DIN rail mounting (With DIN rail)		
D0	DIN rail mounting (Without DIN rail)		
D3	For 3 stations Specify a longe		
:	:	rail than the	
D24	For 24 stations	standard length.	

When it is necessary to mount a DIN rail without an SI unit, select "D0" and order DIN rail length separately, referring to L3 in the dimensions.


 The 25A- series specifications and dimensions are the same as those of the standard model.

Click here for details.

For details about the EX260 Integrated-type (For Output) Serial Transmission System, refer to the Web Catalog and the Operation Manual. For details about part numbers of SI units to be mounted, refer to page 35 in this catalog. Please download the Operation Manual via our website, https://www.smcworld.com




Plug-in Connector Connecting Base 25A-SY5000 Series



Type 10 Side Ported Type 11 Bottom Ported Plug-in Connector Connecting Base (C Sus 25A-SY5000 Series RoHS

How to Order Manifold



Series compatible with secondary batteries

SY5000

9 P, E port entry

•••	_ point officially
U	U side (2 to 10 stations)
D	D side (2 to 10 stations)
В	Both sides (2 to 16 stations)

6 SUP/EXH block assembly

- NilInternal pilotSInternal pilot, Built-in silencer
- 3/5(E) port is plugged for the built-in
- silencer type.
- When the built-in silencer type is used, keep the exhaust port from coming in direct contact with water or other liquids.

A, B port (Metric)

Symbol		A, B port	Type 10/ Side ported SY5000	Type 11/ Bottom ported SY5000	
C4	t	ø4 One-touch fitting			
		ø6 One-touch fitting		•	
C8	Stra	ø8 One-touch fitting		•	
CM *1	0	Straight port, mixed sizes			al Substant
P, E	P, E port size (One-touch fittings)		ø10	ø10	

*1 Indicate the size on the manifold specification sheet in the

case of "CM."

* The direction of P, E port fittings is the same as for the A, B port.

 The 25A- series specifications and dimensions are the same as those of the standard model.

Click here for details.

For details about the EX126 Integrated-type (For Output) Serial Transmission System, refer to the Web Catalog and the Operation Manual. For details about part numbers of SI units to be mounted, refer to page 35 in this catalog. Please download the Operation Manual via our website, https://www.smcworld.com

8 Mounting

DIN rail option

Mounting

Direct mounting DIN rail mounting

Standard length

With DIN bracket (Without DIN rail)

For 16 stations of specified stations.

Specify a longer rail

than the total length

Enter the number of stations inside \Box .

(Refer to "DIN Rail Option" below.) Only direct mounting is available for

Type 11 (Bottom ported).

For 3 stations

Symbol

Nil

D

Nil

0

3

16

2 Type

10	Side ported
11	Bottom ported

3 SI unit

0	Without SI unit
V	CC-Link (Positive common NPN)

 Only a terminal block plate is mounted for the valve without SI unit.
 For SI unit part number, refer to page 35.

4 Valve stations

Symbol	Stations	Note	
02	2 stations		
:	:	Double wiring*1	
08	8 stations		
02	2 stations	Creatified lowerst*?	
:	:	Specified layout*2 (Available up to 16 solenoids)	
16	16 stations	(Available up to 10 solellolus)	


*1 Double wiring: 2-position single, double, 3-position, and 4-position valves can be used on all manifold stations. Use of a 2-position single solenoid will

result in an unused control signal. If this is not desired, order with a specified layout.

- *2 Specified layout: Indicate the wiring specifications on the manifold specification sheet. (Note that 2-position double, 3-position, and 4-position valves cannot be used where single wiring has been specified.)
- This also includes the number of the blanking plate assembly.

A 31
 A

Plug-in Connector Connecting Base 25A-SY5000 Series



Plug-in Connector Connecting Base EX126 (C Subject of Connecting Base 25A-SY5000 Series (RoHS)

How to Order Manifold



Series compatible with secondary batteries

Series

ype 12 op Ported

5 SY5000

2 SI	unit
0	Without SI unit
V	CC Link (Desitive seman

 V | CC-Link (Positive common NPN)
 * Only a terminal block plate is mounted for the valve without SI unit.

For SI unit part number, refer to page 35.

3 Valve stations

_				
Symbol	Stations	Note		
02	2 stations			
:		Double wiring*1		
08	8 stations	-		
02	2 stations	Creating lowert*?		
:	:	Specified layout*2 (Available up to 16 solenoids		
16	16 stations			

- *1 Double wiring: 2-position single, double, 3- position, and 4-position valves can be used on all manifold stations.
 Use of a 2-position single solenoid will result in an unused control signal. If this is not desired, order with a
 - specified layout. Specified layout: Indicate the wiring
- *2 Specifications on the manifold specification sheet. (Note that 2-position double, 3-position, and 4-position valves cannot be used where single wiring has been specified.)
- This also includes the number of the blanking plate assembly.

4 P, E port entry

•••		
U *1	U side (2 to 10 stations)	
D *1	D side (2 to 10 stations)	
B Both sides (2 to 16 stations)		

*1 S For type "S," supply/exhaust block assembly with built-in silencer, choose "U" or "D" for P port entry.

5 SUP/EXH block assembly

Nil	Internal pilot	
S	Internal pilot, Built-in silencer	

- * For built-in silencer type, P and E ports are available on U and D sides. 3/5(E) port is plugged. The silencer exhaust port is located on the opposite side of P, E port entry. (Example: When the P, E port entry is D side, the silencer exhaust port is U side.)
- When the built-in silencer type is used, keep the exhaust port from coming in direct contact with water or other liquids.

6 Mounting

Nil	Direct mounting			
D	DIN rail mounting (With DIN rail)			
D0	DIN rail mounting (Without DIN rail)			
D3	For 3 stations Specify a longe i rail than the For 16 stations standard length			
:				
D16				


 The 25A- series specifications and dimensions are the same as those of the standard model.

Click here for details.

For details about the EX126 Integrated-type (For Output) Serial Transmission System, refer to the Web Catalog and the Operation Manual. For details about part numbers of SI units to be mounted, refer to page 35 in this catalog. Please download the Operation Manual via our website, https://www.smcworld.com

SMC

Plug-in Connector Connecting Base 25A-SY5000 Series



25A-SY5000 Series

SI Unit Part Nos.

Description	SI unit part no.	Note
	EX260-SPR1-X117	PROFIBUS DP M12 connector, 32 outputs, Negative common (PNP)
	EX260-SPR2-X117	PROFIBUS DP M12 connector, 32 outputs, Positive common (NPN)
	EX260-SPR3-X117	PROFIBUS DP M12 connector, 16 outputs, Negative common (PNP)
	EX260-SPR4-X117	PROFIBUS DP M12 connector, 16 outputs, Positive common (NPN)
	EX260-SDN1-X117	DeviceNet [™] M12 connector, 32 outputs, Negative common (PNP)
	EX260-SDN2-X117	DeviceNet [™] M12 connector, 32 outputs, Positive common (NPN)
	EX260-SDN3-X117	DeviceNet [™] M12 connector, 16 outputs, Negative common (PNP)
	EX260-SDN4-X117	DeviceNet [™] M12 connector, 16 outputs, Positive common (NPN)
	EX260-SEC1-X117	EtherCAT M12 connector, 32 outputs, Negative common (PNP)
	EX260-SEC2-X117	EtherCAT M12 connector, 32 outputs, Positive common (NPN)
	EX260-SEC3-X117	EtherCAT M12 connector, 16 outputs, Negative common (PNP)
EX260 SI unit	EX260-SEC4-X117	EtherCAT M12 connector, 16 outputs, Positive common (NPN)
EX200 SI unit	EX260-SMJ1-X117	CC-Link M12 connector, 32 outputs, Negative common (PNP)
	EX260-SMJ2-X117	CC-Link M12 connector, 32 outputs, Positive common (NPN)
	EX260-SMJ3-X117	CC-Link M12 connector, 16 outputs, Negative common (PNP)
	EX260-SMJ4-X117	CC-Link M12 connector, 16 outputs, Positive common (NPN)
	EX260-SPN1-X117	PROFINET M12 connector, 32 outputs, Negative common (PNP)
	EX260-SPN2-X117	PROFINET M12 connector, 32 outputs, Positive common (NPN)
	EX260-SPN3-X117	PROFINET M12 connector, 16 outputs, Negative common (PNP)
	EX260-SPN4-X117	PROFINET M12 connector, 16 outputs, Positive common (NPN)
	EX260-SEN1-X117	EtherNet/IP™ M12 connector, 32 outputs, Negative common (PNP)
	EX260-SEN2-X117	EtherNet/IP [™] M12 connector, 32 outputs, Positive common (NPN)
	EX260-SEN3-X117	EtherNet/IP™ M12 connector, 16 outputs, Negative common (PNP)
	EX260-SEN4-X117	EtherNet/IP [™] M12 connector, 16 outputs, Positive common (NPN)
EX126 SI unit	EX126D-SMJ1-X220	CC-Link (Terminal block, 16 outputs, Positive common (NPN))


Valve Mounting Screw Part No.

Description	Part no.	Note
Description	25A-SS5Y5	Note
Round head combination screw	SY5000-223-1A	Part numbers shown on the left are for 10 valves. (20 pcs.)


One-touch Fittings Part Nos.

		Port size	25A-SY5000
	Metric	ø4 One-touch fitting (Straight type)	90-VVQ1000-51A-C4
A, B port		ø6 One-touch fitting (Straight type)	
pon		ø8 One-touch fitting (Straight type)	90-VVQ1000-51A-C8
P, E Metric	ø10 One-touch fitting	90-VVQ2000-51A-C10	
port	size	(Straight type)	90-VVQ2000-5TA-CTU


Manifold Options



How to Order Individual SUP/EXH Block Assembly



5-Port Solenoid Valve Body Ported/Single Unit 25A-SY5000/7000 Series



SMC

* The 25A- series specifications and dimensions are the same as those of the standard model.

Control Valv

Air Cylinders

Related Products

Actuators

Air Grippers

Equipment

Vacuum

Air Preparation

Equipment

Filters

lean

Air F

Iodular F.R.L./Pressure Control Equipment

Equipment

Control

Switches

Detection

Fluid Control Equipment

Electric Actuators

Switches


Auto

Ē

Rotary

5-Port Solenoid Valve Base Mounted/Single Unit 25A-SY5000/7000 Series

How to Order



* Refer to the standard products for the lead wire length of L and M plug connectors and the connector assembly with cover for L and M plug connector.


st The 25A- series specifications and dimensions are the same as those of the standard model.



5-Port Solenoid Valve Body Ported Manifold Bar Stock Type/Individual Wiring 25A-SY5000/7000 Series

How to Order Manifold


Туре 20



Air Grippers Equipment Vacuum Air Preparation Equipment Clean Air Filters Modular F.R.L./Pressure Control Equipment Control Equipment Fittinas/Flow **Detection** Switches Fluid Control Equipment Electric Actuators Auto Switches

Air Cylinders Control Val

25A-SY5000/7000 Series



		E	lectrical entry
24, 12, 6	24, 12, 6, 5, 3 VDC/100, 110, 200, 220 VAC		
Grommet	L plug connector	M plug connector	DIN terminal
G: With lead wire (Length 300 mm) H: With lead wire (Length 600 mm)	L: With lead wire (Length 300 mm) LN: Without lead wire LO: Without connector	M: With lead wire (Length 300 mm) MN: Without lead wire MO: Without connector	D: With connector Y: With connector

* "LN," "MN" type: with 2 sockets.


* "Y" type is a DIN terminal conforming to EN-175301-803C (former DIN43650C).


* Refer to the standard products for the lead wire length of L and M plug connectors and the

connector assembly with cover for L and M plug connector.

* The 25A- series specifications and dimensions are the same as those of the standard model.







∕∂SMC

* The 25A- series specifications and dimensions are the same as those of the standard model. However, the blanking plate assembly has different dimensions. Refer to page 42. Rotary Actuators

Air Grippers

Vacuum Equipment

Air Preparation

Equipment

Clean Air Filters

Modular F.R.L./Pressure Control Equipment

Control Equipment

Detection Switches

Fluid Control Equipment


Electric Actuators

Switches

Auto

Fittinas/Flow

25A-SY5000/7000 Series



Electrical entry

24, 12, 6, 5, 3 VDC/100, 110, 200, 220 VAC			24, 12 VDC/ 100, 110, 200, 220 VAC
Grommet	L plug connector	M plug connector	DIN terminal
G: With lead wire (Length 300 mm) H: With lead wire (Length 600 mm)	LN: Without lead wire	M: With lead wire (Length 300 mm) MN: Without lead wire MO: Without connector	D: With connector Y: With connector

* "LN," "MN" type: with 2 sockets.

* "Y" type is a DIN terminal conforming to EN-175301-803C (former DIN43650C).


* Refer to the standard products for the lead wire length of L and M plug connectors and the connector assembly with cover for L and M plug connector.

* The 25A- series specifications and dimensions are the same as those of the standard model.



25A-SY5000/7000 Series

How to Order Pilot Valve Assembly



* Since V111 and V115 are CE-compliant as standard, the suffix "-Q" is not necessary.

SMC

5-Port Solenoid Valve 25A-SY5000/7000 Series

One-touch Fittings Part Nos. for Body Ported

Port size		25A-SY5000	25A-SY7000	
		ø4 One-touch fitting (Straight type)	90-VVQ1000-51A-C4	
Culinder port	Metric size	ø6 One-touch fitting (Straight type)	90-VVQ1000-51A-C6	
Cylinder port	Cylinder port Metric size	ø8 One-touch fitting (Straight type)	90-VVQ1000-51A-C8	90-VVQ2000-51A-C8
		ø10 One-touch fitting (Straight type)		90-VVQ2000-51A-C10

Gasket Assembly Part Nos.

Valve model	Manifold type	25A-SY5000	25A-SY7000
Body ported	Туре 20	SY5000-GS-3	SY7000-GS-3
Base mounted	Type 41/42	SY5000-GS-4 (-Q)	SY7000-GS-4 (-Q)

25A-SY5000


25A-SY7000

* The gasket assembly includes 10 sets of a gasket and mounting screws.

Bracket Assembly Part Nos.

Description	Part no.
Bracket (For F1)	25A-SX ⁵ 000-16-2A (With mounting screw)
Bracket (For F2)	25A-SX ⁵ 7000-16-1A (With mounting screw)

Port Block Assembly Part Nos.



C6 One-touch fitting for ø6
C8 One-touch fitting for ø8
C8 One-touch fitting for ø8

C10 One-touch fitting for ø10


25A-SY5000/7000 Series

Manifold Options

Blanking plate assembly


(Mounting screw: 2 pcs., with gasket)

It is used by attaching on the manifold block for being prepared for removing a valve for maintenance reasons or planning to mount a spare valve, etc.



Dimensions

Manifold type/For type 20



Í
<u></u> 도
₽, 1


Dimensions [mm]						
Series	Manifold type	W 1	W2	H1	H2	
25A-SY5000	Type 20	33.3	69.6	44.5	15.2	
25A-SY7000	Type 20	39.4	76.4	41.1	18.3	

How to Order 25A - SY 5 000 - 26 - 1A • Series 5 25A-SY5000 7 25A-SY7000

▲ Caution

When mounted on a type 20 manifold, only the P port is plugged. In addition, it cannot be used for the type 20 CE-compliant manifold.


Manifold type/For type 41/42



Dimensions [mm]					
Series	Manifold type	w	H1	H2	
25A-SY5000	Type 41	106.4	51	21.7	
254-515000	Type 42	107.6	56	26.7	
25A-SY7000	Type 42	118.1	55.6	32.8	

SMC

Plug-in Unit/Base Mounted F Kit (D-sub connector kit) 25A-VQ2000 Series




SMC

Caution Use the standard (DC) specification when continuously energizing for long periods of time.

* The 25A- series specifications and dimensions are the same as those of the standard model.

▲ 43

Plug-in Unit/Base Mounted T Kit (Terminal block box kit) 25A-VQ2000 Series



Click here for details.

Control Valv

Air Cylinders

Air Grippers

Equipment

Equipment


Control Equipment

Control Equipment

Equipment

Switches


Plug-in Unit/Base Mounted L Kit (Lead wire) 25A-VQ2000 Series



* The 25A- series specifications and dimensions are the same as those of the standard model. Click here for details.

SMC

Plug-in Unit/Base Mounted S Kit (Serial transmission) 25A-VQ2000 Series



* The 25A- series specifications and dimensions are the same as those of the standard model. Click here for details. SMC

Directional Control Valv

Sub-plate Single Unit 25A-VQ2000 Series

* For CE-compliant How to Order models, DC-type only. [Option] In the case of (Valve) + (Sub-plate) 25A-VQ2 1 0 5 W - 02 1 CE-compliant Nil Series compatible with Entry is the same as Q CE-compliant secondary batteries standard products. For CE-compliant models, DC-type only. Enclosure Thread type Nil Dustproof Nil Rc Dust-tight/Water-jet-proof type **W***1 (IP65) Ν NPT NPTF т *1 Valves are IP65 specifications. * When the valve is a standard F G (dust-protected) specification, it is not compatible with 200 or 220 VAC. Port size **02** 1/4 In the case of (Sub-plate) alone 25A-VQ2000-PW-02

* The 25A- series specifications and dimensions are the same as those of the standard model.

Click here for details.


25A-VQ2000 Series

Manifold Options

Blanking plate assembly

25A-VVQ2000V-10A-1

It is used by attaching on the manifold block for being prepared for removing a valve for maintenance reasons or planning to mount a spare valve, etc.



* The 25A- series specifications and dimensions are the same as those of the standard model.

Click here for details.


SI Unit Part Nos.

Description	SI unit part no.	Note
EX124 SI unit EX124D-SMJ1-X220		CC-Link
EX124 SI unit	EX124D-SDN1-X220	DeviceNet [™]
EX120 SI unit	EX120-SMJ1-X220	CC-Link (VQ2000/Without option "W")
EX120 SI UIII	EX120-SDN1-X220	DeviceNet [™] (VQ2000/Without option "W")

One-touch Fittings Part Nos.


Port size			One-touch fitting part no.
		ø4 One-touch fitting (Straight type)	90-VVQ1000-51A-C4
Cylinder port	rt Metric size	ø6 One-touch fitting (Straight type)	90-VVQ1000-51A-C6
		ø8 One-touch fitting (Straight type)	90-VVQ1000-51A-C8
1 (P), 3 (R) port	Metric size	ø10 One-touch fitting (Straight type)	90-VVQ2000-51A-C10

Plug-in/Plug Lead: Single Unit Base Mounted 25A-VQ4000 Series




SMC

Plug-in Unit/Base Mounted F Kit (D-sub connector kit) 25A-VQ4000 Series



Plug-in Unit/Base Mounted T Kit (Terminal block box kit) 25A-VQ4000 Series




SMC

- *3 External pilot specifications are the same as standard products. Combination of external pilot and perfect interface is not possible.
- * When two or more symbols are specified, indicate them alphabetically.

* The 25A- series specifications and dimensions are the same as those of the standard model.

Plug-in Unit/Base Mounted L Kit (Lead wire cable) 25A-VQ4000 Series




SMC

- * When two or more symbols are specified, indicate them alphabetically.
- * The 25A- series specifications and dimensions are the same as those of the standard model. Click here for details.

Control Val


Plug-in Unit/Base Mounted S Kit (Serial transmission unit) 25A-VQ4000 Series



SMC

Combination of external pilot and perfect interface is not possible. * When two or more symbols are specified, indicate them alphabetically. The 25A- series specifications and dimensions are the same as those of the standard model.

Plug Lead Unit/Base Mounted C Kit (Connector kit) 25A-VQ4000 Series




25A-VQ4000 Series

Manifold Options

Blanking plate assembly

25A-VVQ4000-10A-1 (Plug-in type) 25A-VVQ4000-10A-5 (Plug lead type)

It is used by attaching on the manifold block for being prepared for removing a valve for maintenance reasons or planning to mount a spare valve, etc.



* The 25A- series specifications and dimensions are the same as those of the standard model.

Click here for details.

SI Unit Part Nos.

Description	SI unit part no.	Note	
EX124 SI unit	EX124D-SMJ1-X220	CC-Link/D side mounting	
	EX124D-SDN1-X220	DeviceNet™/D side mounting	
	EX124U-SMJ1-X220	CC-Link/U side mounting	
	EX124U-SDN1-X220	DeviceNet [™] /U side mounting	

One-touch Fittings Part Nos.

Port size			One-touch fittings part no.
	O dia dan a art Matria aire	ø6 One-touch fitting (Straight type)	90-VVQ4000-50B-C6
Culinder port		ø8 One-touch fitting (Straight type)	90-VVQ4000-50B-C8
Cylinder port Metric size	wethe size	ø10 One-touch fitting (Straight type)	90-VVQ4000-50B-C10
	-	ø12 One-touch fitting (Straight type)	90-VVQ4000-50B-C12

Plug-in Unit 25A-SQ2000 Series Ontion1

Control Va

Air Cylinders

Actuators

Air Grippers

Equipment

Equipment

Filters

Air

Control Equipment


Control Equipment

Equipment

Electric Actuators

Switches

Auto



single solenoids and 2 for type 3P and 4P double solenoids.) *2 Refer to the Web Catalog for the details of EX140 integrated-type (for output) serial transmission system. Refer to "SI unit part nos." below when ordering the CE-compliant SI unit.

SI unit part nos.


Symbol	Protocol type	SI unit part no.	Page
SDQ	DeviceNet™	EX140-SDN1-X220	n 60
SDV	CC-Link	EX140-SMJ1-X220	p. 60
·			

Blanking plate assembly

25A-SSQ2000-10A-3

* The 25A- series specifications and dimensions are the same as those of the standard model.

25A-SQ2000 Series



* The 25A- series specifications and dimensions are the same as those of the standard model.

SMC

Plug Lead Unit 25A-SQ2000 Series

Control Va

Air Cylinders

Related Products

Rotary Actuators

Air Grippers

Equipment Vacuum

Air Preparatior Equipment

Air Filters

lean

0

Modular F.R.L./Pressure Control Equipment

Control Equipment

Detection Switches


Fluid Control Equipment

Electric Actuators

Switches

Auto

Fittings/Flow



Electrical entry

Kit type		Lead wire connector location	Cable specifications	Stations	Max. number of stations for special wiring specifications	*1 Max. number of solenoids
F kit	FD0		D-sub connector (25P) kit, without cable			
The electric	FD1		D-sub connector (25P) kit, with 1.5 m cable	1 to 12 stations	16 stations	24
of copper.	FD2	FD2 D side	D-sub connector (25P) kit, with 3.0 m cable		TO Stations	24
D-sub connector kit	FD3		D-sub connector (25P) kit, with 5.0 m cable			
Connector kit Mounting screw: Stainless steel One-touch fitting Body: Stainless steel	С	_	Connector kit	1 to 16 stations	_	_

*1 The maximum number of stations should not be more than the maximum number of solenoids. (The number of solenoids are counted as: 1 for single solenoids and 2 for type 3P and 4P double solenoids.)

SMC


Refer to the Web Catalog for manifold spare parts.

Blanking plate assembly

25A-SSQ2000-10A-4

The 25A- series specifications and dimensions are the same as those of the standard model.

25A-SQ2000 Series



* The 25A- series specifications and dimensions are the same as those of the standard model. Click here for details.

Plug Lead Unit 25A-SQ2000 Series

SI Unit Part Nos.

Description	SI unit part no.	Note
EX140 SI unit	EX140-SMJ1-X220	CC-Link
	EX140-SDN1-X220	DeviceNet [™]


One-touch Fittings Part Nos.

Port size			One-touch fittings part no.
Cylinder port	Metric size	ø4 One-touch fitting (Straight type)	90-VVQ1000-51A-C4
		ø6 One-touch fitting (Straight type)	90-VVQ1000-51A-C6
		ø8 One-touch fitting (Straight type)	90-VVQ1000-51A-C8
1 (P), 3 (R) port	Metric size	ø10 One-touch fitting (Straight type)	90-VVQ2000-51A-C10

Base Mounted

Plug Lead Unit

5-Port Solenoid Valve 25A-VQZ1000 Series Single Unit



\land Caution

Use standard (DC) specification for continuous duty.


* The 25A- series specifications and dimensions are the same as those of the standard model.



Base Mounted

Plug Lead Unit

5-Port Solenoid Valve 25A-VQZ1000 Series Manifold Connector Kit



*∕∂*SMC

Use standard (DC) specification for continuous duty.


Click here for details.

[Ontion]

Body Ported

Plug Lead Unit

5-Port Solenoid Valve 25A-VQZ1000 Series Single Unit



A Caution


Use standard (DC) specification for continuous duty.

The 25A- series specifications and dimensions are the same as those of the standard model.



Body Ported Plug Lead Unit

5-Port Solenoid Valve 25A-VQZ1000 Series Manifold Connector Kit



/!\ Caution Use standard (DC) specification for continuous duty.


* The 25A- series specifications and dimensions are the same as those of the standard model.

Click here for details.

Ontion]


Plug-in Unit Base Mounted 25A-VQ1000/2000 Series Double check block (Separated)

How to Order



^{*} The 25A- series specifications and dimensions are the same as those of the standard model. Click here for details.

Rubber Seal 3-Port/Pilot Poppet Type 25A-VP342/542/742 Series



There is no "S" type for AC mode, since a rectifier prevents *1 surge voltage generation.

The 25A- series specifications and dimensions are the same as those of the standard model.

Control Val

Air Cylinders

Air Grippers

Equipment

Air Preparation Equipment

Clean Air Filters

Control Equipment

Equipment

Control

Detection Switches

Fluid Control Equipment


Electric Actuators

Switches

Auto

Fittings/Flow


Rubber Seal 3-Port/Pilot Poppet Type 25A-VP344/544/744 Series



*1 There is no "S" type for AC mode, since a rectifier prevents surge voltage generation.


* The 25A- series specifications and dimensions are the same as those of the standard model.






SMC

68





	VO317(-Q)	Common or individual exhaust	O-ring (KA00066, 4 pcs.)*1 Bolts (XT012-25C#1, 2 pcs.)
*	I It is not applied to "Cor	tinuous duty type." Refer to the acce	ssories in the Web Catalog.

(14 0 0 0 0 0

* The 25A- series specifications and dimensions are the same as those of the standard model. Click here for details.



3-Port Solenoid Valve Direct Operated Poppet Type **25A-VG342 Series** Rubber Seal



4.8 W DC (Standard type) 2 W DC (Energy-saving type)

No lubrication required

Possible to use in vacuum or under low pressures


External pilot Vacuum: Up to -101.2 kPa Low pressure: 0 to 0.2 MPa

Changeable actuation:

N.C., N.O., or external pilot

Can be used as a selector or divider valve (External pilot)






* The 25A- series specifications and dimensions are the same as those of the standard model.

Click here for details.

5-Port Air Operated Valve 25A-SYA5000/7000 Series

How to Order



How to Order Manifold Base

Same manifolds as the SY series (Non plug-in type) are prepared. (For 20, 41 and 42 Types)


25A-SS5YA⁵₇. Fill the same as 25A-SS5Y ⁵₇. (Refer to page 40.)

- Specify the part numbers for valves and options together beneath the manifold base part number.
- <Example>
 - 25A-SS5YA5-42-03-02····1 set (Type 42, 3 station manifold base part no.)
 - * 25A-SYA5140 1 set (Single air operated valve part no.)
 - * 25A-SYA5240 1 set (Double air operated valve part no.)
 - * 25A-SY5000-26-1A 1 set (Blanking plate assembly part no.)

- The asterisk denotes the symbol for assembly. Prefix it to the part nos. of the solenoid valve, etc.
- When single body ported air operated valves are ordered, manifold mounting screws and gaskets are not included. Order them separately if necessary. (For details, refer to page 42.)
- * The 25A- series specifications and dimensions are the same as those of the standard model.




3-Port Air Operated Valve 25A-SYJA500/700 Series




Auto Switches


25A-SYJA500/700 Series



Finger Valve RoHS **25A-VHK A** Series




Standard Type





1(P): One-touch fitting 2(A): One-touch fitting

\frown	2(A)	Applicable tubing O.D. [mm]			
1(P)	ø4	ø6	ø8	
ble tubing . [mm]	ø4	•			
cable tub .D. [mm]	ø6	•	•		
Applic O.	ø8			\bullet	



1(P): Male thread 2(A): One-touch fitting





1(P): One-touch fitting 2(A): Male thread


	2(A)	Port size R			
1(P)	1⁄8	1⁄4	3⁄8	
Applicable tubing O.D. [mm]	ø4	•			
cable t D. [mr	ø6	•	•	•	
Applic O.	ø8	•	•	•	

* The 25A- series specifications and dimensions are the same as those of the standard model.


Click here for details.








Standard Type




1(P): One-touch fitting 2(A): One-touch fitting

	2(A)	Applicable tubing O.D. [mm]			
1(P)	ø4	ø6	ø8	
ubing n]	ø4	•			
Applicable tubing O.D. [mm]	ø6	•	•		
Applic O.	ø8			۲	



1(P): Male thread 2(A): One-touch fitting

	2(A)	Applicable tubing O.D. [mm]				
1(P)	ø4	ø6	ø8		
Port size R	1⁄8	٠	•			
	1⁄4		•	•		
Pol	3⁄8		•			



1(P): One-touch fitting 2(A): Male thread


2(A)	Port size R						
)	1⁄8	1⁄4	3⁄8				
ø4	•						
ø6	•	•	•				
ø8	•	•	•				
) ø4 ø6) 1⁄8 ø4 ● ø6 ●	1/8 1/4 ø4 • ø6 •				

* The 25A- series specifications and dimensions are the same as those of the standard model.

Click here for details.

Conforming to OSHA Standard Pressure Relief 3-Port Valve with Locking Holes (Single Action) 25A-VHS20/30/40/50 Series

RoHS



ianaio,	Berniet material	
Symbol	Material	
Α	Flame-resistant PBT	
В	Aluminum	

Option Part Nos.

Model	Bracket assembly part no.*1
25A-VHS20	VHS20PW-180AS-6
25A-VHS30	VHS30PW-180AS-6
25A-VHS40	VHS40PW-180AS-6
25A-VHS40-06	VHS40PW-180-06AS-6
25A-VHS50	VHS50PW-180AS-6

OSHA standard (Occupational Safety and Health Administration Department of Labor)


For safety control, OSHA rule requires energy sources for certain equipment be turned off or disconnected and that the device either be locked or labelled with a warning tag.

> * The 25A- series specifications and dimensions are the same as those of the standard model.


> > Click here for details.

*1 Bracket/1 pc., Mounting screw/2 pcs.

OSHA Standard Compliant Pressure Relief 3-Port Valve with L	ocking Holes
Single Action	RoHS
25A-VHS20/30/40/50-D Series	
Double Action	
25A-VHS20W/30W/40W/50W-I	D Series



How to Order



• Option/Semi-standard: Select one each for **a to f**. • Option/Semi-standard symbol:

When more than one specification is required, indicate in alphanumeric order.

Example) 25A-VHS30-N03-BS-RZ-D

Series compatible with secondary batteries

				0					
				Symbol	Description		Body		
						20	30	40	50
2		Ца	ndle operation	Nil	Single action				\bullet
9		110		W	Double action				
				+					
_				Nil	Rc*1				
8		Pij	pe thread type	Ν	NPT	•			
				F	G				
				+					
				01	1/8	•	_	—	—
				02	1/4			•	—
4			Port size	03	3/8			•	—
Y		Fort size		04	1/2	_	—	•	—
				06	3/4	—	_	•	
				10	1	_	—	_	
				+					
		a	Mounting	Nil	Without mounting option	•		•	\bullet
_	5	a		В	With bracket				
6	Option	b		+					
	0		Silencer	Nil	Without silencer	•			
				S	With built-in silencer (for EXH port)				
				+					
		c	c Handle color	Nil	Red				
				K	Black	•			
				+					
	ard	d	Handle material	Nil	Resin				
_	P 2	u		М	Metal			•	
6	sta			+					
	Semi-standard	е	e Flow direction	Nil	Flow direction: Left to right	•		•	
	s.	C	T IOW direction	R	Flow direction: Right to left	•			
				+					
		f	Pressure unit	Nil	Product label in SI units: MPa			•	
		•	Pressure unit	Z *2	Product label in imperial units: psi	○*3	○*3	⊖*3	⊖*3

*1 The pipe thread type for the EXH port is G.

*2 For the pipe thread type: NPT only. This product is for overseas use only according to the New Measurement Act. (The SI unit type is provided for use in Japan.)

*3 O: For the pipe thread type: NPT only

* The 25A- series specifications and dimensions are the same as those of the standard model.

Click here for details.


Option/Part Nos.

Optional apositional			Model		
Optional specifications	25A-VHS20-D	25A-VHS30-D	25A-VHS40-D	25A-VHS40-06-D	25A-VHS50-D
Bracket assembly*1	25A-VHS24P-180AS	25A-VHS34P-180AS	25A-VHS44P-180AS	25A-VHS44P-180AS	25A-VHS54P-180AS
Silencer assembly*2	VHS24P-190AS	VHS34P-190AS	VHS44P-190AS	VHS54P-190AS	VHS54P-190AS

*1 The assembly consists of a bracket A/B and 2 mounting screws.

*2 The assembly consists of the element assembly and an O-ring.

Conforming to OSHA Standard Pressure Relief 3-Port Valve with Locking Holes (Double Action) 25A-VHS2510/3510/4510/5510 Series



* The 25A- series specifications and dimensions are the same as those of the standard model.

Click here for details.

*∕∂*SMC

Directional Control Valves

Air Cylinders

Air Grippers

Equipment

Equipment

Air

Control Equipment

Control Equipment

Fluid Control Equipment

Electric Actuators

Auto Switches

RoHS