Capable of air cylinder multipoint positioning and control



- Ambient temperature:−20°C to 60°C (No freezing)
- Applicable to cylinders with diameters of Ø125 to Ø400
- ■Input signal: 4 to 20 mA
- With stroke position signal output function (4 to 20 mA)
- **HART transmission**
- With auto calibration function
- Supports the fail safe function



