

DWG NO Ⓐ AC60X-F06-6-D-X2105 △1





SPECIFICATIONS
1. REFER TO PRODUCT SPECIFICATION FOR EACH PRODUCT.

CAUTION FOR PRODUCTION
1. SILENCER SHOULD BE INSTALLED BEFORE SHIPMENT.
2. PRESSURE GAUGE WITH SEALANT IS PACKAGED TOGETHER.
3. DIGITAL PRESSURE SWITCH AND REDUCING NIPPLE ARE PACKAGED TOGETHER.
△1 4. NO NEED PLUG FOR THE GAUGE PORT OF FILTER REGULATOR AND SOFT START-UP VALVE.
5. NO NEED SEALANT FOR REDUCING NIPPLE.
△1 6. NO NEED RESIN PLUG FOR THE FRONT AND BACK PORT OF CROSS SPACER.
△1 7. ⑬⑭HEXAGON SOCKET HEAD PLUG SHOULD BE INSTALLED BEFORE SHIPMENT.

△1 NOTE
PRESSURE GAUGE AND DIGITAL PRESSURE SWITCH ARE FOR OVERSEAS USE ONLY ACCORDING TO THE NEW MEASUREMENT ACT.
(THE SI UNIT TYPE IS PROVIDED FOR USE IN JAPAN.)

BE SURE TO REFER "CATALOG" AND "OPERATING MANUAL" FOR F.R.L. PRECAUTION BEFORE HANDLING.

UNLESS OTHERWISE NOTED ALONG WITH A SEPARATE CONTRACT OR AGREEMENT WITHIN THE PRODUCT SPECIFICATIONS, THE SAFETY INSTRUCTIONS SPECIFIED IN THE PRODUCT CATALOG ARE APPLIED. PLEASE CONTACT YOUR LOCAL SMC SALES OFFICE FOR FURTHER DETAILS.

ITEM	PART NO	PART NAME	MATERIAL	QTY	REMARKS
15	Y340P-070	PRODUCT LABEL	PET	1	COMPLETE PRODUCT NO. INDICATED
△1 14	TB00384	HEXAGON SOCKET HEAD PLUG	STEEL	2	R3/4×17 Zn.CHROMATE TREATMENT
△1 13	TB00004	HEXAGON SOCKET HEAD PLUG	STEEL	2	R1/8 Zn.CHROMATE TREATMENT
12	VA00179	REDUCING NIPPLE	STEEL	1	R3/8×R1/4 Zn.CHROMATE TREATMENT
△1 11	Y600-D	SPACER	-	2	
△1 10	Y600T-D	SPACER WITH BRACKET	-	4	
△1 9	ANA1-06	SILENCER	-	1	
8	ISE70-F02-L2	DIGITAL PRESSURE SWITCH	-	1	
△1 7	G36-P10-01-L-X30	PRESSURE GAUGE	-	2	
6	Y610-F03-1-D	T-SPACER	-	1	
△1 5	AVL5000-F06-A	SOFT START-UP VALVE	-	1	
△1 4	Y64-F06-D	CROSS SPACER	-	1	
3	AM60-F10-L-D	MIST SEPARATOR	-	1	
2	AW60K-F06-6-D	FILTER REGULATOR	-	1	
1	E600-F06-D	PIPING ADAPTER	-	2	

REV	QTY	DESCRIPTION	DATE	PREPARED	REV NO
△1	20	COMPONENT EQUIPMENT CHANGES, NOTES ADDED	2023-11-06	Y.Ishikawa	DOC1057310
△0	-	INITIAL RELEASE	2023-02-15	K.Sugihara	-

FINISH -
PAINT -
MASS -
PACKING -
MATERIAL -
MATERIAL SIZE -

MODEL QTY

THIRD ANGLE

TOLERANCES JIS B 0405

RANGE(mm)	GRADE f (+)	m (+)	c (+)
0.5≤D≤3	0.05	0.1	0.2
3<D≤6	0.05	0.1	0.3
6<D≤30	0.1	0.2	0.5
30<D≤120	0.15	0.3	0.8
120<D≤400	0.2	0.5	1.2
400<D≤1000	0.3	0.8	2
1000<D≤2000	0.5	1.2	3

DRAWN DATE
DESIGNED Y.Ishikawa 2023-11-06
CHECKED G.Mimura 2023-11-07
APPROVED K.Matsushita 2023-11-08

SCALE FREE

DWG NAME AIR COMBINATION

DWG NO Ⓐ AC60X-F06-6-D-X2105

REVISION △1 H

DWG NAME

DWG REC

DWG ID GC10833701

SMC Corporation

SW-A1-V06

FINISH:表面処理 / PAINT:塗装 / MASS:質量
PACKING:包装区分 / MATERIAL:材質
MATERIAL SIZE:材料寸法