

Circulating Fluid Temperature Controller Thermo-chiller




Compact Dual/Basic Type for Lasers

Air-cooled Refrigeration

The temperatures of **2 fluid channel** systems can be controlled individually by 1 chiller.

Space saving

Footprint reduced by **21 %**



Energy saving

Power consumption reduced by **17 %**

- 1 refrigerator, fan, and pump
- Uses a heating method that doesn't require a heater

- Cooling capacity (CH1, 2 total) **8.0 kW/9.5 kW (50 Hz/60 Hz)**
- Temperature stability **$\pm 0.1^{\circ}\text{C}$ CH1, $\pm 0.5^{\circ}\text{C}$ CH2**
- Set temperature range **15 to 25°C CH1, CH1 temperature + 0 to 15°C CH2**
- Water splash-resistant outdoor installation type (IPX4 compliant)
- Low noise function (due to adjustable fan rotation count)
- Increased cooling capacity function (With compressor inverter: Option C)
- Circulating fluid pressure adjustment function (With pump inverter: Option P)

HRLE Series



21-EU770-UK

Thermo-chiller

Compact Dual/Basic Type for Lasers

HRLE Series



RoHS

Power supply	3-phase 200 VAC (50 Hz)
	3-phase 200 to 230 VAC (60 Hz)

How to Order

HRLE 090 - A - 20 -

Cooling capacity

	CH1, 2 total
090	9.5 kW

Cooling method

A	Air-cooled refrigeration
---	--------------------------

Power supply

20	3-phase 200 VAC (50 Hz)
	3-phase 200 to 230 VAC (60 Hz)

Option

—	None
C	With compressor inverter
M	Applicable to DI water piping
P	With pump inverter

• When multiple options are combined, indicate the symbols in alphabetical order.



Air-cooled refrigeration

Specifications

Model			HRLE090-A-20	
Cooling method			Air-cooled refrigeration	
Refrigerant			R410A (HFC)	
Refrigerant charge		kg	2	
Control method			PID control	
Ambient temperature		°C	2 to 45	
Circulating fluid system	Circulating fluid*1		Tap water, Deionised water	
	Set temperature range		°C CH1: 15 to 25, CH2: CH1 + 0 to 15	
	Cooling capacity (CH1, 2 total) 50 Hz/60 Hz*2		kW 8.0/9.5	
	Heating capacity (CH1, 2 total) 50 Hz/60 Hz*3		kW 2.0/2.5	
	Temperature stability*4		°C CH1: ±0.1, CH2: ±0.5	
	Pump capacity	Rated flow 50 Hz/60 Hz*5		l/min CH1: 25/35, CH2: 2/2
		Max. flow rate 50 Hz/60 Hz		l/min 55/65
		Max. pump head		m 50
	Min. operating flow rate 50 Hz/60 Hz*6		l/min CH1: 25/35, CH2: 1/1	
	Tank capacity (CH1, 2 total)		L Approx. 18	
	Circulating fluid outlet, circulating fluid return port		CH1: Rc1, CH2: Rc1/2	
Tank drain port		Rc1/4		
Fluid contact material		Stainless steel, Copper (Heat exchanger brazing), Bronze (Pump), Ceramic, Carbon, FKM, PP, PE, POM, PVC, PA, EPDM		
Electrical system	Power supply		3-phase 200 VAC (50 Hz) Allowable voltage range ±10 % (No continuous voltage fluctuation) 3-phase 200 to 230 VAC (60 Hz) Allowable voltage range ±10% (No continuous voltage fluctuation)	
	Earth leakage breaker (Standard)	Rated current	A 30	
		Sensitivity current	mA 30	
	Rated operating current 50 Hz/60 Hz		A 14/17	
	Rated power consumption 50 Hz/60 Hz		kW(kVA) 4.3/5.3 (4.9/5.8)	
Communication function			Contact input/output, Serial communication (RS-485)	
Noise level		dB(A)	65	
Accessories*7			Operation Manual (for installation/operation) 2 pcs. (English 1 pc./Japanese 1 pc.), Anchor bolt fixing brackets 2 pcs. (includes 4 M8 bolts), Cable accessory (For communication cable)	
Weight		kg	140	

*1 Use fluid that fulfills the conditions below as the circulating fluid.

Tap water: Standard of The Japan Refrigeration And Air Conditioning Industry Association (JRA GL-02-1994)

Deionised water: Electric conductivity 0.4 μS/cm or higher (Electric resistivity 2.5 MΩ·cm or lower)

*2 ① Ambient temperature: 32 °C, ② Circulating fluid: Tap water, ③ Circulating fluid temperature: CH1 20 °C/CH2 25 °C, ④ Circulating fluid flow rate: Rated flow, ⑤ Power supply: 200 VAC

*3 ① Ambient temperature: 32 °C, ② Circulating fluid: Tap water, ③ Circulating fluid flow rate: Rated flow, ④ Power supply: 200 VAC

*4 ① Ambient temperature: 32 °C, ② Circulating fluid: Tap water, ③ Circulating fluid temperature: CH1 20 °C/CH2 25 °C, ④ Circulating fluid flow rate: Rated flow, ⑤ Power supply: 200 VAC, ⑥ Piping length: Shortest, ⑦ Load: Same as the cooling capacity

*5 Circulating fluid discharge pressure = at 0.5 MPa

*6 Fluid flow rate to maintain the cooling capacity and to keep the circulating fluid discharge pressure at 0.5 MPa or less

If the actual flow rate is lower than this, install bypass piping.

*7 The anchor bolt fixing brackets (includes 4 M8 bolts) are used for securing the product to wooden skids when packaging the thermo-chiller. The anchor bolt is not included.



RoHS

Power supply	3-phase 380 to 415 VAC (50/60 Hz)
	3-phase 460 to 480 VAC (60 Hz)

How to Order

HRLE 090 - A - 40 -

Cooling capacity

	CH1, 2 total
090	9.5 kW

Cooling method

A	Air-cooled refrigeration
---	--------------------------

Power supply

40	3-phase 380 to 415 VAC (50/60 Hz)
	3-phase 460 to 480 VAC (60 Hz)

Option

—	None
C	With compressor inverter
M	Applicable to DI water piping
P	With pump inverter

- When multiple options are combined, indicate the symbols in alphabetical order.



Air-cooled refrigeration

Specifications

Model			HRLE090-A-40		
Cooling method			Air-cooled refrigeration		
Refrigerant			R410A (HFC)		
Refrigerant charge		kg	2		
Control method			PID control		
Ambient temperature		°C	2 to 45		
Circulating fluid system	Circulating fluid*1		Tap water, Deionised water		
	Set temperature range		°C	CH1: 15 to 25, CH2: CH1 + 0 to 15	
	Cooling capacity (CH1, 2 total) 50 Hz/60 Hz*2		kW	8.0/9.5	
	Heating capacity (CH1, 2 total) 50 Hz/60 Hz*3		kW	2.0/2.5	
	Temperature stability*4		°C	CH1: ±0.1, CH2: ±0.5	
	Pump capacity	Rated flow 50 Hz/60 Hz*5		l/min	CH1: 25/35, CH2: 2/2
		Max. flow rate 50 Hz/60 Hz		l/min	55/65
		Max. pump head		m	50
	Min. operating flow rate 50 Hz/60 Hz*6		l/min	CH1: 25/35, CH2: 1/1	
	Tank capacity (CH1, 2 total)		L	Approx. 18	
Circulating fluid outlet, circulating fluid return port			CH1: Rc1, CH2: Rc1/2		
Tank drain port			Rc1/4		
Fluid contact material			Stainless steel, Copper (Heat exchanger brazing), Bronze (Pump), Ceramic, Carbon, FKM, PP, PE, POM, PVC, PA, EPDM		
Electrical system	Power supply			3-phase 380 to 415 VAC (50/60 Hz) Allowable voltage range ±10 % (No continuous voltage fluctuation) 3-phase 460 to 480 VAC (60 Hz) Allowable voltage range +4%, -10% (Max. voltage less than 500 V and no continuous voltage fluctuation)	
	Applicable earth leakage breaker*8	Rated current		A	20
		Sensitivity current		mA	30
		Rated operating current 50 Hz/60 Hz		A	6.8/8.2
		Rated power consumption 50 Hz/60 Hz		kW(kVA)	4.3/5.3 (4.9/5.8)
Communication function			Contact input/output, Serial communication (RS-485)		
Noise level		dB(A)	67		
Accessories*7			Operation Manual (for installation/operation) 2 pcs. (English 1 pc./Japanese 1 pc.), Anchor bolt fixing brackets 2 pcs. (includes 4 M8 bolts), Cable accessory (For communication cable)		
Weight		kg	140		

*1 Use fluid that fulfills the conditions below as the circulating fluid.

Tap water: Standard of The Japan Refrigeration And Air Conditioning Industry Association (JRA GL-02-1994)

Deionised water: Electric conductivity 0.4 μS/cm or higher (Electric resistivity 2.5 MΩ·cm or lower)

*2 ① Ambient temperature: 32 °C, ② Circulating fluid: Tap water, ③ Circulating fluid temperature: CH1 20 °C/CH2 25 °C, ④ Circulating fluid flow rate: Rated flow, ⑤ Power supply: 400 VAC

*3 ① Ambient temperature: 32 °C, ② Circulating fluid: Tap water, ③ Circulating fluid flow rate: Rated flow, ④ Power supply: 400 VAC

*4 ① Ambient temperature: 32 °C, ② Circulating fluid: Tap water, ③ Circulating fluid temperature: CH1 20 °C/CH2 25 °C, ④ Circulating fluid flow rate: Rated flow, ⑤ Power supply: 400 VAC, ⑥ Piping length: Shortest, ⑦ Load: Same as the cooling capacity

*5 Circulating fluid discharge pressure = at 0.5 MPa

*6 Fluid flow rate to maintain the cooling capacity and to keep the circulating fluid discharge pressure at 0.5 MPa or less

If the actual flow rate is lower than this, install bypass piping.

*7 The anchor bolt fixing brackets (includes 4 M8 bolts) are used for securing the product to wooden skids when packaging the thermo-chiller.


The anchor bolt is not included.

*8 To be prepared by the customer

Cooling Capacity


HRLE090-A-20/40

[50 Hz]



HRLE090-A-20/40


[60 Hz]



- * The cooling capacity is the sum of the capacities of CH1 and CH2.
- * The ambient temperature of 32 °C is at 60 % fan output (default setting).
- * The ambient temperatures of 40 °C and 45 °C are at 100 % fan output. (The noise level rises by approx. 3 dB(A) from the rated condition.)

Pump Capacity


HRLE090-A-20/40




- * The pump capacity is the capacity of CH1 when 2 l/min are applied to CH2.

Dimensions

HRLE090-A-20/40



Parts Description



HRLE Series Options

C Option symbol

With Compressor Inverter

HRLE090-A-□-C

● With compressor inverter

The compressor inverter increases the cooling capacity of the 50 Hz area to that of the 60 Hz area. (Refer to the 60 Hz graph under “Cooling Capacity” on page 3.)

* No change in external dimensions

M Option symbol

Applicable to DI Water Piping

HRLE090-A-□-M

● Applicable to DI water piping

The contact materials of the circulating fluid circuit are made from non-copper materials.

Applicable model	HRLE090-A-□-M
Contact materials of circulating fluid	Stainless steel (including heat exchanger brazing), SiC, Carbon, PA, PP, PE, POM, FKM, EPDM, PVC, PTFE

* No change in external dimensions

P Option symbol

With Pump Inverter


HRLE090-A-□-P

● With pump inverter

The pump inverter increases the pump capacity of the 50 Hz area to that of the 60 Hz area.

Pressure setting is also available, allowing for auto control to any pressure without the need for valve position adjustments.

* No change in external dimensions



* The pump capacity is the capacity of CH1 when 2 l/min are applied to CH2.

HRLE Series

Optional Accessories

Optional Accessories List

No.	Description	Part no.	Applicable model
①	G thread conversion fitting set	HRL-EP003	Converts the piping connection port from Rc to G
		HRL-EP011	Select the HRL-EP011 when using the HRL-JK001.
②	NPT thread conversion fitting set	HRL-EP004	Converts the piping connection port from Rc to NPT
		HRL-EP012	Select the HRL-EP012 when using the HRL-JK001.
③	Bypass piping set	HRL-BP001	When the circulating fluid flow rate falls below the min. required flow rate, the temperature stability declines. The min. required flow rate can be secured by connecting bypass piping.
④	Electric conductivity control set	HRL-DI001	This set can be used to display and control the electric conductivity of the circulating fluid.
⑤	Particle filter set	HRL-PF001	Allows you to remove foreign matter from CH1
		HRL-PF002	Allows you to remove foreign matter from CH2
⑥	Handle	HRS-S0600	A handle for the HRL-PF001 used for filter vessel removal
		HRR-S0079	A handle for the HRL-PF002 used for filter vessel removal
⑦	Filter for circulating fluid fill port	HRS-PF007	Prevents foreign matter from entering the tank when supplying the circulating fluid
⑧	Automatic water fill setting	HRL-JK001	Automatically refills the tank when the circulating fluid level decreases
⑨	Ball valve set (With pressure gauge)	HRL-BB001	Allows you to adjust the circulating fluid pressure and flow rate



SMC Corporation (Europe)

Austria	+43 (0)2262622800	www.smc.at	office@smc.at
Belgium	+32 (0)33551464	www.smc.be	info@smc.be
Bulgaria	+359 (0)2807670	www.smc.bg	office@smc.bg
Croatia	+385 (0)13707288	www.smc.hr	office@smc.hr
Czech Republic	+420 541424611	www.smc.cz	office@smc.cz
Denmark	+45 70252900	www.smcdk.com	smc@smcdk.com
Estonia	+372 6510370	www.smcpcneumatics.ee	info@smcee.ee
Finland	+358 207513513	www.smc.fi	smcfi@smc.fi
France	+33 (0)164761000	www.smc-france.fr	info@smc-france.fr
Germany	+49 (0)61034020	www.smc.de	info@smc.de
Greece	+30 210 2717265	www.smchellas.gr	sales@smchellas.gr
Hungary	+36 23513000	www.smc.hu	office@smc.hu
Ireland	+353 (0)14039000	www.smcautomation.ie	sales@smcautomation.ie
Italy	+39 03990691	www.smcitalia.it	mailbox@smcitalia.it
Latvia	+371 67817700	www.smc.lv	info@smc.lv

Lithuania	+370 5 2308118	www.smclt.lt	info@smclt.lt
Netherlands	+31 (0)205318888	www.smc.nl	info@smc.nl
Norway	+47 67129020	www.smc-norge.no	post@smc-norge.no
Poland	+48 222119600	www.smc.pl	office@smc.pl
Portugal	+351 214724500	www.smc.eu	apoioclientept@smc.smces.es
Romania	+40 213205111	www.smcromania.ro	smcromania@smcromania.ro
Russia	+7 8123036600	www.smc.eu	sales@smcru.com
Slovakia	+421 (0)413213212	www.smc.sk	office@smc.sk
Slovenia	+386 (0)73885412	www.smc.si	office@smc.si
Spain	+34 945184100	www.smc.eu	post@smc.smces.es
Sweden	+46 (0)86031200	www.smc.nu	smc@smc.nu
Switzerland	+41 (0)523963131	www.smc.ch	helpcenter@smc.ch
Turkey	+90 212 489 0 440	www.smcpcnomatik.com.tr	info@smcpcnomatik.com.tr
UK	+44 (0)845 121 5122	www.smc.uk	sales@smc.uk