


ON 9M0


SPECIFICATIONS

OPERATING PRESSURE(IN-OUT) MPa	0.1~0.5
MEDIA	PURE WATER·CHEMICAL LIQUID
FLUID TEMPERATURE °C	0~80
AMBIENT TEMPERATURE °C	0~60
PORT SIZE	TUBE SIZE 0.D.3/8"
△ CRACKING PRESSURE kPa	5 OR LESS



SPECIAL SPECIFICATIONS

- 1) LQ3 CONNECTION (TUBE SIZE: 3/8")
- 2) NUT MATERIAL: PFA



				FINISH	
				PAINT	
1	ADDITION CRACKING PRESSURE	2014-03-13	A. Sato	LV30***-DMR2194	
-	INITIAL RELEASE	2011-01-27	A. Sato	-	
REV. QTY	DESCRIPTION	DATE PREPARED	REV. NO	MATERIAL	MODEL QTY
TOLERANCES JIS B 0405		DRAWN	R. Watanabe	SCALE	THIRD ANGLE
GRADE		DATE	2014-03-13	FREE	
RANGE (mm)	f ±	m ±	c ±	DWG NAME	
0.5 ≤ D ≤ 3	0.05	0.1	0.2	CHECK VALVE	
3 < D ≤ 6	0.05	0.1	0.3	DWG NO	
6 < D ≤ 30	0.1	0.2	0.5	© LVK30-Z11	
30 < D ≤ 120	0.15	0.3	0.8	REVISION	
120 < D ≤ 400	0.2	0.5	1.2	1	
400 < D ≤ 1000	0.3	0.8	2		
1000 < D ≤ 2000	0.5	1.2	3		
DESIGNED	A. Sato	CHECKED	Y. Okita		
DATE	2014-03-13	DATE	2014-03-14		
APPROVED	T. Maruyama	DATE	2014-03-17		

FINISH: 表面处理 / PAINT: 塗装 / PACKING: 包装区分
 MATERIAL: 材質 / MATERIAL SIZE: 材料寸法

DWG NAME

DWG REC


DWG ID BA22456802

SMC Corporation

ON 9MO


SPECIFICATIONS

OPERATING PRESSURE(IN-OUT) MPa	0.1~0.5
MEDIA	PURE WATER·CHEMICAL LIQUID
FLUID TEMPERATURE °C	0~80
AMBIENT TEMPERATURE °C	0~60
PORT SIZE	TUBE SIZE O.D.1/2"
△ CRACKING PRESSURE kPa	5 OR LESS



SPECIAL SPECIFICATIONS

- 1) LQ3 CONNECTION (TUBE SIZE: 1/2")
- 2) NUT MATERIAL: PFA



				FINISH		
				PAINT		
				PACKING		
1 ADDITION CRACKING PRESSURE 2014-03-13 A.Sato LV30***-DMR2194 - INITIAL RELEASE 2011-01-27 A.Sato -				MATERIAL		MODEL QTY
REV	QTY	DESCRIPTION	DATE PREPARED	REV NO		
TOLERANCES JIS B 0405 GRADE RANGE (mm) f m c 0.5 ≤ D ≤ 3 ± 0.05 ± 0.1 ± 0.2 3 < D ≤ 6 ± 0.05 ± 0.1 ± 0.3 6 < D ≤ 30 ± 0.1 ± 0.2 ± 0.5 30 < D ≤ 120 ± 0.15 ± 0.3 ± 0.8 120 < D ≤ 400 ± 0.2 ± 0.5 ± 1.2 400 < D ≤ 1000 ± 0.3 ± 0.8 ± 2 1000 < D ≤ 2000 ± 0.5 ± 1.2 ± 3			DRAWN R.Watanabe DATE 2014-03-13 DESIGNED A.Sato DATE 2014-03-13 CHECKED Y.Okita DATE 2014-03-14 APPROVED T.Maruyama DATE 2014-03-17	SCALE FREE DWG NAME CHECK VALVE DWG NO © LVK40-Z13 REVISION 1	THIRD ANGLE	

FINISH: 表面处理 / PAINT: 塗装 / PACKING: 包装区分
 MATERIAL: 材質 / MATERIAL SIZE: 材料寸法

DWG NAME

DWG REC


DWG ID BA22457302

SMC Corporation


ON 9MO

SPECIFICATIONS

OPERATING PRESSURE(IN-OUT) MPa	0.1~0.5
MEDIA	PURE WATER·CHEMICAL LIQUID
FLUID TEMPERATURE °C	0~80
AMBIENT TEMPERATURE °C	0~60
PORT SIZE	TUBE SIZE 0.D.3/4"
△ CRACKING PRESSURE kPa	3 OR LESS




TUBE SIZE O.D. 3/4"



SPECIAL SPECIFICATIONS

- 1) LQ3 CONNECTION (TUBE SIZE: 3/4")
- 2) NUT MATERIAL: PFA



				FINISH	
				PAINT	
△ 1	ADDITION CRACKING PRESSURE	2014-03-13	A. Sato	LV30***-DMR2194	
△ 0	INITIAL RELEASE	2011-01-27	A. Sato	-	
REV	QTY	DESCRIPTION	DATE PREPARED	REV NO	MODEL QTY
TOLERANCES JIS B 0405		DRAWN	R. Watanabe	SCALE	
GRADE		DATE	2014-03-13	FREE	
RANGE (mm)	f ±	m ±	c ±	DESIGNED	A. Sato
0.5 ≤ D ≤ 3	0.05	0.1	0.2	DATE	2014-03-13
3 < D ≤ 6	0.05	0.1	0.3	CHECKED	Y. Okita
6 < D ≤ 30	0.1	0.2	0.5	DATE	2014-03-14
30 < D ≤ 120	0.15	0.3	0.8	APPROVED	T. Maruyama
120 < D ≤ 400	0.2	0.5	1.2	DATE	2014-03-17
400 < D ≤ 1000	0.3	0.8	2	DWG NO	
1000 < D ≤ 2000	0.5	1.2	3	© LVK50-Z19	
				THIRD ANGLE	
				DWG NAME	CHECK VALVE
				REVISION	1

FINISH: 表面处理 / PAINT: 塗装 / PACKING: 包装区分
 MATERIAL: 材質 / MATERIAL SIZE: 材料寸法

DWG NAME

DWG REC

DWG ID BA22457902

SMC Corporation